


DAC25-FWX Series 25 Watt AC/DC Power Supply



Dual Output

Isolated output 3000VAC

Internal Input Filter

Up to 80% Efficiency

Encapsulated compact size 3" X2"

EN62368-1, CE recognized

ITE & AC Motor Applications

3 year Warranty

-DAC25-20: 5V, 5V - DAC25-21: 5V, 24V

-DAC25-22: 12V, 12V - DAC25-23: 15V, 15V

-DAC25-24: 5V, 12V - DAC25-25: 5V, 15V

- DAC25-26: 24V, 24V - DAC25-27: 3.3V, 5V




		UNIT			
INPUT	Voltage/Freq	V	Universal Input voltage AC 90V ~ 264V 100~240 VAC 47 ~ 63Hz		
	Current Typ. 110V 220V	A			
	Min. Load	-	20%		
	Inrush Current	A	115V 12A (Ta=25°C, Io=100% at cold Start); 230V 20A (Ta=25°C, Io=100% at cold Start)		
	Line Frequency	Hz	47 ~ 63 Typ. 50/60		

		UNIT	DAC25-20FWX	DAC25-21FWX	DAC25-22FWX	DAC25-23FWX
OUTPUT	Nominal Voltage	VDC	+/- 5	+5 /+24	+/- 12	+/- 15
	Efficiency typ	%	75	78	78	80
	Current	A	+/- 2.5	+2.4/+ 0.5	+/- 1.0	+/- 0.8
	Transient Recovery time	us	Vi nom, Io nom = 0.5 Io nom Typ. 1000us			
	Line Regulation	%	+/-1%	+/-1%	+/-1%	+/-1%
	Load Regulation	%	+/-5%	+/-5%	+/-5%	+/-5%
	Ripple Noise 20MHz BW full load	mVp-p	150	100/150	150	150
	Voltage Accuracy	%	5	5	5	5
	Over Load Protection	-	Auto Recovery			
	Short Circuit Protection	-	CONT. Auto Recovery			
	Over Voltage Protection	-	120%-150% rated output Voltage Protection type: Zener diode clamp			

	UNIT	DAC25-24FWX	DAC25-25 FWX	DAC25-26FWX	DAC25-27FWX	
OUTPUT	Nominal Voltage	VDC	+5/+12	+5 /+15	+/-24	+3.3 / +5
	Efficiency typ	%	76	76	80	76
	Current	A	+2.4/+1.0	+2.4/+ 0.8	+/- 0.5	2.5 / 1.0
	Transient Recovery time	us	Vi nom, Io nom = 0.5 Io nom Typ. 1000us			
	Line Regulation	%	+/-1%	+/-1%	+/-1%	+/-1%
	Load Regulation	%	+/-5%	+/-5%	+/-5%	+/-5%
	Ripple Noise 20MHz BW full load	mVp-p	150/240	150/240	150	150/240
	Voltage Accuracy	%	5	5	5	5
	Over Load Protection -		Auto Recovery			
	Short Circuit Protection -		CONT. Auto Recovery			
	Over Voltage Protection		120%-150% rated output Voltage Protection type: Zener diode clamp			

Isolation	Isolation Voltage	Input / Output 3KVac/ 5mA/5Secs
	Isolation Capacitance	
	Isolation Resistance	Input / Output, @500 Vdc 100MΩ
Environment	Operating Temp/Hum.	-20~ +75%
	Storage Temp/Hum.	-40 ~ +85% HUMIDITY 95% 5RH%
	Derating	Vi nom, Io nom+51 to 71°C 2 %/°C
Safety	CE	EN62368-1
	EMI Conduction & Radiation	Compliance to EN55032
	EMS Immunity	Compliance to EN55024
Size	MM	76.2 X 50.8 X 25.4 (mm) 3" X 2" X 1" 112 grams


OUTPUT DERATING CURVE AND RECCOMENDED MOUNTING DIAGRAM



Terminal Output

PIN	Model		
	Single	Dual	Dual
1	FG	FG	FG
2	ACN	ACN	ACN
3	ACL	ACL	ACL
4	-Vo	-Vo	+Vo2
5	NO PIN	Com	Com
6	+Vo	+Vo	+Vo1

DIMENSIONAL DRAWING (mm)





Unit: mm unless otherwise specified, all tolerances are ±0.50



BLOCK DIAGRAM

Dual Output



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ETA-USA:](#)

[DAC25-20FWX](#) [DAC25-21FWX](#) [DAC25-22FWX](#) [DAC25-23FWX](#) [DAC25-24FWX](#) [DAC25-25FWX](#) [DAC25-26FWX](#)
[DAC25-27FWX](#)