



ST1 SERIES TOGGLE SWITCH

ANTI-VANDAL SWITCHES
DETECTOR SWITCHES
DIP SWITCHES
KEYLOCK SWITCHES
NAVIGATION SWITCHES
PUSHBUTTON SWITCHES
ROCKER SWITCHES
ROTARY SWITCHES
SLIDE SWITCHES
SNAP ACTION SWITCHES
TACTILE SWITCHES
TOGGLE SWITCHES
CAP OPTIONS



APPLICATIONS / MARKETS



RoHS

SPECIFICATIONS

Rating: Maintained Switches: 20A 125VAC [cULus]
15A 277VAC [cULus]
2.0HP 125-277VAC [cULus]
Momentary Switches: 20A 125VAC [cULus]
15A 277VAC [cULus]
1.5HP 125-277VAC [cULus]

Electrical Life: 6,000 cycles

Contact Resistance: 50mΩ Max.

Insulation Resistance: 2MΩ Min. at 500VDC for 1 Minute

Dielectric Strength: 1,000VAC for 1 Minute

Operating Temperature: 0°C to 85°C

Storage Temperature: -20°C to 85°C

Mounting Nut Torque: 0.6Nm~1.0Nm

FEATURES & BENEFITS

- Heavy duty rating with UL approvals
- Many functions available
- Tab, screw, and solder terminal options
- Soldered wire leads (500mm long) optional

PART NUMBER CONFIGURATOR

Series



ST1 - 1 Pole

Terminal



1 - 4.8mm Tabs
2 - Solder
4 - 6.3mm Tabs
6 - Screw
W - Wire Leads
500mm long

Function



1 - 1 Pole Off - On
3 - 1 Pole On - On
4 - 1 Pole Off - (On)
Middle - End
5 - 1 Pole
On - Off - On
C - 1 Pole
On - Off - (On)
D - 1 Pole
(On) - Off - (On)

Rating



D - 20A 125VAC

Actuator Type



0 - Standard Bat
1 - Short Bat

Bushing Type



0 - M12 x 1.0
2 - 15/32" - 32UNS

NOTES:

() = Denotes function is momentary

Specifications subject to change without notice 2.16.2022



E-SWITCH®


www.e-switch.com

800.867.2717


1

ST1 SERIES TOGGLE SWITCH


TERMINAL OPTIONS




1 = 4.8mm TABS



2 = SOLDER



4 = 6.3mm TABS



6 = SCREW



E-SWITCH®

www.e-switch.com

800.867.2717


2

ANTI-VANDAL SWITCHES
DETECTOR SWITCHES
DIP SWITCHES
KEYLOCK SWITCHES
NAVIGATION SWITCHES
PUSHBUTTON SWITCHES
ROCKER SWITCHES
ROTARY SWITCHES
SLIDE SWITCHES
SNAP ACTION SWITCHES
TACTILE SWITCHES
TOGGLE SWITCHES
CAP OPTIONS

TERMINAL OPTIONS
(CONTINUED)

SWITCH	WIRE	LENGTH
SW1-1	WIRE, 18AWG AWM UL3266, GREEN	500.0 [19.7 in]
SW1-2	WIRE, 18AWG AWM UL3266, PINK	500.0 [19.7 in]
SW1-3	WIRE, 18AWG AWM UL3266, YELLOW	500.0 [19.7 in]


** WIRE LEADS PROVIDED ARE DEPENDANT ON THE FUNCTION SELECTED **



W = WIRED LEADS 500mm

FUNCTION OPTIONS


FUNCTIONS: 1, 3, & 4



FUNCTION	POS. 1 	POS. 2 	POS. 3 
1 - OFF - ON	OFF	N/A	ON
3 - ON - ON	ON	NA	ON
4-OFF-(ON)MIDDLE-END	(ON)	OFF	N/A
TERMINAL CLOSURES	1-3	N/A	1-3

() = DENOTES MOMENTARY

FUNCTIONS: 5, C, & D




FUNCTION	POS. 1 	POS. 2 	POS. 3 
5 - ON - OFF - ON	ON	OFF	ON
C - ON - OFF - (ON)	ON	OFF	(ON)
D - (ON) - OFF - (ON)	(ON)	OFF	(ON)
TERMINAL CLOSURES	2-3	N/A	1-2

() = DENOTES MOMENTARY




ST1 SERIES TOGGLE SWITCH

ACTUATOR OPTIONS




0 = STANDARD BAT




1 = SHORT BAT

BUSHING OPTIONS




0 = M12 X 1.0




2 = 15/32"-32UNS

PANEL CUTOUT OPTIONS



RECOMMENDED PANEL CUTOUT



ALTERNATE PANEL CUTOUT



E-SWITCH®

www.e-switch.com

800.867.2717

5

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

E-Switch:

[ST14DD00](#) [ST143D00](#) [ST145D00](#) [ST141D00](#) [ST144D00](#) [ST145D10](#) [ST161D00](#) [ST141D10](#) [ST16DD00](#)
[ST164D00](#) [ST161D02](#) [ST165D00](#) [ST123D00](#) [ST143D10](#) [ST124D00](#) [ST12DD00](#) [ST144D10](#) [ST14DD10](#)
[ST163D00](#) [ST121D00](#) [ST14CD00](#) [ST161D10](#) [ST125D00](#) [ST115D00](#) [ST141D02](#) [ST143D02](#) [ST1WDD10](#)
[ST121D02](#) [ST141D12](#)