




RECOMMENDED
PANEL CUT OUT




▲ SWITCH FUNCTION		
POS. 1	POS. 2	POS. 3
OFF	N/A	ON
OPEN	N/A	1-3

NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X = ± 0.5
X.XX = ± 0.25
3. TERM. NOS. FOR REFERENCE ONLY
4. ELECTRICAL LIFE: 6,000 CYCLES
5. OPERATING TEMP: 0°C to 85°C
6. CONTACT RESISTANCE: 50mΩ MAX. INITIAL
7. INSULATION RESISTANCE: 2MΩ AT 500VDC
8. DIELECTRIC STRENGTH: 1000VAC FOR 1 MINUTE
9. ▲ DENOTES CRITICAL PARAMETER
10. CONTACT RATING: 20A 125VAC,
15A 277VAC
2HP 125/277VAC
- ▲ 11. SUPPLIED HARDWARE: 2 HEXNUTS




Ø6.00
[Ø.236 in]



▲ M12 X 1.0
(HARDWARE
NOT SHOWN)

▲ 6.30
[.248 in]

REV	ECO NO	DESCRIPTION	DATE	BY	 E-SWITCH®				OBJECT ID
D	ECO-101417	correct Switch Function	05/22/23	MW	TITLE ST141D10				000001068
					SCALE	DATE	DR	DWG	REV
					1:1	3/18/2010	CAB	34-ST141D10	D

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[ST141D10](#)