

VTA-C/D

25W



FEATURES

- Variety of Models
- Chassis mount type
- Compact and High Efficiency
- Triple Output
- Isolated Power Supply

MODEL/CHANNEL		Unit	VTA01-C/D			VTA01-CB/DB			VTA03-C/D			VTA04-C/D		
OUTPUT (Double)	Output Current	Vdc	5	+12	-12	+12	+5	-12	+5	+12	-5	+5	+15	-15
	Output Current 25W (24, 48V)	A	2.8	0.5	0.4	1.5	0.7	0.25	2.8	0.5	0.5	2.8	0.36	0.36
	Output Current 30W (24, 48V)	A	3	0.75	0.5	1.7	0.8	0.3	3	0.75	0.75	3	0.5	0.5
	Line Regulation (12, 24, 110V)	mV	40	96	96	96	40	96	40	96	40	40	120	120
	Line Regulation (48V)	mV	35	84	84	84	35	84	35	84	35	35	105	105
	Load Regulation	mVp	50	120	120	120	50	120	50	120	50	50	150	150
	Ripple and Noise	mVp	100	170	170	170	100	170	100	170	100	100	200	200
	Drift	mV	40	75	75	75	40	75	40	75	40	40	90	90
	Dynamic Load Regulation	mV	150	360	360	360	150	360	150	360	150	150	450	450
	Voltage Adjustment Range	-	V1: +/-5%(maximum) of Rated Output Voltage at 25°C, rated input and no load V2, V3: fixed with tolerance +/-3.5% of Rated Output Voltage at 25°C, rated input and no load											
	Rise Up Time	mS	200mS(maximum) at 25°C and rated input/output											
	Temp. Coefficient	°C	0.03%/°C											
	Recovery Time	mS	0.5mS(typical)											
	Hold Up Time	mS	Not specified (Vin=110 10mS(maximum) at 25°C and rated input/output)											
MODEL/CHANNEL		Unit	VTA01C12			VTA01C12B			VTA03-12			VTA04B-12		
INPUT	Input Voltage 12V	Vdc	DC 12V											
	Input Voltage Range	Vdc	DC 9.2V-16V											
	Efficiency	%	75			77			73			75		
	MTBF	H	520,000											
	Switching Frequency	-	40 Fix											

VTA-C/D

25W


MODEL/CHANNEL		Unit	VTA01C24	VTA01C24B	VTA03C24	VTA04C24
	Input Voltage 24V	Vdc	DC 24V			
	Input Voltage Range	Vdc	DC 19-32V			
	Efficiency	%	75			
	MTBF	H	520,000			
	Switching Frequency	-	40 Fix			
MODEL/CHANNEL		Unit	VTA01C48	VTA01C48B	VTA03C48	VTA04C48
	Input Voltage 48V	Vdc	DC 48V			
	Input Voltage Range	Vdc	DC 38-63V			
	Efficiency	%	72	77	74	75
	MTBF	H	520,000			
	Switching Frequency	-	37 Fix			
MODEL/CHANNEL		Unit	VTA01D	VTA01DB	VTA03D	VTA04D
	Input Voltage 110V	Vdc	DC 110V			
	Input Voltage Range	Vdc	DC 85-140V			
	Input Current	A	20A(maximum)			
	Efficiency	%	75	73	77	75
	MTBF	H	500,000			
	Switching Frequency	-	43 Fix			
MODEL/CHANNEL		Unit				
Environment	Operating Temperature	°C	0 to +50°C			
	Operating Humidity	%	85%RH(non-condensing)			
	Storage Temperature	°C	-20 to +85°C			
	Withstand Voltage	%	Primary-Secondary AC1,500Vfor 1minute (Vin=110 2000) Primary-Frame Ground AC1,500V for 1minute (Vin=110 2000) Secondary-Frame Ground AC500V for 1minute			
	Isolation Resistance	-	Primary-Secondary-Frame Ground 50MΩ(minimum) by DC500V insulation tester			
	Shock	-	294m/s^2			
	Cooling	-	Convection			
	Vibration	-	5-10Hz: 10mm double amplitude,10-55Hz: 19.6m/s^2, 20 minutes period for 60 minutes each along X, Y, Z axes(non-operating)			
Protection	Over Current Protection	A	Current Limiting with automatic recovery			
	Over Voltage Protection	-	zener diode clamping			
	Reverse Voltage Protection	-	by internal fuse (Vin=110 by internal bridge diode)			
Dimension	Size(WxHxD) / Weight	mm/g	85Wx135Lx31H/390g			







ETA-USA

The Power Professionals

Block Diagram



OCP Curve



ETA-USA

3170 Vineyard Blvd. Suite 180 Morgan Hill, CA 95037 <http://www.eta-usa.com>
Toll-free (US only): 800-ETA-POWR (800-382-7697) Telephone: 408 778-2793 FAX: 408-779-2753

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ETA-USA:](#)

[VTA03C12](#) [VTA03C48](#) [VTA03C24](#) [VTA01C12](#) [VTA01C48](#) [VTA01C24](#) [VTA04C24](#) [VTA04C48](#) [VTA04C12](#)