



**SCHEMATIC**  
 ▲ ON - (ON)  
 DPDT Illuminated  
 ( ) DENOTES MOMENTARY FUNCTION



- NOTE:**
1. ALL DIMENSIONS IN MM [INCH]
  2. GENERAL TOLERANCE: X.X =  $\pm 0.4$   
X.XX =  $\pm 0.25$
  3. TERMINAL NUMBERS FOR REF ONLY
  - ▲ 4. CONTACT MATERIAL: SILVER
  5. RATING: 3A 250 VAC cUL
  6. ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
  7. MECHANICAL LIFE: 1,000,000 CYCLES.
  8. INSULATION RESISTANCE: 1,000 M $\Omega$  @ 500VDC MIN.
  9. DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
  10. CONTACT RESISTANCE: 50m $\Omega$  MAX. @ 1A 12VDC
  11. OPERATING TEMP.: -20°C to 55°C
  12. ▲ DENOTES CRITICAL PARAMETER.
  - ▲ 13. LAMP VOLTAGE: 20mA 3V
  14. TRAVEL: 3.2mm
  15. ACTUATION FORCE: 3.5  $\pm$  1.0 N
  16. MOUNTING NUT TORQUE: 5-14 Nm
  17. INGRESS PROTECTION: IP67
  18. HARDWARE SUPPLIED: O-RING AND HEXNUT



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
C	ECO-100297	UPDATE PANEL CUTOOUT	09/23/21	JM	TITLE ULV7F2H11311				000026290
					SCALE	DATE	DR	DWG	REV
					3:2	7/24/2015	RC	T970007	C

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[ULV7F2H11311](#)