





▲ ACTUATOR SPRING
LOCATION TO IDENTIFY
TERMINAL ORIENTATION



NOTES:

1. ALL DIMENSIONS IN mm [INCHES]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 0.1A; 30V
5. CONTACT RESISTANCE: 50 MILLI-OHMS MAX INITIAL.
6. TIMING: NON-SHORTING
- ▲ 7. TRAVEL: FULL 1.8mm; 1.0 TO LOCK POSITION
8. OPERATING FORCE: 150 ± 50 gf
9. ELECTRICAL LIFE: 10,000 CYCLES MAKE AND BREAK
CYCLES AT FULL LOAD
10. ▲ DENOTE CRITICAL PARAMETER

REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
B	ECO-101489	update print	01/15/23	MW	TITLE TL2203EE				000017802
					SCALE	DATE	DR	DWG	REV
					3:1	12/17/2012	rc	P010406	B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[TL2203EE](#)