





▲ CIRCUIT: SPST



## NOTES

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=± 0.4  
X.XX=± 0.25
3. TERMINAL NUMBERS FOR REF. ONLY.
- ▲ 4. OPERATING FORCE:  $300 \pm 50$ gf
5. OPERATING LIFE: 500,000 CYCLES
6. TRAVEL:  $0.5 \pm 0.15$ mm
7. CONTACT RATING: 12VDC @ 50mA
8. CONTACT RESISTANCE:  $100\text{m } \Omega$  MAX
9. INSULATION RESISTANCE:  $100\text{M } \Omega$  MIN @ 100VDC.
- ▲ 10. CONTACT MATERIAL: SILVER
11. OPERATING TEMPERATURE:  $-40^\circ\text{C}$  TO  $85^\circ\text{C}$
12. PACKAGING: TUBE 60 PCS. PER
13. ▲ DENOTES CRITICAL PARAMETER
14. 2002/95/EC (ROHS) COMPLIANT



TITLE TL6100DF300QP

|     |        |             |         |    |
|-----|--------|-------------|---------|----|
| A   | 21179  | New Release | 7/23/13 | rc |
| REV | PCR NO | DESCRIPTION | DATE    | BY |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

|       |                   |          |                |          |
|-------|-------------------|----------|----------------|----------|
| SCALE | DATE<br>5/31/2013 | DR<br>rc | DWG<br>T350013 | REV<br>A |
|-------|-------------------|----------|----------------|----------|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[TL6100DF300QP](#)