







▲ CIRCUIT LAYOUT

PANEL MOUNTING

PANEL MOUNTING	
PANEL THICK	(W) DIMENSION
0.75 - 1.25	17.6 - 17.8
1.25 - 2.0	17.8 - 18.0
2.0 - 3.0	18.0 - 18.2

▲ ILLUMINATION
COLOR: RED/YELLOW

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25

3. TERM. NOS. FOR REFERENCE ONLY.

- ▲ 4. CONTACT RATING: 0.5A @ 100VAC
0.2A @ 250VAC
0.5A @ 25VDC

5. CONTACT MATERIAL: SILVER

6. ELECTRICAL LIFE: 200,000 Typical

7. MECHANICAL LIFE: 1,000,000 CYCLES TYP.

8. CONTACT RESISTANCE: 50 mΩ INITIAL TYP. MAX.

9. DIELECTRIC STRENGTH: 1,000 VAC FOR 1 MIN.

10. TRAVEL TO MAKE: 2.20mm ±0.2

11. OPERATING FORCE: 200 +/- 100 gf

12. OPERATING TEMPERATURE: -20° to +70°C

13. ▲ DENOTES CRITICAL PARAMETER

- ▲ 14. LED COLOR: RED: 3 CHIPS; 1.95-2.5 VDC @20mA TYP.
YEL: 3 CHIPS; 1.5-2.3 VDC @20mA TYP.

REV	ECO NO	DESCRIPTION	DATE	BY
B	ECO-101562	DIM 19.5+/-0.50 WAS 19.50	02/22/23	JS



E-SWITCH®

OBJECT ID
000006909

TITLE ULP12OAM1QPMCL1REDYEL

SCALE
3:2

DATE
12/21/2011

DR
BGL

DWG
B810040

REV
B

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[ULP12OAM1QPMCL1REDYEL](#)