






SWITCH SCHEMATIC
(MOMENTARY)



PCB MOUNTING

NOTES:

1. ALL DIMENSIONS IN MM
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. CONTACT RATING: 0.1A Max. @ 28VDC
- ▲ 5. CONTACT MATERIAL: GOLD
6. ELECTRICAL LIFE: 200,000 Typical
7. MECHANICAL LIFE: 1,000,000 CYCLES TYP.
8. OPERATING TEMP: -40°C to +85°C
9. OPERATING FORCE: 200 $\pm$ 100 gf
10. CONTACT RESISTANCE: 100 MILLI-OHM INITIAL TYP. MAX.
11. DIELECTRIC STRENGTH: 1000 VAC FOR 1 MINUTE
12. TRAVEL TO MAKE: 2.20mm $\pm$ 0.2
13. 2011/65/EU (ROHS) COMPLIANT
14. ▲ DENOTES CRITICAL PARAMETER
- ▲ 15. LED COLOR: RED: 1 CHIP, 2.1-2.5 VDC@20mA
GRN: 1 CHIP, 3.2-4.0 VDC@20mA
BLU: 1 CHIP, 3.1-3.8 VDC@20mA



E	22858	update Note 15	5/23/17	MW
D	22350	SHOW "E" ON BOTTOM VIEW	6/16/16	MW
C	21141	CORRECT PIN DIMENSIONS, TITLE	5/29/13	EBP
B	19751	UPDATE DRAWING	03/10/11	BMA
A	18455	RELEASED FOR PRODUCTION	03/16/09	BLR
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED



TITLE **ULP12OAP1RSSCL1RGB**

SCALE
1.5:1

DATE
3/16/2009

DR
BF

DWG
B800053

REV
E

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[ULP12OAP1RSSCL1RGB](#)