



SIMATIC ET 200SP, Analog input module, AI 8xRTD/TC 2-wire High Feature Pack
quantity: 10 units, suitable for BU type A0, A1, Color code CC00, channel
diagnostics, 16 bit, +/-0.1%

General information	
Product type designation	AI 8xRTD/TC 2-wire HF
HW functional status	From FS05
Firmware version	
• FW update possible	Yes
usable BaseUnits	BU type A0, A1
Color code for module-specific color identification plate	CC00
Product function	
• I&M data	Yes; I&M0 to I&M3
• Isochronous mode	No
• Measuring range scalable	Yes
Engineering with	
• STEP 7 TIA Portal configurable/integrated from version	V14 / -
• STEP 7 configurable/integrated from version	V5.6
• PROFIBUS from GSD version/GSD revision	One GSD file each, Revision 3 and 5 and higher
• PROFINET from GSD version/GSD revision	GSDML V2.3
Operating mode	
• Oversampling	No
• MSI	No
CiR - Configuration in RUN	
Reparameterization possible in RUN	Yes
Calibration possible in RUN	Yes
Supply voltage	
Rated value (DC)	24 V
permissible range, lower limit (DC)	19.2 V
permissible range, upper limit (DC)	28.8 V
Reverse polarity protection	Yes
Input current	
Current consumption, max.	35 mA
Power loss	
Power loss, typ.	0.75 W
Address area	
Address space per module	
• Address space per module, max.	16 byte; + 1 byte for QI information
Hardware configuration	
Automatic encoding	Yes
• Mechanical coding element	Yes
• Type of mechanical coding element	Type A
Selection of BaseUnit for connection variants	
• 2-wire connection	BU type A0, A1

Analog inputs	
Number of analog inputs	8
permissible input voltage for voltage input (destruction limit), max.	30 V
Constant measurement current for resistance-type transmitter, typ.	2 mA
Cycle time (all channels), min.	Sum of the basic conversion times and additional processing times (depending on the parameterization of the active channels)
Technical unit for temperature measurement adjustable	Yes; °C/°F/K
Input ranges (rated values), voltages	
• -1 V to +1 V — Input resistance (-1 V to +1 V) • -250 mV to +250 mV — Input resistance (-250 mV to +250 mV) • -50 mV to +50 mV — Input resistance (-50 mV to +50 mV) • -80 mV to +80 mV — Input resistance (-80 mV to +80 mV)	- Yes; 16 bit incl. sign 1 MΩ - Yes; 16 bit incl. sign 1 MΩ - Yes; 16 bit incl. sign 1 MΩ - Yes; 16 bit incl. sign 1 MΩ
Input ranges (rated values), thermocouples	
• Type B — Input resistance (Type B) • Type C — Input resistance (Type C) • Type E — Input resistance (Type E) • Type J — Input resistance (type J) • Type K — Input resistance (Type K) • Type L — Input resistance (Type L) • Type N — Input resistance (Type N) • Type R — Input resistance (Type R) • Type S — Input resistance (Type S) • Type T — Input resistance (Type T) • Type U — Input resistance (Type U) • Type TXK/TXK(L) to GOST — Input resistance (Type TXK/TXK(L) to GOST)	- Yes; 16 bit incl. sign 1 MΩ - Yes; 16 bit incl. sign 1 MΩ - Yes; 16 bit incl. sign 1 MΩ - Yes; 16 bit incl. sign 1 MΩ - Yes; 16 bit incl. sign 1 MΩ - Yes; 16 bit incl. sign 1 MΩ - Yes; 16 bit incl. sign 1 MΩ - Yes; 16 bit incl. sign 1 MΩ - Yes; 16 bit incl. sign 1 MΩ
Input ranges (rated values), resistance thermometer	
• Ni 100 — Input resistance (Ni 100) • Ni 1000 — Input resistance (Ni 1000) • LG-Ni 1000 — Input resistance (LG-Ni 1000) • Ni 120 — Input resistance (Ni 120) • Ni 200 — Input resistance (Ni 200) • Ni 500 — Input resistance (Ni 500) • Pt 100 — Input resistance (Pt 100) • Pt 1000 — Input resistance (Pt 1000) • Pt 200 — Input resistance (Pt 200)	- Yes; 16 bit incl. sign 1 MΩ - Yes; 16 bit incl. sign 1 MΩ - Yes; 16 bit incl. sign 1 MΩ - Yes; 16 bit incl. sign 1 MΩ - Yes; 16 bit incl. sign 1 MΩ - Yes; 16 bit incl. sign 1 MΩ - Yes; 16 bit incl. sign 1 MΩ - Yes; 16 bit incl. sign 1 MΩ - Yes; 16 bit incl. sign 1 MΩ

• Pt 500 — Input resistance (Pt 500)	Yes; 16 bit incl. sign 1 MΩ
Input ranges (rated values), resistors	
• 0 to 150 ohms — Input resistance (0 to 150 ohms)	Yes; 15 bit 1 MΩ
• 0 to 300 ohms — Input resistance (0 to 300 ohms)	Yes; 15 bit 1 MΩ
• 0 to 600 ohms — Input resistance (0 to 600 ohms)	Yes; 15 bit 1 MΩ
• 0 to 3000 ohms — Input resistance (0 to 3000 ohms)	Yes; 15 bit 1 MΩ
• 0 to 6000 ohms — Input resistance (0 to 6000 ohms)	Yes; 15 bit 1 MΩ
• PTC — Input resistance (PTC)	Yes; 15 bit 1 MΩ
Thermocouple (TC)	
Temperature compensation	
— parameterizable	Yes
— Reference channel of the module	Yes
— internal comparison point	Yes; with BaseUnit type A1
— Reference channel of the group	Yes
— Number of reference channel groups	4; Group 0 to 3
— fixed reference temperature	Yes
Cable length	
• shielded, max.	200 m; 50 m with thermocouples
Analog value generation for the inputs	
Measurement principle	integrating (Sigma-Delta)
Integration and conversion time/resolution per channel	
• Resolution with overrange (bit including sign), max.	16 bit
• Integration time, parameterizable	Yes
• Basic conversion time, including integration time (ms) — additional processing time for wire-break check	2 ms; In the ranges resistance thermometers, resistors and thermocouples
• Interference voltage suppression for interference frequency f1 in Hz	16.6 / 50 / 60 Hz
• Conversion time (per channel)	180 / 60 / 50 ms
Smoothing of measured values	
• Number of smoothing levels	4; None; 4/8/16 times
• parameterizable	Yes
Encoder	
Connection of signal encoders	
• for voltage measurement	Yes
• for resistance measurement with two-wire connection	Yes
• for resistance measurement with three-wire connection	No
• for resistance measurement with four-wire connection	No
Errors/accuracies	
Linearity error (relative to input range), (+/-)	0.01 %; ±0.1 % for resistance thermometers and resistance
Temperature error (relative to input range), (+/-)	0.0009 %/K; ±0.005 % / K at thermocouple
Crosstalk between the inputs, min.	-50 dB
Repeat accuracy in steady state at 25 °C (relative to input range), (+/-)	0.05 %
Operational error limit in overall temperature range	
• Voltage, relative to input range, (+/-)	0.1 %
• Resistance, relative to input range, (+/-)	0.1 %
Basic error limit (operational limit at 25 °C)	
• Voltage, relative to input range, (+/-)	0.05 %
• Resistance, relative to input range, (+/-)	0.05 %
Interference voltage suppression for $f = n \times (f_1 \pm 1 \%)$, f_1 = interference frequency	
• Series mode interference (peak value of interference < rated value of input range), min.	70 dB
• Common mode voltage, max.	10 V
• Common mode interference, min.	90 dB

Interrupts/diagnostics/status information			
Diagnostics function	Yes		
Alarms			
• Diagnostic alarm	Yes		
• Limit value alarm	Yes; two upper and two lower limit values in each case		
Diagnoses			
• Monitoring the supply voltage	Yes		
• Wire-break	Yes; channel by channel		
• Group error	Yes		
• Overflow/underflow	Yes; channel by channel		
Diagnostics indication LED			
• Monitoring of the supply voltage (PWR-LED)	Yes; green PWR LED		
• Channel status display	Yes; green LED		
• for channel diagnostics	Yes; red LED		
• for module diagnostics	Yes; green/red DIAG LED		
Potential separation			
Potential separation channels			
• between the channels	No		
• between the channels and backplane bus	Yes		
• between the channels and the power supply of the electronics	Yes		
Permissible potential difference			
between the inputs (UCM)	10 V DC		
Isolation			
Isolation tested with	707 V DC (type test)		
Ambient conditions			
Ambient temperature during operation			
• horizontal installation, min.	-30 °C; < 0 °C as of FS05		
• horizontal installation, max.	60 °C		
• vertical installation, min.	-30 °C; < 0 °C as of FS05		
• vertical installation, max.	50 °C		
Altitude during operation relating to sea level			
• Installation altitude above sea level, max.	5 000 m; Restrictions for installation altitudes > 2 000 m, see manual		
Dimensions			
Width	15 mm		
Height	73 mm		
Depth	58 mm		
Classifications			
		Version	Classification
	eClass	14	27-24-26-01
	eClass	12	27-24-26-01
	eClass	9.1	27-24-26-01
	eClass	9	27-24-26-01
	eClass	8	27-24-26-01
	eClass	7.1	27-24-26-01
	eClass	6	27-24-26-01
	ETIM	9	EC001596
	ETIM	8	EC001596
	ETIM	7	EC001596
	IDEA	4	3562
	UNSPSC	15	32-15-17-05
Approvals / Certificates			
General Product Approval			



[Manufacturer Declaration](#)

[Miscellaneous](#)

[Metrological Approval](#)





last modified:

5/22/2024 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[6ES71346JF002CA1](#)