



SIMATIC DP, Electronic module for ET 200 PRO 8 DI 24 V DC, Module diagnostics; incl. bus module, Connection module IO 6ES7194-4..00-0AA0 order separately

General information	
Product function	
• Isochronous mode	No
Supply voltage	
Rated value (DC)	24 V
Reverse polarity protection	Yes; Against destruction; encoder power supply outputs applied with reversed polarity
Input current	
from supply voltage 1L+, max.	20 mA
from backplane bus 3.3 V DC, max.	20 mA
Encoder supply	
Number of outputs	8
Short-circuit protection	Yes; per module, electronic
Output current	
• up to 55 °C, max.	1 A
Power loss	
Power loss, typ.	2.5 W
Address area	
Address space per module	
• Address space per module, max.	1 byte
Digital inputs	
Number of digital inputs	8
Input characteristic curve in accordance with IEC 61131, type 1	Yes
Input characteristic curve in accordance with IEC 61131, type 2	No
Number of simultaneously controllable inputs	
all mounting positions	
— up to 55 °C, max.	8
Input voltage	
• Rated value (DC)	24 V
• for signal "0"	-3 to +5V
• for signal "1"	13 to 30V
Input current	
• for signal "1", typ.	7 mA
Input delay (for rated value of input voltage)	
for standard inputs	
— parameterizable	No
— at "0" to "1", min.	1.2 ms
— at "0" to "1", max.	4.8 ms
— at "1" to "0", min.	1.2 ms
— at "1" to "0", max.	4.8 ms

Cable length	
• unshielded, max.	30 m
<b>Encoder</b>	
Connectable encoders	
• 2-wire sensor	Yes
— permissible quiescent current (2-wire sensor), max.	1.5 mA
<b>Interrupts/diagnostics/status information</b>	
Diagnostics function	Yes
<b>Alarms</b>	
• Diagnostic alarm	Yes
<b>Diagnoses</b>	
• Diagnostic information readable	Yes
• Short-circuit	Yes; Sensor supply to M; module by module
<b>Diagnostics indication LED</b>	
• Group error SF (red)	Yes
• Status indicator digital input (green)	Yes; Per channel
<b>Potential separation</b>	
between backplane bus and all other circuit components	Yes
<b>Potential separation digital inputs</b>	
• between the channels	No
• between the channels and backplane bus	Yes
<b>Isolation</b>	
Isolation tested with	707 V DC (type test)
<b>Dimensions</b>	
Width	45 mm
Height	130 mm
Depth	35 mm
<b>Weights</b>	
Weight, approx.	140 g

last modified: 8/27/2023 

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6ES71414BF000AA0](#)