



SCALANCE XC224 manageable Layer 2 IE switch; IEC 62443-4-2 certified; 24x 10/100 Mbit/s RJ45 ports; 1x console port, diagnostics LED; redundant power supply; temperature range -40 °C to +70 °C; assembly: DIN rail/S7 mounting rail/wall Office redundancy functions features (RSTP, VLAN,...); PROFINET IO device Ethernet/IP-compliant, C-plug slot;

product type designation	SCALANCE XC224
transfer rate	
transfer rate	10 Mbit/s, 100 Mbit/s
interfaces / for communication / maximum configuration for modular devices	
number of electrical ports / maximum	24
interfaces / for communication / integrated	
number of electrical connections	
• for network components or terminal equipment	24; RJ45
number of 10/100 Mbit/s RJ45 ports / integrated	
• with securing collar	24
interfaces / other	
number of electrical connections	
• for operator console	1
• for signaling contact	1
• for power supply	1
type of electrical connection	
• for operator console	RJ11
• for signaling contact	2-pole terminal block
• for power supply	4-pole terminal block
design of the removable storage	
• C-PLUG	Yes
signal inputs/outputs	
operating voltage / of the signaling contacts	
• at DC / rated value	24 V
operational current / of the signaling contacts	
• at DC / maximum	0.1 A
supply voltage, current consumption, power loss	
product component / connection for redundant voltage supply	Yes
type of voltage / 1 / of the supply voltage	DC
• supply voltage / 1 / rated value	24 V
• power loss [W] / 1 / rated value	9 W
• consumed current / 1 / at rated supply voltage / maximum	0.375 A
• supply voltage / 1 / rated value	9.6 ... 31.2 V
• consumed current / 1 / maximum	0.75 A
• type of electrical connection / 1 / for power supply	4-pole terminal block
• product component / 1 / fusing at power supply input	Yes
• fuse protection type / 1 / at input for supply voltage	2.5 A / 125 V
ambient conditions	
ambient temperature	
• during operation	-40 ... +70 °C

<ul style="list-style-type: none"> during storage during transport 	-40 ... +85 °C
relative humidity	-40 ... +85 °C
<ul style="list-style-type: none"> at 25 °C / without condensation / during operation / maximum 	95 %
protection class IP	IP20
design, dimensions and weights	
design	compact
width	120 mm
height	147 mm
depth	125 mm
net weight	0.88 kg
material / of the enclosure	Polycarbonate (PC-GF10) / pressure die cast aluminum
fastening method	
<ul style="list-style-type: none"> 35 mm top hat DIN rail mounting 	Yes
<ul style="list-style-type: none"> wall mounting 	Yes
<ul style="list-style-type: none"> S7-300 rail mounting 	Yes
<ul style="list-style-type: none"> S7-1500 rail mounting 	Yes
product features, product functions, product components / general	
cascading in the case of a redundant ring / at reconfiguration time of <1~0.31~s	50
cascading in cases of star topology	any (depending only on signal propagation time)
product function / QoS according to DSCP	Yes
product feature	
<ul style="list-style-type: none"> Cut Through switching method 	No
<ul style="list-style-type: none"> Store & Forward switching method 	Yes
product functions / management, configuration, engineering	
product function	
<ul style="list-style-type: none"> CLI 	Yes
<ul style="list-style-type: none"> web-based management 	Yes
<ul style="list-style-type: none"> MIB support 	Yes
<ul style="list-style-type: none"> TRAPs via email 	Yes
<ul style="list-style-type: none"> configuration with STEP 7 	Yes
<ul style="list-style-type: none"> RMON 	Yes
<ul style="list-style-type: none"> SMTP server 	No
<ul style="list-style-type: none"> port mirroring 	Yes
<ul style="list-style-type: none"> multiport mirroring 	Yes
<ul style="list-style-type: none"> CoS 	Yes
<ul style="list-style-type: none"> PROFINET IO diagnosis 	Yes
PROFINET conformity class	B
product function / switch-managed	Yes
telegram length / for Ethernet / maximum	1632 byte
protocol / is supported	
<ul style="list-style-type: none"> Telnet 	Yes
<ul style="list-style-type: none"> HTTP 	Yes
<ul style="list-style-type: none"> HTTPS 	Yes
<ul style="list-style-type: none"> TFTP 	Yes
<ul style="list-style-type: none"> BOOTP 	No
<ul style="list-style-type: none"> GMRP 	Yes
<ul style="list-style-type: none"> DCP 	Yes
<ul style="list-style-type: none"> LLDP 	Yes
<ul style="list-style-type: none"> EtherNet/IP 	Yes
<ul style="list-style-type: none"> SNMP v1 	Yes
<ul style="list-style-type: none"> SNMP v2 	Yes
<ul style="list-style-type: none"> SNMP v3 	Yes
<ul style="list-style-type: none"> IGMP (snooping/querier) 	Yes
identification & maintenance function	
<ul style="list-style-type: none"> I&M0 - device-specific information 	Yes
<ul style="list-style-type: none"> I&M1 - higher level designation/location designation 	Yes
product function	
<ul style="list-style-type: none"> is supported / identification link 	Yes

product functions / diagnostics

product function	
• port diagnostics	Yes
• statistics Packet Size	Yes
• statistics packet type	Yes
• error statistics	Yes
• SysLog	Yes

product functions / VLAN

product function	
• VLAN - port based	Yes
• VLAN - protocol-based	No
• VLAN - IP-based	No
• VLAN dynamic	Yes
number of VLANs / maximum	257
number of VLANs - dynamic / maximum	257
number of VLANs / at ring redundancy (HRP; MRP; standby link)	257
protocol / is supported / GVRP	Yes

product functions / DHCP

product function	
• DHCP server	Yes
• DHCP client	Yes
• DHCP Option 82	Yes
• DHCP Option 66	Yes
• DHCP Option 67	Yes

product functions / redundancy

product function	
• of the PROFINET IO device / is supported / PROFINET system redundancy	Yes
• ring redundancy	Yes
• High Speed Redundancy Protocol (HRP)	Yes
• high speed redundancy protocol (HRP) with redundancy manager	Yes
• high speed redundancy protocol (HRP) with standby redundancy	Yes
protocol / is supported / Media Redundancy Protocol (MRP)	Yes
product function	
• media redundancy protocol (MRP) with redundancy manager	Yes
• Media Redundancy Protocol Interconnection (MRP-I)	Yes
• of the PROFINET IO device / is supported / H-Sync forwarding	Yes
• redundancy procedure STP	Yes
• redundancy procedure RSTP	Yes
• redundancy procedure RSTP+	Yes
• redundancy procedure MSTP	Yes
• Parallel Redundancy Protocol (PRP)/operation in the PRP-network	Yes
• Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA)	No
• passive listening	Yes
protocol / is supported	
• LACP	Yes

product functions / security

product function	
• IEEE 802.1x (radius)	Yes
• broadcast/multicast/unicast limiter	Yes
• broadcast blocking	Yes
protocol / is supported	
• SSH	Yes
• SSL	Yes

product functions / time

product function	
------------------	--

<ul style="list-style-type: none"> • SICLOCK support • NTP-client • SNTP client 	Yes Yes Yes
protocol / is supported	
<ul style="list-style-type: none"> • NTP • SNTP 	Yes Yes
system modification during operation	
product function / configuration in RUN via CiR/H-CiR	Yes
standards, specifications, approvals	
IT security for industrial automation systems / according to IEC 62443-4-2:2019	Yes
MTBF	41 a
reference code	
<ul style="list-style-type: none"> • according to IEC 81346-2 • according to IEC 81346-2:2019 	KF KFE
standards, specifications, approvals / CE	
certificate of suitability / CE marking	Yes
product conformity / according to EMC-guideline	2014/30/EU
standard	
<ul style="list-style-type: none"> • for EMC interference emission • for immunity to EMC 	EN 61000-6-4, EN 50121-4 EN 61000-6-2, EN 50121-4
certificate of suitability / RoHS conformity	Yes; 2011/65/EU
standards, specifications, approvals / hazardous environments	
certificate of suitability	
<ul style="list-style-type: none"> • ATEX • for ATEX / as marking • for ATEX / as certificate • IECEx • for IECEx / as marking • for IECEx / as certificate • CCC / for hazardous zone according to GB standard • CCC / for hazardous zone according to GB standard / as marking • for cULus HazLoc / as marking • for cULus HazLoc / as File Nr. • FM registration • for FM / as marking • for FM / as certificate 	Yes; EN 60079-0, EN 60079-15 II 3 G Ex nA II T4 Gc KEMA 07ATEX0145 X Yes; IEC 60079-0, IEC 60079-15 Ex nA II T4 Gc IECEx DEK 14.0025X Yes Ex nA IIC T4 Gc CL1, DIV2, Group A,B,C,D T4, CL1, Zone 2, Group IIC, T4 E240480 (NWHP, NWHP7) Yes; FM class 3600:2011, FM class 3611:2004, FM class 3810:2005, ANSI/ISA-61010-1:2004 CL1, DIV2, group A,B,C,D T4, CL1, Zone 2, group IIC, T4 Ta: -40 °C +70 °C FM16US0205X
standards, specifications, approvals / other	
certificate of suitability	
<ul style="list-style-type: none"> • railway application in accordance with EN 50121-4 • Regulatory Compliance Mark (RCM) • for UL 61010-2-201 / as File Nr. • for UL 60950-1 / as File Nr. • EAC approval 	Yes Yes E85972 (NRAQ, NRAQ7) E115352 (NWGQ, NWGQ7) Yes
standards, specifications, approvals / marine classification	
Marine classification association	
<ul style="list-style-type: none"> • American Bureau of Shipping Europe Ltd. (ABS) • French marine classification society (BV) • DNV GL • Korean Register of Shipping (KRS) • Lloyds Register of Shipping (LRS) • Nippon Kaiji Kyokai (NK) • Polski Rejestr Statkow (PRS) • Royal Institution of Naval Architects (RINA) 	Yes Yes Yes Yes Yes Yes Yes Yes
accessories	
product extension / optional / C-PLUG	Yes
further information / internet links	
internet link	
<ul style="list-style-type: none"> • to web page: selection aid TIA Selection Tool 	http://www.siemens.com/tia-selection-tool

- to website: Industrial communication
- to website: Industry Mall
- to website: Information and Download Center
- to website: Image database
- to website: CAX-Download-Manager
- to website: Industry Online Support

<http://www.siemens.com/simatic-net>
<https://mall.industry.siemens.com>
<http://www.siemens.com/industry/infocenter>
<http://automation.siemens.com/bilddb>
<http://www.siemens.com/cax>
<https://support.industry.siemens.com>

security information

security information

Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action (e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit <http://www.siemens.com/industrialsecurity>. To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit <http://support.automation.siemens.com>. (V3.4)

last modified:

8/11/2023 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6GK52240BA002AC2](#)