


P.C. MOUNTING



CIRCUIT: 4PDT

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=± 0.4
X.XX=± 0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. RATING 0.1A @30V DC

▲ 5. MATERIALS:

CONTACT/TERMINALS: SILVER PLATE
 HOUSING: PBT UL94V0
 BASE: PA66 UL94V0
 ACTUATOR: PA66 UL94V0
 CAP: ABS UL94V0

6. CONTACT RESISTANCE: 100 MILLI-OHM (INITIAL)

▲ 7. TIMING: NON-SHORTING

8. OPERATING FORCE: 280± 50GF

9. TRAVEL: LATCHING

2MM TO LOCK



3MM OVERALL

10. ELECTRICAL LIFE: 10000 CYCLES



11. OPERATING TEMP: -20°C TO +70°C

12. 2002/95/EC (ROHS) COMPLIANT

13. ▲ DENOTES CRITICAL PARAMETER.



ISOMETRIC



G	15943	ADD ROHS NOTE	4/4/06	BK
F	15260	CHANGED CAP DESCRIPTION	9/8/05	PH
E	15060	CHANGED NOTE	7/5/05	JB
D	14969	CHANGED A NOTE	6/2/05	JB
C	14893	CHANGED NOTES AND DIMENSIONS	5/3/05	JB
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
 TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

E-SWITCH®

TITLE PBH4UEENAGV1RBLK-UL94V0

SCALE 2:1

DATE 02/03/05

DR AR

DWG XQ0001P

REV G

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

E-Switch:

[PBH4UEENAGV1RBLKUL94VO](#)