


product type designation

product description



PROFIBUS ECOFAST Hybrid Cable

ECOFAST Hybrid cable (data and energy wires), product sold by meter, unassembled

PROFIBUS ECOFAST Hybrid Cable, Trailable cable with 4x Cu (1.5 mm²) and 2xCU (0.64 mm) shielded, sold by the meter, delivery unit max. 1000 m minimum order quantity: 20 m.

suitability for use

Hybrid cable for connection of ECOFAST stations

cable designation

02Y (ST)C 1 x 2 x 0.65/2.56 - 150 LI LIH-Z 11Y 4 x 1 x 1.5 VI FRNC

electrical data

attenuation factor per length

- at 9.6 kHz / maximum
- at 38.4 kHz / maximum
- at 4 MHz / maximum
- at 16 MHz / maximum

0.004 dB/m
0.004 dB/m
0.025 dB/m
0.049 dB/m

impedance

- rated value
- at 9.6 kHz
- at 38.4 kHz
- at 3 MHz ... 20 MHz

150 Ω
270 Ω
185 Ω
150 Ω

relative symmetrical tolerance

- of the characteristic impedance at 9.6 kHz
- of the characteristic impedance at 38.4 kHz
- of the characteristic impedance at 3 MHz ... 20 MHz

10 %
10 %
10 %

loop resistance per length / maximum

138 Ω/km

shield resistance per length / maximum

15 Ω/km

insulation resistance coefficient

20 GΩ·m

operating voltage / maximum

80 V

capacity per length / at 1 kHz

30 pF/m

operating voltage / RMS value

100 V

conductor cross section / of the power line

1.5 mm²

continuous current / of the power lines

12 A

mechanical data

design of the shield

Overlapped aluminum-clad foil, sheathed in a braided screen of tin-plated copper wires

number of electrical cores

6

type of electrical connection / FastConnect

No

outer diameter

- of inner conductor
- of the wire insulation
- of cable sheath

0.67 mm
2.56 mm
11 mm

symmetrical tolerance of the outer diameter / of cable sheath

0.3 mm

material

- of the wire insulation
- of cable sheath

polyethylene (PE)
PUR

color	
<ul style="list-style-type: none"> • of the insulation of data wires • of the power line insulation • of cable sheath 	red / green Black Violet
bending radius	
<ul style="list-style-type: none"> • with multiple bends / minimum permissible 	82.5 mm
number of bending cycles	5000000; For use in cable carriers, for 5 million bending cycles with a bending radius of 82.5 mm (7.5x D) and an acceleration of 2.5 m/s ²
tensile load / maximum	300 N
weight per length	150 kg/km
ambient conditions	
ambient temperature	
<ul style="list-style-type: none"> • during operation • during storage • during transport • during installation • note 	-40 ... +60 °C -40 ... +60 °C -40 ... +60 °C -40 ... +60 °C Electrical properties measured at 20 Cel, verification according to DIN 47250 part 4 respectively DIN VDE 0472
fire behavior	flame-retardant according to IEC 60332-1
class of burning behaviour / according to EN 13501-6	Eca
chemical resistance	
<ul style="list-style-type: none"> • to mineral oil • to grease 	Conditional resistance Conditional resistance
radiological resistance / to UV radiation	resistant
product features, product functions, product components / general	
product feature	
<ul style="list-style-type: none"> • halogen-free • silicon-free 	Yes Yes
standards, specifications, approvals	
UL/ETL listing / 300 V Rating	No
UL/ETL style / 600 V Rating	No
certificate of suitability	
<ul style="list-style-type: none"> • EAC approval • RoHS conformity 	Yes Yes
further information / internet links	
internet link	
<ul style="list-style-type: none"> • to website: Selection guide for cables and connectors • to web page: selection aid TIA Selection Tool • to website: Industrial communication • to website: Image database • to website: CAX-Download-Manager • to website: Industry Online Support 	https://sie.ag/2QdlxcP http://www.siemens.com/tia-selection-tool http://www.siemens.com/simatic-net http://automation.siemens.com/bilddb http://www.siemens.com/cax https://support.industry.siemens.com
security information	
security information	<p>Siemens provides products and solutions with industrial cybersecurity functions that support the secure operation of plants, systems, machines and networks. In order to protect plants, systems, machines and networks against cyber threats, it is necessary to implement – and continuously maintain – a holistic, state-of-the-art industrial cybersecurity concept. Siemens' products and solutions constitute one element of such a concept. Customers are responsible for preventing unauthorized access to their plants, systems, machines and networks. Such systems, machines and components should only be connected to an enterprise network or the internet if and to the extent such a connection is necessary and only when appropriate security measures (e.g. firewalls and/or network segmentation) are in place. For additional information on industrial cybersecurity measures that may be implemented, please visit www.siemens.com/cybersecurity-industry. Siemens' products and solutions undergo continuous development to make them more secure. Siemens strongly recommends that product updates are applied as soon as they are available and that the latest product versions are used. Use of product versions that are no longer supported, and failure to apply the latest updates may increase customer's exposure to cyber threats. To stay informed about product updates, subscribe to the Siemens Industrial Cybersecurity RSS Feed under https://www.siemens.com/cert. (V4.7)</p>
Approvals / Certificates	
General Product Approval	Marine / Shipping

[Manufacturer Declaration](#)



[Declaration of Conformity](#)



other	Environment
-------	-------------

[Manufacturer Declaration](#)

[Confirmation](#)

[Confirmation](#)

last modified:

4/4/2024 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[6XV18307AH10](#)