




PARAMETERS	SYMBOL	MAX.	UNITS
LAMP VOLTAGE (AC)	V	125	V
STARTUP VOLTAGE	V _s	95	V
CURRENT	I	0.8	mA
SERIES RESISTANCE	R	120	OHMS



PANEL THICKNESS	X dimension
0.75-1.25 [0.30-.049]	19.2-0.1 [7.56]
1.25-2.0 [0.49-.079]	19.4-0.1 [7.64]
2.0-3.0 [0.79-.118]	19.8-0.1 [7.80]



PANEL CUTOOUT
NOT TO SCALE

NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25

$$X.XX=\pm 0.25$$

- ### 3. RATING:

6A @250VAC;9A @125VAC (UL, CSA, VDE)



4(1)A @250VAC

4. LAMP VOLTAGE: 125V (NEON BULB)

CONTACT SURFACE: Coin Silver, Silver Plate

TERMINAL: Copper Alloy W/ Silver Plate.

6. CONTACT RESISTANCE: 20 MILLIOHMS TYP. INITIAL
7. INSULATION RESISTANCE: 1000MEGOHMS
8. DIELECTRIC STRENGTH: >1500V RMS MIN. @SEA LEVEL
>3000V RMS @SEA LEVEL
9. MECHANICAL LIFE: 50,000 CYCLES.
10. ELECTRICAL LIFE: 10,000 CYCLES.

**E-SWITCH®**

					TITLE		
					R1973B BLK YEL EF1		
A	13000	RELEASED FOR PRODUCTION	4/4/03	AR			
REV.	ECN No.	DESCRIPTION	DATE	CHKD			
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED					SCALE	DATE	
					1.5:1	4/4/03	
					DR	DWG	
					AR	M400040	
					REV	A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[R1973BBLKYELEF1](#)