




SWITCH FUNCTION	
POS. 1	POS. 2
ON	ON
2-1	2-3



NOTE:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERMINAL NUMBERS FOR REF ONLY
- ▲ 4. CONTACT MATERIAL: SILVER
5. RATING: 3A @120VAC or 28VDC, 1A @250VAC
6. MECHANICAL LIFE: 6,000 MAKE-AND-BREAK CYCLES
7. CONTACT RESISTANCE: 50 m Ω MAX. INITIAL @ 2-4VDC
8. INSULATION RESISTANCE: 1,000 MEGA-OHM MIN @ 1000VDC
9. ELECTRIC STRENGTH: 1,000 V RMS @SEA LEVEL
10. OPERATING TEMP.: -30°C to 85°C
11. OPERATING FORCE: 350 $\pm$ 100gf
12. TRAVEL: Electrical Make: 1.34 $\pm$ 0.25mm / Full travel: 1.88 $\pm$ 0.30mm
13. ▲ DENOTES CRITICAL PARAMETER



C	24159	update Travel note	1/23/20	MW				
B	22430	add 1A @250VAC, remove thread callout	8/9/16	MW				
A	22046	New-Release	11/10/15	rc	TITLE 800CSP1B6M2QE			
REV	PCR NO	DESCRIPTION	DATE	BY	SCALE	DATE	DR	REV
					2:1	11/10/2015	rc	C

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

SCALE

2:1

DATE

11/10/2015

DR

rc

DWG

T835001

REV

C

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[E-Switch:](#)

[800CSP1B6M2QE](#)