



SIMATIC ET 200eco PN, DI 16x 24 V DC, M12-L, 8x M12, double assignment, input type 3 (IEC 61131), sink input (PNP, sinking input), input delay 0.05..20 ms, channel diagnostics for: wire break at input, encoder power supply short-circuit, 0.25 ms isochronous mode, prioritized startup, MSI, MRP, S2 redundancy, I&M0...3, multi-fieldbus, PN IO, Ethernet IP, Modbus TCP, degree of protection IP67 / IP69K

General information	
HW functional status	FS01
Firmware version	V5.1.x
• FW update possible	Yes
Vendor identification (VendorID)	002AH
Device identifier (DeviceID)	0306H
Manufacturer ID according to ODVA (VendorID)	04E3H
Device ID according to ODVA (Product code)	0FA5H
Product function	
• I&M data	Yes; I&M0 to I&M3
• Isochronous mode	Yes
• Prioritized startup	Yes
Engineering with	
• STEP 7 TIA Portal configurable/integrated from version	STEP 7 V17 or higher with HSP 0363
• PROFINET from GSD version/GSD revision	GSDML V2.3.x
• Multi Fieldbus Configuration Tool (MFCT)	from V1.3 SP1
Operating mode	
• DI	Yes
• Counter	No
• MSI	Yes
Supply voltage	
power supply according to NEC Class 2 required	No
Load voltage 1L+	
• Rated value (DC)	24 V
• permissible range, lower limit (DC)	20.4 V
• permissible range, upper limit (DC)	28.8 V
• Reverse polarity protection	Yes; Against destruction; encoder power supply outputs applied with reversed polarity
Input current	
Current consumption (rated value)	90 mA; without load
from load voltage 1L+ (unswitched voltage)	12 A; Maximum value
from load voltage 2L+, max.	12 A; Maximum value
Encoder supply	
Number of outputs	8
24 V encoder supply	
• Short-circuit protection	Yes; Group-by-group for 2 channels, electronic
• Output current, max.	100 mA; per output
Power loss	
Power loss, typ.	8.1 W
Address area	

Address space per module	
• Inputs	2 byte; + 2 bytes for QI information
<b>Hardware configuration</b>	
Submodules	
• Number of configurable submodules, max.	2
<b>Digital inputs</b>	
Number of digital inputs	16
Digital inputs, parameterizable	Yes
Source/sink input	P-reading
Input characteristic curve in accordance with IEC 61131, type 3	Yes
Number of simultaneously controllable inputs	
all mounting positions	
— up to 60 °C, max.	16
Input voltage	
• Rated value (DC)	24 V
• for signal "0"	-30 to +5 V
• for signal "1"	+11 to +30V
Input current	
• for signal "1", typ.	2.4 mA
Input delay (for rated value of input voltage)	
for standard inputs	
— parameterizable	Yes; 0.05 / 0.1 / 0.4 / 0.8 / 1.6 / 3.2 / 12.8 / 20 ms
Cable length	
• unshielded, max.	30 m
<b>Encoder</b>	
Connectable encoders	
• 2-wire sensor	Yes
— permissible quiescent current (2-wire sensor), max.	1.5 mA
<b>Interfaces</b>	
Number of PROFINET interfaces	1
<b>1. Interface</b>	
Interface type	PROFINET with 100 Mbit/s full duplex (100BASE-TX)
Interface types	
• M12 port	Yes; 2x M12, 4-pin, D-coded
• Number of ports	2
• integrated switch	Yes
Protocols	
• PROFINET IO Device	Yes
• Open IE communication	Yes
<b>Interface types</b>	
M12 port	
• Autonegotiation	Yes
• Autocrossing	Yes
• Transmission rate, max.	100 Mbit/s
<b>Protocols</b>	
Supports protocol for PROFINET IO	Yes
PROFIsafe	No
EtherNet/IP	Yes
Modbus TCP	Yes
PROFINET IO Device	
Services	
— IRT	Yes; 250 µs to 4 ms in 125 µs frame
— Prioritized startup	Yes
Redundancy mode	
• PROFINET system redundancy (S2)	Yes
— on S7-1500R/H	Yes
— on S7-400H	Yes
• PROFINET system redundancy (R1)	No
• H-Sync forwarding	Yes
Media redundancy	

— MRP	Yes
<b>EtherNet/IP</b>	
<b>Services</b>	
— CIP Implicit Messaging	Yes
— CIP Explicit Messaging	Yes
— CIP Safety	No
— Shared device	Yes; 2x EtherNet/IP Scanner
— Number of scanners with shared device, max.	2
<b>Updating times</b>	
— Requested Packet Interval (RPI)	2 ms
<b>Redundancy mode</b>	
— DLR (Device Level Ring)	No
<b>Address area</b>	
— Address space per module, max.	20 byte
— LargeForwardOpen (Class3)	No
<b>Modbus TCP</b>	
<b>Services</b>	
— read coils (code=1)	Yes
— read discrete inputs (code=2)	Yes
— Read Holding Registers (Code=3)	Yes
— write single coil (code=5)	Yes
— write multiple coils (code=15)	Yes
— Write Multiple Registers (Code=16)	Yes
— Parameter change by master	No
— Modbus TCP Security Protocol	No
<b>Address space per station</b>	
— Address space per station, max.	20 byte
— Access-consistent address space	2 byte
<b>Updating time</b>	
— I/O request interval	2 ms
<b>Connections</b>	
— Number of connections per slave	12
<b>Open IE communication</b>	
• TCP/IP	Yes; (only EtherNet/IP or Modbus TCP)
• SNMP	Yes
• LLDP	Yes
• ARP	Yes
<b>Isochronous mode</b>	
Equidistance	Yes
shortest clock pulse	250 µs
max. cycle	4 ms
Jitter, max.	10 µs
<b>Interrupts/diagnostics/status information</b>	
<b>Alarms</b>	
• Diagnostic alarm	Yes; Parameterizable
• Maintenance interrupt	Yes; Parameterizable
• Hardware interrupt	Yes; Parameterizable
<b>Diagnoses</b>	
• Diagnostic information readable	Yes
• Monitoring the supply voltage	Yes
— parameterizable	Yes
• Wire-break	Yes; DI, input current < 0.3 mA, per channel
• Short-circuit encoder supply	Yes; Per channel group
<b>Diagnostics indication LED</b>	
• RUN LED	Yes; green LED
• ERROR LED	Yes; red LED
• MAINT LED	Yes; Yellow LED
• NS LED	Yes; green/red LED
• MS LED	Yes; green/red LED
• IO LED	Yes; red-green-yellow LED
• Channel status display	Yes; green LED

<ul style="list-style-type: none"> <li>• for channel diagnostics</li> </ul>	Yes; red LED
<ul style="list-style-type: none"> <li>• Connection display LINK TX/RX</li> </ul>	Yes; green LED, only link
<b>Potential separation</b>	
between the load voltages	Yes
between Ethernet and electronics	Yes
<b>Potential separation channels</b>	
<ul style="list-style-type: none"> <li>• between the channels</li> </ul>	No
<ul style="list-style-type: none"> <li>• between the channels and the power supply of the electronics</li> </ul>	No
<b>Isolation</b>	
<b>tested with</b>	
<ul style="list-style-type: none"> <li>• 24 V DC circuits</li> </ul>	707 V DC (type test)
<ul style="list-style-type: none"> <li>• Test voltage for interface, rms value [Vrms]</li> </ul>	1 500 V; According to IEEE 802.3
<b>Degree and class of protection</b>	
IP degree of protection	IP65/67/69K
<b>Standards, approvals, certificates</b>	
Suitable for safety-related tripping of standard modules	Yes; From FS01
<b>Highest safety class achievable for safety-related tripping of standard modules</b>	
<ul style="list-style-type: none"> <li>• Performance level according to ISO 13849-1</li> </ul>	PL d
<ul style="list-style-type: none"> <li>• Category according to ISO 13849-1</li> </ul>	Cat. 3
<ul style="list-style-type: none"> <li>• SIL acc. to IEC 62061</li> </ul>	SIL 2
<ul style="list-style-type: none"> <li>• remark on safety-oriented shutdown</li> </ul>	<a href="https://support.industry.siemens.com/cs/de/en/view/39198632">https://support.industry.siemens.com/cs/de/en/view/39198632</a>
<b>Ambient conditions</b>	
<b>Ambient temperature during operation</b>	
<ul style="list-style-type: none"> <li>• min.</li> </ul>	-40 °C
<ul style="list-style-type: none"> <li>• max.</li> </ul>	60 °C
<b>Altitude during operation relating to sea level</b>	
<ul style="list-style-type: none"> <li>• Ambient air temperature-barometric pressure-altitude</li> </ul>	Up to max. 5 000 m, at installation height > 2 000 m additional restrictions
<b>connection method</b>	
Design of electrical connection	4/5-pin M12 circular connectors
Design of electrical connection for the inputs and outputs	M12, 5-pin, A-coded
Design of electrical connection for supply voltage	M12, 4-pin, L-coded
<b>Dimensions</b>	
Width	45 mm
Height	200 mm
Depth	48 mm
<b>Weights</b>	
Weight, approx.	780 g

**last modified:** 8/16/2023 

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6ES71416BH000BB0](#)