







SIMATIC ET 200SP, BaseUnit BU15-P16+A0+2B, BU type A0, Pack quantity: 10 units, Push-in terminals, without AUX terminals, bridged to the left, WxH: 15x 117 mm

General information	
Product type designation	BU type A0
HW functional status	From FS06
Supply voltage	
Rated value (DC)	24 V
external protection for power supply lines	Yes; 24 V DC/10 A miniature circuit breaker with type B or C tripping characteristic
Mains filter	
• integrated	No
Current carrying capacity	
For P1 and P2 bus, max.	10 A
For process terminals, max.	2 A
Hardware configuration	
Formation of potential groups	
• New potential group	No
• Potential group continued from the left	Yes
Slots	
• Number of slots	1; Type A0
Isolation	
Isolation tested with	707 V DC (type test)
Standards, approvals, certificates	
Ecological footprint	
• environmental product declaration	Yes
Global warming potential	
— global warming potential, (total) [CO2 eq]	0.873 kg
— global warming potential, (during production) [CO2 eq]	0.866 kg
— global warming potential, (during operation) [CO2 eq]	0 kg
— global warming potential, (after end of life cycle) [CO2 eq]	-0.0011 kg
Ambient conditions	
Ambient temperature during operation	
• horizontal installation, min.	-30 °C
• horizontal installation, max.	60 °C
• vertical installation, min.	-30 °C
• vertical installation, max.	50 °C
Altitude during operation relating to sea level	
• Installation altitude above sea level, max.	5 000 m; Restrictions for installation altitudes > 2 000 m, see manual
Accessories	
Color coding labels	

<ul style="list-style-type: none">• for process terminals• for AUX terminals• for add-on terminals	CC00 to CC09 does not exist does not exist		
connection method			
Terminals			
<ul style="list-style-type: none">• Terminal type• system-integrated shield connection• Conductor cross-section, min.• Conductor cross-section, max.• Number of process terminals to I/O module• Number of terminals to AUX bus• Number of add-on terminals• Number of terminals with connection to P1 and P2 bus	Push-in terminal Yes; Optional 0.14 mm²; AWG 26 2.5 mm²; AWG 14 16; Pro slot 0 0 2; Pro slot		
Dimensions			
Width	15 mm		
Height	117 mm		
Depth	35 mm		
Weights			
Weight, approx.	40 g		
Classifications			
		Version	Classification
	eClass	14	27-24-26-03
	eClass	12	27-24-26-03
	eClass	9.1	27-24-26-03
	eClass	9	27-24-26-03
	eClass	8	27-24-26-03
	eClass	7.1	27-24-26-03
	eClass	6	27-24-26-03
	ETIM	9	EC001598
	ETIM	8	EC001598
	ETIM	7	EC001598
	IDEA	4	3560
	UNSPSC	15	32-15-17-04
Approvals / Certificates			
General Product Approval		Marine / Shipping	Environment
			

last modified: 10/9/2024 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[6ES71936BP002BA0](#)