

Control Power Transformer, 1000va, PRI 240x480 230x460 220 440v, SEC 120/115/110v, Domestic,



|                                                                 |                                  |
|-----------------------------------------------------------------|----------------------------------|
| product brand name                                              | Control Power Transformer        |
| design of the product                                           | Control power voltage            |
| special product feature                                         | Robust design                    |
| <b>General technical data</b>                                   |                                  |
| weight [lb]                                                     | 30 lb                            |
| Height x Width x Depth [in]                                     | 6.62 × 7 × 6.42 in               |
| ambient temperature [°F] during operation                       | -4 ... +104 °F                   |
| ambient temperature during operation                            | -20 ... +40 °C                   |
| country of origin                                               | Mexico                           |
| operating apparent power rated value                            | 1000 VA                          |
| <b>Enclosure</b>                                                |                                  |
| design of the housing                                           | Open                             |
| <b>Mounting/wiring</b>                                          |                                  |
| mounting position                                               | Any                              |
| fastening method                                                | Surface mounting                 |
| type of electrical connection at input for main current circuit | Screw-type terminals (touchsafe) |
| <b>Inputs/ Outputs</b>                                          |                                  |
| input variables of primary voltage                              | 240x480,230x460,220x440vac       |
| output dimensions of secondary voltage                          | 120/115/110vac                   |
| design of fuse holder of the secondary section                  | touch-safe cover required        |
| phase number of the inputs                                      | 1                                |
| electrical input frequency                                      | 50 ... 60 Hz                     |
| input voltage _1                                                | 240 V                            |
| input voltage _2                                                | 480 V                            |
| input voltage _3                                                | 230 V                            |
| input voltage _4                                                | 460 V                            |
| input voltage _5                                                | 220 V                            |
| input voltage _6                                                | 440 V                            |
| phase number of the outputs                                     | 1                                |
| electrical output frequency                                     | 60 ... 50 Hz                     |
| output voltage _1 rated value                                   | 120 V                            |
| output voltage _3 rated value                                   | 110 V                            |
| output voltage _2 rated value                                   | 115 V                            |
| certificate of suitability                                      | UL / CSA                         |

### Further information

Industrial Controls - Product Overview (Catalogs, Brochures,...)

[www.usa.siemens.com/iccatalog](http://www.usa.siemens.com/iccatalog)

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=US2:MT1000A>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/US/en/ps/US2:MT1000A>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

---

last modified: 1/25/2022 

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[MT1000A](#)