



FUSELESS MOTOR STARTER REVERSING OPERATION 600V AC SZ S00 4.5-6.3A 220/240V AC 50/60HZ SCREW CONNECTION FOR SCREW MOUNTING OR 35 MM RAIL-MOUNTING TYPE OF COORDINATION 1 1NC (PER CONTACTOR)

|                                                                                     |                               |
|-------------------------------------------------------------------------------------|-------------------------------|
| product brand name                                                                  | SIRIUS                        |
| product designation                                                                 | non-fused motor starter 3RA2  |
| design of the product                                                               | reversing starter             |
| manufacturer's article number                                                       |                               |
| • of the supplied contactor                                                         | <a href="#">3RT2015-1AP62</a> |
| • of the supplied circuit-breakers                                                  | <a href="#">3RV2011-1GA10</a> |
| • of the supplied link module                                                       | <a href="#">3RA1921-1DA00</a> |
| <b>General technical data</b>                                                       |                               |
| size of the circuit-breaker                                                         | S00                           |
| size of load feeder                                                                 | S00                           |
| product extension auxiliary switch                                                  | Yes                           |
| insulation voltage with degree of pollution 3 at AC rated value                     | 690 V                         |
| degree of pollution                                                                 | 3                             |
| surge voltage resistance rated value                                                | 6 kV                          |
| shock resistance according to IEC 60068-2-27                                        | 6g / 11 ms                    |
| mechanical service life (operating cycles) of contactor typical                     | 30 000 000                    |
| type of assignment                                                                  | 1                             |
| Substance Prohibitance (Date)                                                       | 03/01/2017                    |
| Weight                                                                              | 0.82 kg                       |
| <b>Ambient conditions</b>                                                           |                               |
| ambient temperature                                                                 |                               |
| • during operation                                                                  | -20 ... +60 °C                |
| • during storage                                                                    | -50 ... +80 °C                |
| • during transport                                                                  | -55 ... +80 °C                |
| <b>Main circuit</b>                                                                 |                               |
| number of poles for main current circuit                                            | 3                             |
| design of the switching contact                                                     | electromechanical             |
| adjustable current response value current of the current-dependent overload release | 4.5 ... 6.3 A                 |
| operating voltage                                                                   |                               |
| • rated value                                                                       | 690 V                         |
| • at AC-3 rated value maximum                                                       | 690 V                         |
| operating frequency rated value                                                     | 50 ... 60 Hz                  |
| operational current at AC-3 at 400 V rated value                                    | 4.9 A                         |
| operating power at AC-3                                                             |                               |
| • at 400 V rated value                                                              | 2 200 W                       |
| • at 500 V rated value                                                              | 3 000 W                       |
| <b>Control circuit/ Control</b>                                                     |                               |
| control supply voltage at AC                                                        |                               |
| • at 50 Hz rated value                                                              | 220 V                         |

|                                                                                                                                                                                                                                                                                                                                                                                                                       |                                                                                      |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------|
| <ul style="list-style-type: none"> <li>• at 50 Hz rated value</li> <li>• at 60 Hz rated value</li> <li>• at 60 Hz rated value</li> </ul>                                                                                                                                                                                                                                                                              | 187 ... 242 V<br>240 V<br>192 ... 264 V                                              |
| <b>apparent holding power of magnet coil at AC</b>                                                                                                                                                                                                                                                                                                                                                                    | 4.8 VA                                                                               |
| <b>inductive power factor with the holding power of the coil</b>                                                                                                                                                                                                                                                                                                                                                      | 0.25                                                                                 |
| <b>Auxiliary circuit</b>                                                                                                                                                                                                                                                                                                                                                                                              |                                                                                      |
| <b>number of NC contacts for auxiliary contacts</b>                                                                                                                                                                                                                                                                                                                                                                   | 1                                                                                    |
| <b>Protective and monitoring functions</b>                                                                                                                                                                                                                                                                                                                                                                            |                                                                                      |
| <b>trip class</b>                                                                                                                                                                                                                                                                                                                                                                                                     | CLASS 10                                                                             |
| <b>design of the overload release</b>                                                                                                                                                                                                                                                                                                                                                                                 | thermal (bimetallic)                                                                 |
| response value current of instantaneous short-circuit trip unit                                                                                                                                                                                                                                                                                                                                                       | 81.9 A                                                                               |
| <b>UL/CSA ratings</b>                                                                                                                                                                                                                                                                                                                                                                                                 |                                                                                      |
| <b>full-load current (FLA) for 3-phase AC motor</b>                                                                                                                                                                                                                                                                                                                                                                   |                                                                                      |
| <ul style="list-style-type: none"> <li>• at 480 V rated value</li> <li>• at 600 V rated value</li> </ul>                                                                                                                                                                                                                                                                                                              | 4.8 A<br>6.1 A                                                                       |
| <b>yielded mechanical performance [hp]</b>                                                                                                                                                                                                                                                                                                                                                                            |                                                                                      |
| <ul style="list-style-type: none"> <li>• for single-phase AC motor <ul style="list-style-type: none"> <li>— at 110/120 V rated value</li> <li>— at 230 V rated value</li> </ul> </li> <li>• for 3-phase AC motor <ul style="list-style-type: none"> <li>— at 200/208 V rated value</li> <li>— at 220/230 V rated value</li> <li>— at 460/480 V rated value</li> <li>— at 575/600 V rated value</li> </ul> </li> </ul> | 0.25 hp<br>0.5 hp<br><br>1 hp<br>1.5 hp<br>3 hp<br>5 hp                              |
| <b>Short-circuit protection</b>                                                                                                                                                                                                                                                                                                                                                                                       |                                                                                      |
| <b>product function short circuit protection</b>                                                                                                                                                                                                                                                                                                                                                                      | Yes                                                                                  |
| <b>design of the short-circuit trip</b>                                                                                                                                                                                                                                                                                                                                                                               | magnetic                                                                             |
| <b>conditional short-circuit current (I<sub>q</sub>)</b>                                                                                                                                                                                                                                                                                                                                                              |                                                                                      |
| <ul style="list-style-type: none"> <li>• at 400 V according to IEC 60947-4-1 rated value</li> </ul>                                                                                                                                                                                                                                                                                                                   | 153 000 A                                                                            |
| <b>Installation/ mounting/ dimensions</b>                                                                                                                                                                                                                                                                                                                                                                             |                                                                                      |
| <b>mounting position</b>                                                                                                                                                                                                                                                                                                                                                                                              | vertical                                                                             |
| <b>fastening method</b>                                                                                                                                                                                                                                                                                                                                                                                               | Snap-mounted to DIN rail or screw-mounted with additional push-in lug                |
| <b>height</b>                                                                                                                                                                                                                                                                                                                                                                                                         | 170 mm                                                                               |
| <b>width</b>                                                                                                                                                                                                                                                                                                                                                                                                          | 90 mm                                                                                |
| <b>depth</b>                                                                                                                                                                                                                                                                                                                                                                                                          | 97.1 mm                                                                              |
| <b>required spacing</b>                                                                                                                                                                                                                                                                                                                                                                                               |                                                                                      |
| <ul style="list-style-type: none"> <li>• for grounded parts <ul style="list-style-type: none"> <li>— forwards</li> <li>— backwards</li> <li>— upwards</li> <li>— at the side</li> <li>— downwards</li> </ul> </li> <li>• for live parts <ul style="list-style-type: none"> <li>— forwards</li> <li>— backwards</li> <li>— upwards</li> <li>— downwards</li> <li>— at the side</li> </ul> </li> </ul>                  | 0 mm<br>0 mm<br>20 mm<br>9 mm<br>10 mm<br><br>0 mm<br>0 mm<br>20 mm<br>10 mm<br>9 mm |
| <b>Connections/ Terminals</b>                                                                                                                                                                                                                                                                                                                                                                                         |                                                                                      |
| type of electrical connection for main current circuit                                                                                                                                                                                                                                                                                                                                                                | screw-type terminals                                                                 |
| type of connectable conductor cross-sections for main contacts stranded                                                                                                                                                                                                                                                                                                                                               | 0.5 ... 4 mm <sup>2</sup> , 2x (0.75 ... 2.5 mm <sup>2</sup> )                       |
| connectable conductor cross-section for main contacts finely stranded with core end processing                                                                                                                                                                                                                                                                                                                        | 0.5 ... 2.5 mm <sup>2</sup>                                                          |
| <b>Safety related data</b>                                                                                                                                                                                                                                                                                                                                                                                            |                                                                                      |
| proportion of dangerous failures with high demand rate according to SN 31920                                                                                                                                                                                                                                                                                                                                          | 73 %                                                                                 |
| <b>B10 value with high demand rate according to SN 31920</b>                                                                                                                                                                                                                                                                                                                                                          | 1 000 000                                                                            |
| <b>Electrical Safety</b>                                                                                                                                                                                                                                                                                                                                                                                              |                                                                                      |
| <b>protection class IP on the front according to IEC 60529</b>                                                                                                                                                                                                                                                                                                                                                        | IP20                                                                                 |
| <b>touch protection on the front according to IEC 60529</b>                                                                                                                                                                                                                                                                                                                                                           | finger-safe, for vertical contact from the front                                     |

## Approvals Certificates

### General Product Approval



[KC](#)



### EMV

### Test Certificates

### Marine / Shipping



[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)



### Marine / Shipping

### other

### Railway



[Miscellaneous](#)

[Confirmation](#)

[Special Test Certificate](#)

### Dangerous goods

### Environment

[Transport Information](#)



[Environmental Confirmations](#)

## Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RA2210-1GA15-2AP6>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RA2210-1GA15-2AP6>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RA2210-1GA15-2AP6>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)


[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3RA2210-1GA15-2AP6&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RA2210-1GA15-2AP6&lang=en)


Characteristic: Tripping characteristics, I<sup>2</sup>t, Let-through current

<https://support.industry.siemens.com/cs/ww/en/ps/3RA2210-1GA15-2AP6/char>

Further characteristics (e.g. electrical endurance, switching frequency)

<http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RA2210-1GA15-2AP6&objecttype=14&gridview=view1>







last modified:

3/3/2023 

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[3RA22101GA152AP6](#)