

Combination Starter Non Reversing Fast Bus FLA Range 49-59A 3 Pole 240VAC
Coil S2 Open Type 1NO (>&<) 1NC Aux

| | |
|--|-------------------------------|
| product brand name | SIRIUS |
| product designation | non-fused motor starter 3RA2 |
| design of the product | direct starter |
| manufacturer's article number | |
| • of the supplied contactor | 3RT2037-1AP60 |
| • of the supplied circuit-breakers | 3RV2032-4XA15 |
| • of the supplied busbar adapter | 8US1261-6MT10 |
| • of the supplied link module | 3RA2931-1AA00 |
| General technical data | |
| size of the circuit-breaker | S2 |
| size of load feeder | S2 |
| product extension auxiliary switch | Yes |
| insulation voltage with degree of pollution 3 at AC rated value | 690 V |
| degree of pollution | 3 |
| surge voltage resistance rated value | 6 kV |
| shock resistance according to IEC 60068-2-27 | 6g / 11 ms |
| mechanical service life (operating cycles) of contactor typical | 10 000 000 |
| type of assignment | 2 |
| Weight | 2.87 kg |
| Ambient conditions | |
| ambient temperature | |
| • during operation | -20 ... +60 °C |
| • during storage | -50 ... +80 °C |
| • during transport | -55 ... +80 °C |
| Main circuit | |
| number of poles for main current circuit | 3 |
| design of the switching contact | electromechanical |
| adjustable current response value current of the current-dependent overload release | 49 ... 59 A |
| operating voltage | |
| • rated value | 690 V |
| • at AC-3 rated value maximum | 690 V |
| operating frequency rated value | 50 ... 60 Hz |
| operational current at AC-3 at 400 V rated value | 55 A |
| operating power at AC-3 | |
| • at 400 V rated value | 30 000 W |
| Control circuit/ Control | |
| control supply voltage at AC | |
| • at 50 Hz rated value | 220 V |
| • at 50 Hz rated value | 176 ... 242 V |
| • at 60 Hz rated value | 240 V |
| • at 60 Hz rated value | 192 ... 264 V |
| apparent holding power of magnet coil at AC | 16 VA |
| inductive power factor with the holding power of the coil | 0.37 |
| Auxiliary circuit | |
| number of NC contacts for auxiliary contacts | 2 |
| number of NO contacts for auxiliary contacts | 2 |
| Protective and monitoring functions | |
| trip class | CLASS 10 |
| design of the overload release | thermal (bimetallic) |
| response value current of instantaneous short-circuit trip unit | 767 A |

| UL/CSA ratings | | |
|--|-----------|--|
| full-load current (FLA) for 3-phase AC motor | | |
| • at 600 V rated value | 52 A | |
| yielded mechanical performance [hp] | | |
| • for single-phase AC motor | | |
| — at 110/120 V rated value | 5 hp | |
| — at 230 V rated value | 10 hp | |
| • for 3-phase AC motor | | |
| — at 220/230 V rated value | 20 hp | |
| — at 575/600 V rated value | 50 hp | |
| Short-circuit protection | | |
| product function short circuit protection | | Yes |
| design of the short-circuit trip | | magnetic |
| conditional short-circuit current (Iq) | | |
| • at 400 V according to IEC 60947-4-1 rated value | 150 000 A | |
| Installation/ mounting/ dimensions | | |
| mounting position | | vertical |
| fastening method | | for snapping onto 60 mm busbar systems |
| height | | 350 mm |
| width | | 55 mm |
| depth | | 208 mm |
| required spacing | | |
| • for grounded parts | | |
| — forwards | 0 mm | |
| — backwards | 6 mm | |
| — upwards | 50 mm | |
| — at the side | 10 mm | |
| — downwards | 10 mm | |
| • for live parts | | |
| — forwards | 0 mm | |
| — backwards | 6 mm | |
| — upwards | 50 mm | |
| — downwards | 10 mm | |
| — at the side | 10 mm | |
| Connections/ Terminals | | |
| type of electrical connection for main current circuit | | screw-type terminals |
| type of connectable conductor cross-sections for main contacts stranded | | 1 ... 50 mm², 2x (1 ... 25 mm²) |
| connectable conductor cross-section for main contacts finely stranded with core end processing | | 1 ... 35 mm² |
| Safety related data | | |
| proportion of dangerous failures with high demand rate according to SN 31920 | | 73 % |
| B10 value with high demand rate according to SN 31920 | | 1 000 000 |
| Electrical Safety | | |
| protection class IP on the front according to IEC 60529 | | IP20 |
| touch protection on the front according to IEC 60529 | | finger-safe, for vertical contact from the front |
| Approvals Certificates | | |
| General Product Approval | | For use in hazardous locations |
| | | Test Certificates |



[Special Test Certificate](#)

Marine / Shipping



| Marine / Shipping | other | Railway | Dangerous goods | Environment |
|-------------------|-------|---------|-----------------|-------------|
|-------------------|-------|---------|-----------------|-------------|



[Confirmation](#)

[Special Test Certificate](#)

[Transport Information](#)

[Environmental Confirmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RA2155-4XD37-0AP6>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RA2155-4XD37-0AP6>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RA2155-4XD37-0AP6>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RA2155-4XD37-0AP6&lang=en

Characteristic: Tripping characteristics, I²t, Let-through current

<https://support.industry.siemens.com/cs/ww/en/ps/3RA2155-4XD37-0AP6/char>

Further characteristics (e.g. electrical endurance, switching frequency)

<http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3RA2155-4XD37-0AP6&objecttype=14&gridview=view1>

last modified:

12/15/2020

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[3RA21554XD370AP6](#)