

STARTER, 3RE41223AA311GB0, WITH MODS



product brand name	Siemens
product designation	Non-reversing motor starter
special product feature	Start-Stop Push Buttons
General technical data	
weight [lb]	8 lb(av)
Height x Width x Depth [in]	11 × 7 × 5 in
touch protection against electrical shock	NA for enclosed products
installation altitude [ft] at height above sea level maximum	6 560 ft
country of origin	Germany
Power and control electronics	
number of poles for main current circuit	3
type of voltage of the control supply voltage	AC
control supply voltage	
• at AC at 50 Hz rated value	110 V
• at AC at 60 Hz rated value	120 V
disconnecter functionality	No
yielded mechanical performance [hp] for 3-phase AC motor	
• at 200/208 V rated value	2 hp
• at 220/230 V rated value	3 hp
• at 460/480 V rated value	5 hp
• at 575/600 V rated value	7.5 hp
Contactor	
number of NO contacts for main contacts	3
operating voltage for main current circuit at AC at 60 Hz maximum	600 V
operating voltage at AC-3 rated value maximum	600 V
mechanical service life (operating cycles) of the main contacts typical	30 000 000
Auxiliary contact	
number of NC contacts for auxiliary contacts	1
number of NO contacts for auxiliary contacts	1
number of total auxiliary contacts maximum	8
contact rating of auxiliary contacts of contactor according to UL	10A@600V(A600), 2.5A@600V(Q600)
Coil	
apparent pick-up power of magnet coil at AC	67 VA
apparent holding power of magnet coil at AC	6.5 VA
operating range factor control supply voltage rated value of magnet coil	0.8 ... 1.1
ON-delay time	9 ... 38 ms
OFF-delay time	4 ... 16 ms
Overload relay	

product function				
• overload protection		Yes		
• test function		Yes		
• external reset		Yes		
reset function		Manual, automatic and remote (with optional accessory)		
adjustment range of thermal overload trip unit		4.5 ... 6.3		
number of NC contacts of auxiliary contacts of overload relay		1		
number of NO contacts of auxiliary contacts of overload relay		1		
contact rating of auxiliary contacts of overload relay according to UL		5A@600VAC (B600), 1A@250VDC (R300)		
Enclosure				
degree of protection NEMA rating of the enclosure		NEMA 1 standard size enclosure		
design of the housing		indoors, usable on a general basis		
Mounting/wiring				
mounting position		vertical		
fastening method		Surface mounting and installation		
type of electrical connection for supply voltage line-side		Screw-type terminals		
tightening torque [lbf-in] for supply		18 ... 21 lbf-in		
type of connectable conductor cross-sections at line-side for AWG cables single or multi-stranded		2x (16 ... 12), 2x (14 ... 8)		
temperature of the conductor for supply maximum permissible		60 °C		
material of the conductor for supply		CU		
type of electrical connection for load-side outgoing feeder		Screw-type terminals		
tightening torque [lbf-in] for load-side outgoing feeder		18 ... 21 lbf-in		
type of connectable conductor cross-sections for AWG cables for load-side outgoing feeder single or multi-stranded		2x (16 ... 12), 2x (14 ... 8)		
temperature of the conductor for load-side outgoing feeder maximum permissible		60 °C		
material of the conductor for load-side outgoing feeder		CU		
type of electrical connection of magnet coil		Screw-type terminals		
tightening torque [lbf-in] at magnet coil		7 ... 10 lbf-in		
type of connectable conductor cross-sections of magnet coil for AWG cables single or multi-stranded		2x (16 ... 12), 2x (14 ... 8)		
temperature of the conductor at magnet coil maximum permissible		75 °C		
material of the conductor at magnet coil		CU		
type of electrical connection for auxiliary contacts		Screw-type terminals		
tightening torque [lbf-in] at contactor for auxiliary contacts		7 ... 10 lbf-in		
type of connectable conductor cross-sections at contactor for AWG cables for auxiliary contacts single or multi-stranded		2x (20 ... 16), 2x (18 ... 14)		
temperature of the conductor at contactor for auxiliary contacts maximum permissible		75 °C		
material of the conductor at contactor for auxiliary contacts		CU		
type of electrical connection at overload relay for auxiliary contacts		Screw-type terminals		
tightening torque [lbf-in] at overload relay for auxiliary contacts		7 ... 10 lbf-in		
type of connectable conductor cross-sections at overload relay for AWG cables for auxiliary contacts single or multi-stranded		2x (20 ... 16), 2x (18 ... 14)		
temperature of the conductor at overload relay for auxiliary contacts maximum permissible		70 °C		
material of the conductor at overload relay for auxiliary contacts		CU		
Short-circuit current rating				
design of the fuse link for short-circuit protection of the main circuit required		Class J		
design of the short-circuit trip		Thermal magnetic circuit breaker		
maximum short-circuit current breaking capacity (Icu)				
• at 240 V		5 kA		
• at 480 V		5 kA		
• at 600 V		5 kA		
certificate of suitability		UL 60947-4-1		
Approvals Certificates				
General Product Approval	Test Certificates	other	Dangerous goods	Environment

[Confirmation](#)[Transport Information](#)[Environmental Con-
firmations](#)

Further information

Industrial Controls - Product Overview (Catalogs, Brochures,...)

www.usa.siemens.com/iccatalog

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=3RE4122-3AA31-1GB0>

Search Datasheet in Service&Support (Manuals)


<https://support.industry.siemens.com/cs/US/en/ps/3RE4122-3AA31-1GB0/man>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RE4122-3AA31-1GB0&lang=en

Certificates/approvals

<https://support.industry.siemens.com/cs/US/en/ps/3RE4122-3AA31-1GB0/certificate>



LETTER	KNOCKOUT & CONDUIT SIZE
A	ø22.2 FOR 12.7 CONDUIT
B	ø22.2 X ø28.6 FOR 12.7 & 19 CONDUIT
C	ø28.6 X ø34.9 FOR 19 & 25.4 CONDUIT

last modified:

1/25/2022

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[3RE41223AA311GB0](#)