





Solid-state contactor 1-phase 3RF2 AC 51 / 20 A / 40 °C 24-230 V / 110-230 V AC  
short circuit-proof with B miniature circuit breaker

product brand name	SIRIUS
product designation	solid-state contactor
design of the product	single-phase
product type designation	3RF23
<b>General technical data</b>	
product function	short-circuit resistant with B-automatic device
power loss [W] for rated value of the current	
• at AC in hot operating state	20 W
• at AC in hot operating state per pole	20 W
• without load current share typical	3.5 W
insulation voltage rated value	600 V
degree of pollution	3
type of voltage	
• of the operating voltage	AC
• of the control supply voltage	AC
surge voltage resistance of main circuit rated value	6 kV
protection class IP	IP20
protection class IP on the front according to IEC 60529	IP20
shock resistance according to IEC 60068-2-27	15g / 11 ms
vibration resistance according to IEC 60068-2-6	2g
reference code according to IEC 81346-2	Q
Substance Prohibitance (Date)	05/28/2009
SVHC substance name	Lead - 7439-92-1 Lead monoxide (lead oxide) - 1317-36-8 Dibutylbis(pentane-2,4-dionato-O,O')tin - 22673-19-4
Weight	0.19 kg
<b>Main circuit</b>	
number of poles for main current circuit	1
number of NO contacts for main contacts	1
number of NC contacts for main contacts	0
type of voltage of the operating voltage	AC
operating voltage	
• at AC	
— at 50 Hz rated value	24 ... 230 V
— at 60 Hz rated value	24 ... 230 V
operating frequency rated value	50 ... 60 Hz
operating range relative to the operating voltage at AC	
• at 50 Hz	20 ... 253 V
• at 60 Hz	20 ... 253 V
operational current	
• at AC-51 rated value	20 A

<ul style="list-style-type: none"> <li>• at AC-51 according to IEC 60947-4-3</li> <li>• according to UL 508 rated value</li> </ul>	13.2 A 17.6 A
<b>operational current minimum</b>	500 mA
<b>operational current of the MCB at AC rated value</b>	20 A
<b>rate of voltage rise at the thyristor for main contacts maximum permissible</b>	1 000 V/μs
<b>blocking voltage at the thyristor for main contacts maximum permissible</b>	800 V
<b>reverse current of the thyristor</b>	10 mA
<b>derating temperature</b>	40 °C
<b>surge current resistance rated value</b>	1 150 A
<b>I<sup>2</sup>t value maximum</b>	6 600 A <sup>2</sup> ·s
<b>Control circuit/ Control</b>	
<b>type of voltage of the control supply voltage</b>	AC
<b>control supply voltage 1 at AC</b> <ul style="list-style-type: none"> <li>• at 50 Hz</li> <li>• at 60 Hz</li> </ul>	110 ... 230 V 110 ... 230 V
<b>control supply voltage frequency</b> <ul style="list-style-type: none"> <li>• 1 rated value</li> <li>• 2 rated value</li> </ul>	50 Hz 60 Hz
<b>control supply voltage at AC</b> <ul style="list-style-type: none"> <li>• at 50 Hz full-scale value for signal&lt;0&gt; recognition</li> <li>• at 60 Hz full-scale value for signal&lt;0&gt; recognition</li> </ul>	40 V 40 V
<b>control supply voltage</b> <ul style="list-style-type: none"> <li>• at AC initial value for signal &lt;1&gt; detection</li> </ul>	90 V
<b>symmetrical line frequency tolerance</b>	5 Hz
<b>control current at minimum control supply voltage</b> <ul style="list-style-type: none"> <li>• at AC</li> </ul>	2 mA
control current at AC rated value	15 mA
<b>ON-delay time</b>	40 ms; additionally max. one half-wave
<b>OFF-delay time</b>	40 ms; additionally max. one half-wave
<b>Auxiliary circuit</b>	
<b>type of switching contact</b>	normally open contact (NO)
<b>number of NC contacts for auxiliary contacts</b>	0
<b>number of NO contacts for auxiliary contacts</b>	0
number of CO contacts for auxiliary contacts	0
<b>Installation/ mounting/ dimensions</b>	
fastening method side-by-side mounting	Yes
<b>fastening method</b>	screw fixing and snap-on mounting on standard mounting rail 35 mm according to IEC 60715
<b>design of the thread of the screw for securing the equipment</b>	M4
<b>height</b>	95 mm
<b>width</b>	22.5 mm
<b>depth</b>	120 mm
<b>Connections/ Terminals</b>	
<b>product component removable terminal for auxiliary and control circuit</b>	Yes
<b>type of electrical connection</b> <ul style="list-style-type: none"> <li>• for main current circuit</li> <li>• for auxiliary and control circuit</li> </ul>	spring-loaded terminals spring-loaded terminals
<b>type of connectable conductor cross-sections</b> <ul style="list-style-type: none"> <li>• for main contacts <ul style="list-style-type: none"> <li>— solid</li> <li>— finely stranded with core end processing</li> <li>— finely stranded without core end processing</li> </ul> </li> <li>• for AWG cables for main contacts</li> </ul>	2x (0.5 ... 2.5 mm <sup>2</sup> ) 2x (0.5 ... 1.5 mm <sup>2</sup> ) 2x (0.5 ... 2.5 mm <sup>2</sup> ) 2x (18 ... 14)
<b>connectable conductor cross-section for main contacts</b> <ul style="list-style-type: none"> <li>• solid or stranded</li> <li>• finely stranded with core end processing</li> <li>• finely stranded without core end processing</li> </ul>	0.5 ... 2.5 mm <sup>2</sup> 0.5 ... 0.5 mm <sup>2</sup> 0.5 ... 2.5 mm <sup>2</sup>
<b>type of connectable conductor cross-sections</b>	

<ul style="list-style-type: none"><li>• for auxiliary and control contacts<ul style="list-style-type: none"><li>— solid0.5 ... 1.5 mm²</li><li>— finely stranded with core end processing0.5 ... 2.5 mm²</li><li>— finely stranded without core end processing0.5 ... 2.5 mm²</li></ul></li><li>• for AWG cables for auxiliary and control contacts1x (AWG 20 ... 12)</li></ul>			
AWG number as coded connectable conductor cross section for main contacts	14 ... 18		
<b>stripped length of the cable</b>			
<ul style="list-style-type: none"><li>• for main contacts7 mm</li><li>• for auxiliary and control contacts7 mm</li></ul>			
Electrical Safety			
<b>protection class IP on the front according to IEC 60529</b>	IP20		
<b>touch protection on the front according to IEC 60529</b>	finger-safe, for vertical contact from the front		
Ambient conditions			
installation altitude at height above sea level maximum	1 000 m		
<b>ambient temperature</b>			
<ul style="list-style-type: none"><li>• during operation-25 ... +60 °C</li><li>• during storage-55 ... +80 °C</li></ul>			
Electromagnetic compatibility			
<b>conducted interference</b>			
<ul style="list-style-type: none"><li>• due to burst according to IEC 61000-4-42 kV / 5 kHz behavior criterion 2</li><li>• due to conductor-earth surge according to IEC 61000-4-52 kV behavior criterion 2</li><li>• due to conductor-conductor surge according to IEC 61000-4-51 kV behavior criterion 2</li><li>• due to high-frequency radiation according to IEC 61000-4-6140 dBuV in the frequency range 0.15 ... 80 MHz, behavior criterion 1</li></ul>			
<b>field-based interference according to IEC 61000-4-3</b>	80 MHz ... 1 GHz 10 V/m, behavior criterion 1		
<b>electrostatic discharge according to IEC 61000-4-2</b>	4 kV contact discharging / 8 kV air discharging, behavior criterion 2		
<b>conducted HF interference emissions according to CISPR11</b>	Class A for industrial environment		
<b>field-bound HF interference emission according to CISPR11</b>	Class B for the domestic, business and commercial environments		
Short-circuit protection, design of the fuse link			
manufacturer's article number			
<ul style="list-style-type: none"><li>• of gS fuse for semiconductor protection at NH design usable<a href="#">3NE1814-0</a></li><li>• of full range R fuse link for semiconductor protection at cylindrical design usable<a href="#">5SE1325</a></li><li>• of back-up R fuse link for semiconductor protection at NH design usable<a href="#">3NE8015-1</a></li><li>• of back-up R fuse link for semiconductor protection at cylindrical design 10 x 38 mm usable<a href="#">3NC1032</a></li><li>• of back-up R fuse link for semiconductor protection at cylindrical design 14 x 51 mm usable<a href="#">3NC1450</a></li><li>• of back-up R fuse link for semiconductor protection at cylindrical design 22 x 58 mm usable<a href="#">3NC2263</a></li></ul>			
manufacturer's article number of the gG fuse			
<ul style="list-style-type: none"><li>• at NH design usable<a href="#">3NA6807</a></li><li>• at cylindrical design 10 x 38 mm usable<a href="#">3NW6007-1</a></li><li>• at cylindrical design 14 x 51 mm usable<a href="#">3NW6107-1</a></li><li>• at cylindrical design 22 x 58 mm usable<a href="#">3NW6207-1: These fuses have a smaller rated current than the semiconductor relays</a></li></ul>			
manufacturer's article number			
<ul style="list-style-type: none"><li>• of DIAZED fuse usable<a href="#">5SB2711</a></li><li>• of NEOZED fuse usable<a href="#">5SE2320</a></li></ul>			
Approvals Certificates			
General Product Approval	EMV	Test Certificates	
<div><div> EG-Konf.</div><div></div><div> UL</div><div></div><div> RCM</div><div><a href="#">Type Test Certificates/Test Report</a></div></div>			
Test Certificates	other	Railway	Environment



# Further information

## Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

## Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

## Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RF2320-2DA22>

## Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RF2320-2DA22>


## Service&Support (Manuals, Certificates, Characteristics, FAQs,...)



<https://support.industry.siemens.com/cs/ww/en/ps/3RF2320-2DA22>

## Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3RF2320-2DA22&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RF2320-2DA22&lang=en)







last modified:

4/2/2025

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[3RF23202DA22](#)