



Figure similar

AS-i SlimLine module Phased-out product !!! For further information, please contact our sales department S22.5 digital 4 DI, IP20 4 x input for 2-wire sensor spring-type terminals Overall width 22.5 mm

General technical data		
design of the product		SlimLine S22.5 - I/O modules for operation in the control cabinet, IP20
design of the slave type		standard slave
Type		4 inputs
I/O configuration		0
ID/ID2 code		0/F
protocol is supported AS-Interface protocol		Yes
AS interface total current input max	mA	50
operating voltage according to AS-Interface specification	V	26.5 ... 31.6
Addressing		front addressing socket
type of electrical connection of the inputs and outputs		spring-loaded terminals
reference code according to DIN 40719 extended according to IEC 204-2 according to IEC 750		A
reference code according to EN 61346-2		K
note		An external additional supply (AUX POWER) of 20 to 30 V DC is required for the supply of the output circuits. The additional supply must comply with VDE 0106 (PELV), protection class III.
Note 1		detachment tool for spring-loaded terminal connection: See Accessories
Sensor supply		
type of voltage supply for sensor supply		using AS-Interface
input voltage	V	20 ... 30
property of the sensor supply short-circuit and overload resistant		Yes
Inputs		
number of digital inputs		4
type of connection technology		2-wire technology
Input circuit		PNP transistor
type of voltage of the input voltages		DC
Inputs switching level High min	V	10
input current at digital input		
• for signal <1> minimum	mA	5
• with signal <0> maximum	mA	1.5
Inputs sensor supply using AS-Interface		short-circuit and overload resistant
Outputs		
number of digital outputs		0
output voltage at DC at 24 V	V	22 ... 24
Status display		
• display of I/Os		yellow LED
• AS-Interface		green LED

• FAULT		red LED
Assignment of data bits		
• D0		IN1
• D1		IN2
• D2		IN3
• D3		IN4

Ambient conditions

ambient temperature		
• during operation	°C	-25 ... +70
• during storage	°C	-40 ... +85
protection class IP		IP20

Mechanical data

width	mm	22.5
height	mm	103
depth	mm	86
fastening method		35 mm standard rail mounting or wall mounting using push-in lugs
Conductor cross-section		
• solid		2 x (0.25 - 1.5) mm ²
• finely stranded		
— with end sleeve		2 x (0.25 - 1) mm ²
— without end sleeve		2 x (0.25 - 1.5) mm ²
• AWG solid or stranded		AWG 2 x (24 - 16) mm ²

Certificates/ approvals

General Product Approval	EMV
--------------------------	-----



[Confirmation](#)



EMV	Marine / Shipping	other	Environment
-----	-------------------	-------	-------------

[KC](#)



[Confirmation](#)

[Miscellaneous](#)

[Environmental Confirmations](#)

Industrial Communication



Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RK1200-0CG00-0AA2>

Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RK1200-0CG00-0AA2>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RK1200-0CG00-0AA2>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RK1200-0CG00-0AA2&lang=en



last modified:

3/11/2024 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[3RK12000CG000AA2](#)