



AS-i compact module K60 digital 4 DI, IP67 4 x input, maximum 200 mA 4 x M12 socket Y-II assignment Mounting plate 3RK1901-0CA00 must be ordered separately

General technical data	
design of the product	digital I/O modules for operation in the field, IP67 - K60
Type	4 inputs
design of the slave type	standard slave
I/O configuration	0
ID/ID2 code	1/F
Number I/O sockets	4
type of electrical connection of the inputs and outputs	M12 screw-type terminals
AS interface total current input max	270 mA
operating voltage according to AS-Interface specification	26.5 ... 31.6 V
Ground terminal	PIN5 of each M12 socket is connected to the grounding wrist strap in the mounting plate using a pin
Addressing	front addressing socket
Delivery note	the modules are delivered without mounting plate
Sensor supply	
type of voltage supply for sensor supply	using AS-Interface
input voltage	20 ... 30 V
property of the sensor supply short-circuit and overload resistant	Yes
ampacity of the sensor supply for all inputs at ambient temperature 40 °C	200 mA
Inputs	
number of digital inputs	4
type of connection technology	2- and 3-wire technology
Input circuit	PNP transistor
type of voltage of the input voltages	DC
Inputs switching level High min	10 V
input current at digital input - for signal <1> minimum - with signal <0> maximum	6 mA 1.5 mA
Inputs - sensor supply using AS-Interface - socket assignment - PIN 1 - PIN 2 - PIN 3 - PIN 4 - PIN 5	short-circuit and overload resistant sensor supply L+ data input II sensor supply L- data input I ground terminal
design of the pin assignment of the inputs	Y-II assignment
Outputs	
number of digital outputs	0

Outputs external power supply 24 V DC	not required
design of the pin assignment of the outputs	Y-II assignement
Outputs	
• watchdog	not required
Assignment of the data bits	
Assignment of data bits	
• socket	PIN 4 = IN1 (D0), PIN 2 = IN2 (D1)
• socket 2	PIN 4 = IN2 (D1)
• socket 3	PIN 4 = IN3 (D2) , PIN 2 = IN4 (D3)
• socket 4	PIN 4 = IN4 (D3)
• socket 5	not assigned (closed)
• socket 6	not assigned (closed)
• socket 7	not assigned (closed)
• socket 8	not assigned (closed)
Ambient conditions	
ambient temperature	
• during operation	-25 ... +85 °C
• during storage	-40 ... +85 °C
protection class IP	IP67
Display	
Status display	
• display of I/Os	yellow LED
• display of Uaux	not required
• display of AS-Interface/diagnostics	green/red LED
Mechanical data	
width	60 mm
height	152 mm
depth	29 mm
fastening method	standard rail mounting/wall mounting using mounting plate for K60 compact module
shock resistance	15g / 11 ms
Certificates/ approvals	
General Product Approval	EMV



[Confirmation](#)



EMV	Marine / Shipping	other
-----	-------------------	-------

[KC](#)



[Confirmation](#)

[Miscellaneous](#)

Environment	Industrial Communication
-------------	--------------------------

[Environmental Confirmations](#)



Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)


<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RK1200-0CQ00-0AA3>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RK1200-0CQ00-0AA3>



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[3RK12000CQ000AA3](#)