

STARTER, 3RE41235CA114FY0, WITH MODS



product brand name	Siemens
product designation	Non-reversing motor starter
special product feature	Hand-Off-Auto Selector Switch
<b>General technical data</b>	
weight [lb]	21 lb(av)
Height x Width x Depth [in]	14 × 12 × 8 in
touch protection against electrical shock	NA for enclosed products
installation altitude [ft] at height above sea level maximum	6 560 ft
country of origin	Germany
<b>Power and control electronics</b>	
number of poles for main current circuit	3
type of voltage of the control supply voltage	AC
control supply voltage	
• at AC at 50 Hz rated value	24 V
• at AC at 60 Hz rated value	24 V
disconnecter functionality	No
yielded mechanical performance [hp] for 3-phase AC motor	
• at 200/208 V rated value	10 hp
• at 220/230 V rated value	15 hp
• at 460/480 V rated value	30 hp
• at 575/600 V rated value	40 hp
<b>Contactor</b>	
number of NO contacts for main contacts	3
operating voltage for main current circuit at AC at 60 Hz maximum	600 V
operating voltage at AC-3 rated value maximum	600 V
mechanical service life (operating cycles) of the main contacts typical	30 000 000
<b>Auxiliary contact</b>	
number of NC contacts for auxiliary contacts	1
number of NO contacts for auxiliary contacts	1
number of total auxiliary contacts maximum	8
contact rating of auxiliary contacts of contactor according to UL	10A@600V(A600), 5A@600V(P600)
<b>Coil</b>	
apparent pick-up power of magnet coil at AC	188 VA
apparent holding power of magnet coil at AC	16.5 VA
operating range factor control supply voltage rated value of magnet coil	0.8 ... 1.1
ON-delay time	10 ... 80 ms
OFF-delay time	10 ... 18 ms
<b>Overload relay</b>	

product function				
• overload protection		Yes		
• test function		Yes		
• external reset		Yes		
reset function		Manual, automatic and remote (with optional accessory)		
adjustment range of thermal overload trip unit		28 ... 40		
number of NC contacts of auxiliary contacts of overload relay		1		
number of NO contacts of auxiliary contacts of overload relay		1		
contact rating of auxiliary contacts of overload relay according to UL		5A@600VAC (B600), 1A@250VDC (R300)		
Enclosure				
degree of protection NEMA rating of the enclosure		NEMA 3/3R/4/12 enclosure		
design of the housing		Dust- & watertight for outdoor use		
Mounting/wiring				
mounting position		vertical		
fastening method		Surface mounting and installation		
type of electrical connection for supply voltage line-side		Box lug		
tightening torque [lbf-in] for supply		26 ... 39 lbf-in		
type of connectable conductor cross-sections at line-side for AWG cables single or multi-stranded		2x (18 ... 2), 1x (18 ... 1)		
temperature of the conductor for supply maximum permissible		60 °C		
material of the conductor for supply		CU		
type of electrical connection for load-side outgoing feeder		Box lug		
tightening torque [lbf-in] for load-side outgoing feeder		26 ... 39 lbf-in		
type of connectable conductor cross-sections for AWG cables for load-side outgoing feeder single or multi-stranded		2x (18 ... 2), 1x (18 ... 1)		
temperature of the conductor for load-side outgoing feeder maximum permissible		60 °C		
material of the conductor for load-side outgoing feeder		CU		
type of electrical connection of magnet coil		Screw-type terminals		
tightening torque [lbf-in] at magnet coil		7 ... 10 lbf-in		
type of connectable conductor cross-sections of magnet coil for AWG cables single or multi-stranded		2x (18 ... 2), 1x (18 ... 1)		
temperature of the conductor at magnet coil maximum permissible		75 °C		
material of the conductor at magnet coil		CU		
type of electrical connection for auxiliary contacts		Screw-type terminals		
tightening torque [lbf-in] at contactor for auxiliary contacts		7 ... 10 lbf-in		
type of connectable conductor cross-sections at contactor for AWG cables for auxiliary contacts single or multi-stranded		2x (20 ... 16), 2x (18 ... 14)		
temperature of the conductor at contactor for auxiliary contacts maximum permissible		75 °C		
material of the conductor at contactor for auxiliary contacts		CU		
type of electrical connection at overload relay for auxiliary contacts		Screw-type terminals		
tightening torque [lbf-in] at overload relay for auxiliary contacts		7 ... 10 lbf-in		
type of connectable conductor cross-sections at overload relay for AWG cables for auxiliary contacts single or multi-stranded		2x (20 ... 16), 2x (18 ... 14)		
temperature of the conductor at overload relay for auxiliary contacts maximum permissible		70 °C		
material of the conductor at overload relay for auxiliary contacts		CU		
Short-circuit current rating				
design of the fuse link for short-circuit protection of the main circuit required		Class J		
design of the short-circuit trip		Thermal magnetic circuit breaker		
maximum short-circuit current breaking capacity (Icu)				
• at 240 V		5 kA		
• at 480 V		5 kA		
• at 600 V		5 kA		
certificate of suitability		UL 60947-4-1		
Approvals Certificates				
General Product Approval	Test Certificates	other	Dangerous goods	Environment

[Confirmation](#)[Transport Information](#)[Environmental Con-  
firmations](#)

#### Further information

Industrial Controls - Product Overview (Catalogs, Brochures,...)

[www.usa.siemens.com/iccatalog](http://www.usa.siemens.com/iccatalog)

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/us/Catalog/product?mlfb=3RE4123-5CA11-4FF6>

Search Datasheet in Service&Support (Manuals)


<https://support.industry.siemens.com/cs/US/en/ps/3RE4123-5CA11-4FF6/man>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3RE4123-5CA11-4FF6&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RE4123-5CA11-4FF6&lang=en)

Certificates/approvals

<https://support.industry.siemens.com/cs/US/en/ps/3RE4123-5CA11-4FF6/certificate>



last modified:

4/15/2021

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[3RE41235CA114FF6](#)