

Control cable Pre-assembled at one end M12 connector angled, 5-pole with 10 m cable 5 x 0.34 mm² A-coded max. 4 A PUR sheath black



General technical data		
product description		M12 lead, angled on one side
wire length	m	10
General technical data		
ampacity per pin maximum	A	4
operating voltage at DC maximum	V	125
surge voltage resistance rated value	V	1 500
Mechanical data		
type of connection technology		plugged, screwed
connector type		M12
connector coding of the M12 circular connector		A
number of electrical cores		5
type of cable outlet		angled
number of poles		5
color of cable sheath		Black
material of cable sheath		PUR-OB
color of the insulation of data wires		see wiring diagram
material of the wire insulation		polypropylene (PP)
design of the shield		unshielded
type of strain relief		cast
outer diameter		
• of the cable	mm	5
• of inner conductor	mm	0.34
type of connectable conductor cross-sections stranded		5 x 0.34 mm ²
type of plug interlock		M12 x 1 thread
cable end components		open on one side
Ambient conditions		
ambient temperature during operation		
• minimum	°C	-25
• maximum	°C	80
protection class IP		IP67
chemical resistance		
• to ASTM oil 2		conditional, must be checked relative to the application
• to mineral oil		conditional, must be checked relative to the application
• to water		conditional, must be checked relative to the application
• to grease		conditional, must be checked relative to the application
degree of pollution		3
Certificates/ approvals		
certificate of suitability		
• CSA approval		Yes

- UL approval
- IEC approval

Yes
Yes

Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RK1902-4HC01-5AA0>

Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RK1902-4HC01-5AA0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3RK1902-4HC01-5AA0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RK1902-4HC01-5AA0&lang=en



1		brown/ braun (+)
2		white/ weiss (NC)
3		blue/ blau (-)
4		black/ schwarz (NO)
5		gray/ grau

last modified:

12/21/2020

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[3RK19024HC015AA0](#)