

AS-i compact module K45 digital A/B device, 4 DI, IP67, 4 x input, maximum 200 mA 4 x M12 socket mounting plate 3RK1901-2EA00 or 3RK1901-2DA00 is to be ordered separately

General technical data

design of the product	digital I/O modules for operation in the field, IP67 - K45
Type	4 inputs
design of the slave type	A/B slave
I/O configuration	0
ID/ID2 code	A/0
Number I/O sockets	4
type of electrical connection of the inputs and outputs	M12 screw-type terminals
AS interface total current input max	270 mA
operating voltage according to AS-Interface specification	26.5 ... 31.6 V
Ground terminal	Using PIN5 on the M12 sockets. Outgoing via flat tab sleeve (2.8 x 0.8 mm form A)
Addressing	front addressing socket
AS interface Connection Polarity reversal protection	built-in
Delivery note	the modules are delivered without mounting plate

Sensor supply

type of voltage supply for sensor supply	using AS-Interface
input voltage	20 ... 30 V
property of the sensor supply short-circuit and overload resistant	Yes
ampacity of the sensor supply for all inputs	
• at ambient temperature 40 °C	200 mA

Inputs

number of digital inputs	4
type of connection technology	2- and 3-wire technology
Input circuit	PNP transistor
type of voltage of the input voltages	DC
Inputs switching level High min	10 V
input current at digital input	
• for signal <1> minimum	6 mA
• with signal <0> maximum	1.5 mA
Inputs sensor supply using AS-Interface	short-circuit and overload resistant
Inputs socket assignment	
• PIN 1	sensor supply L+
• PIN 2	data input
• PIN 3	sensor supply L-
• PIN 4	data input
• PIN 5	ground terminal
design of the pin assignment of the inputs	standard assignment

Outputs

number of digital outputs	0
---------------------------	---

Display	
Status display	
- display of I/Os - display of Uaux - display of AS-Interface/diagnostics	yellow LED not required green/red dual LED
Assignment of the data bits	
Assignment of data bits	
- socket - socket 2 - socket 3 - socket 4	PIN 4/2 = IN1 (D0) PIN 4/2 = IN2 (D1) PIN 4/2 = IN3 (D2) PIN 4/2 = IN4 (D3)
Ambient conditions	
ambient temperature	
- during operation - during storage	-25 ... +85 °C -40 ... +85 °C
protection class IP	IP67
Mechanical data	
width	45 mm
height	80 mm
depth	30 mm
fastening method	standard rail mounting/wall mounting using mounting plate for K45 compact module
shock resistance	15g / 11 ms
Certificates/ approvals	
General Product Approval	EMV




[KC](#)

Marine / Shipping	other	Environment
	Confirmation	Miscellaneous
		Environmental Confirmations

Industrial Communication

Further information
Information on the packaging https://support.industry.siemens.com/cs/ww/en/view/109813875
Information- and Downloadcenter (Catalogs, Brochures,...) https://www.siemens.com/ic10
Industry Mall (Online ordering system) https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3RK2200-0CQ20-0AA3
Cax online generator http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RK2200-0CQ20-0AA3
Service&Support (Manuals, Certificates, Characteristics, FAQs,...) https://support.industry.siemens.com/cs/ww/en/ps/3RK2200-0CQ20-0AA3
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...) http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3RK2200-0CQ20-0AA3&lang=en



last modified:

4/1/2025 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[3RK22000CQ200AA3](#)