




|                                                  |                                                 |
|--------------------------------------------------|-------------------------------------------------|
| product brand name                               | SIRIUS ACT                                      |
| product designation                              | Key-operated switches                           |
| design of the product                            | Actuating/signaling element                     |
| product type designation                         | 3SU1                                            |
| product line                                     | Plastic, black, 22 mm                           |
| manufacturer's article number of included key    | <a href="#">3SU1950-0FJ50-0AA0</a>              |
| Actuator                                         |                                                 |
| principle of operation of the actuating element  | latching, 2x45° (10:30 h/12 h/13:30 h)          |
| product extension optional light source          | No                                              |
| color                                            |                                                 |
| • of the actuating element                       | blue                                            |
| material of the actuating element                | metal                                           |
| shape of the actuating element                   | Key                                             |
| outer diameter of the actuating element          | 29.5 mm                                         |
| marking of the actuating element                 | Customized labeling, text in lower case letters |
| number of switching positions                    | 3                                               |
| switch position for key distraction              | O+I+II                                          |
| actuating angle                                  |                                                 |
| • clockwise                                      | 45°                                             |
| • anticlockwise                                  | 45°                                             |
| lock make                                        | O.M.R.                                          |
| key number                                       | 73038                                           |
| Front ring                                       |                                                 |
| product component front ring                     | Yes                                             |
| design of the front ring                         | Standard                                        |
| material of the front ring                       | plastic                                         |
| color of the front ring                          | black                                           |
| General technical data                           |                                                 |
| protection class IP                              | IP66, IP67, IP69(IP69K)                         |
| • of the terminal                                | IP20                                            |
| degree of protection NEMA rating                 | 1, 2, 3, 3R, 4, 4X, 12, 13                      |
| shock resistance                                 |                                                 |
| • according to IEC 60068-2-27                    | sinusoidal half-wave 15g / 11 ms                |
| • for railway applications according to EN 61373 | Category 1, Class B                             |
| vibration resistance                             |                                                 |
| • according to IEC 60068-2-6                     | 10 ... 500 Hz: 5g                               |
| • for railway applications according to EN 61373 | Category 1, Class B                             |

|                                                    |            |
|----------------------------------------------------|------------|
| operating frequency maximum                        | 1 800 1/h  |
| mechanical service life (operating cycles) typical | 1 000 000  |
| reference code according to IEC 81346-2            | S          |
| Substance Prohibittance (Date)                     | 10/01/2014 |

#### Ambient conditions

|                                                                |                                                                    |
|----------------------------------------------------------------|--------------------------------------------------------------------|
| ambient temperature                                            |                                                                    |
| • during operation                                             | -25 ... +70 °C                                                     |
| • during storage                                               | -40 ... +80 °C                                                     |
| environmental category during operation according to IEC 60721 | 3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 ... 95%) |

#### Environmental footprint

|                                                        |                 |
|--------------------------------------------------------|-----------------|
| Environmental Product Declaration (EPD)                | Yes             |
| Global Warming Potential [CO2 eq] total                | 0.787 kg        |
| Global Warming Potential [CO2 eq] during manufacturing | 0.566 kg        |
| Global Warming Potential [CO2 eq] during operation     | 0.235 kg        |
| Global Warming Potential [CO2 eq] after end of life    | -0.015 kg       |
| Siemens Eco Profile (SEP)                              | Siemens EcoTech |

#### Installation/ mounting/ dimensions

|                                             |         |
|---------------------------------------------|---------|
| height                                      | 29.5 mm |
| width                                       | 29.5 mm |
| shape of the installation opening           | round   |
| mounting diameter                           | 22.3 mm |
| positive tolerance of installation diameter | 0.4 mm  |
| mounting height                             | 51.7 mm |
| installation width                          | 29.5 mm |
| installation depth                          | 25.4 mm |

#### Approvals Certificates

|                          |                   |                   |
|--------------------------|-------------------|-------------------|
| General Product Approval | Test Certificates | Marine / Shipping |
|--------------------------|-------------------|-------------------|

[Confirmation](#)



[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)



|                   |       |             |
|-------------------|-------|-------------|
| Marine / Shipping | other | Environment |
|-------------------|-------|-------------|



[Confirmation](#)



Siemens  
EcoTech



#### Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1000-4GL11-0AA0-Z Y12>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1000-4GL11-0AA0-Z Y12>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1000-4GL11-0AA0-Z Y12>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SU1000-4GL11-0AA0-Z Y12&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1000-4GL11-0AA0-Z Y12&lang=en)

last modified:

3/2/2024

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[A6X30136239](#)