




|                                                  |                                                                                                 |
|--------------------------------------------------|-------------------------------------------------------------------------------------------------|
| product brand name                               | SIRIUS ACT                                                                                      |
| product designation                              | Indicator lights                                                                                |
| design of the product                            | Actuating/signaling element                                                                     |
| product type designation                         | 3SU1                                                                                            |
| product line                                     | Plastic, black, 22 mm                                                                           |
| Enclosure                                        |                                                                                                 |
| number of command points                         | 1                                                                                               |
| Actuator                                         |                                                                                                 |
| design of the actuating element                  | Illuminated pushbutton design                                                                   |
| principle of operation of the actuating element  | Fixed key                                                                                       |
| product extension optional                       |                                                                                                 |
| • light source                                   | Yes                                                                                             |
| • contact module                                 | Yes                                                                                             |
| color of the actuating element                   | green                                                                                           |
| material of the actuating element                | plastic                                                                                         |
| shape of the actuating element                   | round                                                                                           |
| outer diameter of the actuating element          | 29.5 mm                                                                                         |
| marking of the actuating element                 | Customized labeling, text in lower case / capital letters, all words start with capital letters |
| Front ring                                       |                                                                                                 |
| product component front ring                     | Yes                                                                                             |
| design of the front ring                         | Standard                                                                                        |
| material of the front ring                       | plastic                                                                                         |
| color of the front ring                          | black                                                                                           |
| General technical data                           |                                                                                                 |
| protection class IP                              | IP66, IP67, IP69(IP69K)                                                                         |
| degree of protection NEMA rating                 | 1, 2, 3, 3R, 4, 4X, 12, 13                                                                      |
| shock resistance                                 |                                                                                                 |
| • according to IEC 60068-2-27                    | sinusoidal half-wave 15g / 11 ms                                                                |
| • for railway applications according to EN 61373 | Category 1, Class B                                                                             |
| vibration resistance                             |                                                                                                 |
| • according to IEC 60068-2-6                     | 10 ... 500 Hz: 5g                                                                               |
| • for railway applications according to EN 61373 | Category 1, Class B                                                                             |
| reference code according to IEC 81346-2          | S                                                                                               |
| Substance Prohibittance (Date)                   | 10/01/2014                                                                                      |
| Ambient conditions                               |                                                                                                 |
| ambient temperature                              |                                                                                                 |

|                                                                                            |                                                                    |
|--------------------------------------------------------------------------------------------|--------------------------------------------------------------------|
| <ul style="list-style-type: none"> <li>during operation</li> <li>during storage</li> </ul> | -25 ... +70 °C<br>-40 ... +80 °C                                   |
| environmental category during operation according to IEC 60721                             | 3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 ... 95%) |

#### Environmental footprint

|                                                        |                 |
|--------------------------------------------------------|-----------------|
| Environmental Product Declaration (EPD)                | Yes             |
| Global Warming Potential [CO2 eq] total                | 0.787 kg        |
| Global Warming Potential [CO2 eq] during manufacturing | 0.566 kg        |
| Global Warming Potential [CO2 eq] during operation     | 0.235 kg        |
| Global Warming Potential [CO2 eq] after end of life    | -0.015 kg       |
| Siemens Eco Profile (SEP)                              | Siemens EcoTech |

#### Installation/ mounting/ dimensions

|                                             |         |
|---------------------------------------------|---------|
| height                                      | 29.5 mm |
| width                                       | 29.5 mm |
| shape of the installation opening           | round   |
| mounting diameter                           | 22.3 mm |
| positive tolerance of installation diameter | 0.4 mm  |
| mounting height                             | 11 mm   |
| installation width                          | 29.5 mm |
| installation depth                          | 24.3 mm |

#### Approvals Certificates

| General Product Approval                                                                                                                                                                                                                                                           | Test Certificates                                                                           |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------|
|  <a href="#">Confirmation</a>   | <a href="#">Type Test Certificates/Test Report</a> <a href="#">Special Test Certificate</a> |

| Marine / Shipping                                                                                                                                                                                                                                                                                                                               | other                        | Environment                                                                           |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------|---------------------------------------------------------------------------------------|
|     | <a href="#">Confirmation</a> |  |

Environment



#### Further information

Information on the packaging  
<https://support.industry.siemens.com/cs/ww/en/view/109813875>  
Information- and Downloadcenter (Catalogs, Brochures,...)  
<https://www.siemens.com/ic10>  
Industry Mall (Online ordering system)  
<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1001-0AD40-0AA0-Z Y15>  
Cax online generator  
<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1001-0AD40-0AA0-Z Y15>  
Service&Support (Manuals, Certificates, Characteristics, FAQs,...)  
<https://support.industry.siemens.com/cs/ww/en/ps/3SU1001-0AD40-0AA0-Z Y15>  
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)  
[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SU1001-0AD40-0AA0-Z Y15&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1001-0AD40-0AA0-Z Y15&lang=en)

last modified: 2/6/2024 

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[A6X30136743](#)