



RONIS key-operated switch, 22 mm, round, plastic with metal front ring, lock number SB30, with 2 keys, 2 switch positions O-I, latching, actuating angle 90°, 10:30h/13:30h, key removal O+I, possible special locks: SB31, 421, 455, with laser labeling, lower case

|                                                    |                                                 |
|----------------------------------------------------|-------------------------------------------------|
| product brand name                                 | SIRIUS ACT                                      |
| product designation                                | Key-operated switches                           |
| design of the product                              | Actuating/signaling element                     |
| product type designation                           | 3SU1                                            |
| product line                                       | Plastic with metal front ring, matt, 22 mm      |
| manufacturer's article number of included key      | <a href="#">3SU1950-0FB80-0AA0</a>              |
| <b>Actuator</b>                                    |                                                 |
| principle of operation of the actuating element    | latching, 90° (10:30 h/13:30 h)                 |
| product extension optional light source            | No                                              |
| color                                              |                                                 |
| • of the actuating element                         | silver                                          |
| material of the actuating element                  | metal                                           |
| shape of the actuating element                     | Key                                             |
| outer diameter of the actuating element            | 29.5 mm                                         |
| marking of the actuating element                   | Customized labeling, text in lower case letters |
| number of switching positions                      | 2                                               |
| switch position for key distraction                | O+I                                             |
| actuating angle                                    |                                                 |
| • clockwise                                        | 90°                                             |
| lock make                                          | RONIS                                           |
| key number                                         | SB30                                            |
| <b>Front ring</b>                                  |                                                 |
| product component front ring                       | Yes                                             |
| design of the front ring                           | Standard                                        |
| material of the front ring                         | Metal, matt                                     |
| color of the front ring                            | sand gray                                       |
| <b>General technical data</b>                      |                                                 |
| protection class IP                                | IP66, IP67, IP69(IP69K)                         |
| • of the terminal                                  | IP20                                            |
| degree of protection NEMA rating                   | 1, 2, 3, 3R, 4, 4X, 12, 13                      |
| shock resistance                                   |                                                 |
| • according to IEC 60068-2-27                      | sinusoidal half-wave 15g / 11 ms                |
| • for railway applications according to EN 61373   | Category 1, Class B                             |
| vibration resistance                               |                                                 |
| • according to IEC 60068-2-6                       | 10 ... 500 Hz: 5g                               |
| • for railway applications according to EN 61373   | Category 1, Class B                             |
| operating frequency maximum                        | 1 800 1/h                                       |
| mechanical service life (operating cycles) typical | 1 000 000                                       |
| reference code according to IEC 81346-2            | S                                               |
| Substance Prohibitation (Date)                     | 10/01/2014                                      |

| Ambient conditions                                             |                                                                    |
|----------------------------------------------------------------|--------------------------------------------------------------------|
| ambient temperature                                            |                                                                    |
| • during operation                                             | -25 ... +70 °C                                                     |
| • during storage                                               | -40 ... +80 °C                                                     |
| environmental category during operation according to IEC 60721 | 3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 ... 95%) |

| Installation/ mounting/ dimensions          |         |
|---------------------------------------------|---------|
| height                                      | 29.5 mm |
| width                                       | 29.5 mm |
| shape of the installation opening           | round   |
| mounting diameter                           | 22.3 mm |
| positive tolerance of installation diameter | 0.4 mm  |
| mounting height                             | 49.4 mm |
| installation width                          | 29.5 mm |
| installation depth                          | 25.4 mm |

| Approvals Certificates   |                   |
|--------------------------|-------------------|
| General Product Approval | Test Certificates |



[Confirmation](#)



[Type Test Certificates/Test Report](#)

|                   |                   |       |
|-------------------|-------------------|-------|
| Test Certificates | Marine / Shipping | other |
|-------------------|-------------------|-------|

[Special Test Certificate](#)



[Confirmation](#)

## Environment

[Environmental Confirmations](#)

## Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1030-4BF11-0AA0-Z Y12>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1030-4BF11-0AA0-Z Y12>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1030-4BF11-0AA0-Z Y12>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SU1030-4BF11-0AA0-Z Y12&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1030-4BF11-0AA0-Z Y12&lang=en)

last modified:

3/2/2024

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[A6X30137859](#)