

Siemens  
EcoTech



RONIS key-operated switch, 22 mm, round, metal, shiny, special lock, with 2 keys, 2 switch positions O-I, latching, actuating angle 90°, 10:30h/13:30h, key removal O, possible special locks: SB31, 421, 455



|                                                    |                                  |
|----------------------------------------------------|----------------------------------|
| product brand name                                 | SIRIUS ACT                       |
| product designation                                | Key-operated switches            |
| design of the product                              | Actuating/signaling element      |
| product type designation                           | 3SU1                             |
| product line                                       | Metal, shiny, 22 mm              |
| <b>Actuator</b>                                    |                                  |
| principle of operation of the actuating element    | latching, 90° (10:30 h/13:30 h)  |
| product extension optional light source            | No                               |
| color                                              |                                  |
| • of the actuating element                         | silver                           |
| material of the actuating element                  | metal                            |
| shape of the actuating element                     | Key                              |
| outer diameter of the actuating element            | 29.5 mm                          |
| number of switching positions                      | 2                                |
| switch position for key distraction                | O                                |
| actuating angle                                    |                                  |
| • clockwise                                        | 90°                              |
| lock make                                          | RONIS                            |
| <b>Front ring</b>                                  |                                  |
| product component front ring                       | Yes                              |
| design of the front ring                           | Standard                         |
| material of the front ring                         | Metal, high gloss                |
| color of the front ring                            | silver                           |
| <b>General technical data</b>                      |                                  |
| protection class IP                                | IP66, IP67, IP69(IP69K)          |
| • of the terminal                                  | IP20                             |
| degree of protection NEMA rating                   | 1, 2, 3, 3R, 4, 4X, 12, 13       |
| shock resistance                                   |                                  |
| • according to IEC 60068-2-27                      | sinusoidal half-wave 15g / 11 ms |
| vibration resistance                               |                                  |
| • according to IEC 60068-2-6                       | 10 ... 500 Hz: 5g                |
| operating frequency maximum                        | 1 800 1/h                        |
| mechanical service life (operating cycles) typical | 300 000                          |
| reference code according to IEC 81346-2            | S                                |
| Substance Prohibitance (Date)                      | 10/01/2014                       |
| <b>Ambient conditions</b>                          |                                  |
| ambient temperature                                |                                  |

- during operation
- during storage

-25 ... +70 °C

-40 ... +80 °C

environmental category during operation according to IEC 60721

3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 ... 95%)

#### Environmental footprint

|                                                        |                 |
|--------------------------------------------------------|-----------------|
| Environmental Product Declaration (EPD)                | Yes             |
| Global Warming Potential [CO2 eq] total                | 0.593 kg        |
| Global Warming Potential [CO2 eq] during manufacturing | 0.625 kg        |
| Global Warming Potential [CO2 eq] during operation     | 0.235 kg        |
| Global Warming Potential [CO2 eq] after end of life    | -0.267 kg       |
| Siemens Eco Profile (SEP)                              | Siemens EcoTech |

#### Installation/ mounting/ dimensions

|                                             |         |
|---------------------------------------------|---------|
| height                                      | 29.5 mm |
| width                                       | 29.5 mm |
| shape of the installation opening           | round   |
| mounting diameter                           | 22.3 mm |
| positive tolerance of installation diameter | 0.4 mm  |
| mounting height                             | 49.4 mm |
| installation width                          | 29.5 mm |
| installation depth                          | 25.4 mm |

#### Approvals Certificates

##### General Product Approval



[Confirmation](#)



#### Test Certificates

#### Marine / Shipping

[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)



#### other

#### Environment

[Confirmation](#)



Siemens EcoTech



#### Further information

##### Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

##### Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

##### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1050-4BF01-0AA0-Z Y01>

##### Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1050-4BF01-0AA0-Z Y01>

##### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1050-4BF01-0AA0-Z Y01>

##### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SU1050-4BF01-0AA0-Z Y01&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1050-4BF01-0AA0-Z Y01&lang=en)

last modified:

2/7/2024

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[A6X30140813](#)