



Selector switch, illuminable, 22 mm, round, plastic with metal front ring, white, selector switch, long, 2 switch positions O-I, latching, actuating angle 90°, 10:30h/13:30h, with laser labeling, upper case and lower case, always upper case at the beginning of the word

|                                                    |                                                                                                 |
|----------------------------------------------------|-------------------------------------------------------------------------------------------------|
| product brand name                                 | SIRIUS ACT                                                                                      |
| product designation                                | Selector switches                                                                               |
| design of the product                              | Actuating/signaling element                                                                     |
| product type designation                           | 3SU1                                                                                            |
| product line                                       | Plastic with metal front ring, matt, 22 mm                                                      |
| <b>Enclosure</b>                                   |                                                                                                 |
| number of command points                           | 1                                                                                               |
| <b>Actuator</b>                                    |                                                                                                 |
| design of the actuating element                    | selector, long                                                                                  |
| principle of operation of the actuating element    | latching, 90° (10:30 h/13:30 h)                                                                 |
| product extension optional                         |                                                                                                 |
| • light source                                     | Yes                                                                                             |
| • contact module                                   | Yes                                                                                             |
| color of the actuating element                     | white                                                                                           |
| material of the actuating element                  | plastic                                                                                         |
| shape of the actuating element                     | Handle                                                                                          |
| outer diameter of the actuating element            | 44.8 mm                                                                                         |
| marking of the actuating element                   | Customized labeling, text in lower case / capital letters, all words start with capital letters |
| number of switching positions                      | 2                                                                                               |
| actuating angle                                    |                                                                                                 |
| • clockwise                                        | 90°                                                                                             |
| <b>Front ring</b>                                  |                                                                                                 |
| product component front ring                       | Yes                                                                                             |
| design of the front ring                           | standard                                                                                        |
| material of the front ring                         | Metal, matt                                                                                     |
| color of the front ring                            | sand gray                                                                                       |
| <b>General technical data</b>                      |                                                                                                 |
| protection class IP                                | IP66, IP67, IP69(IP69K)                                                                         |
| degree of protection NEMA rating                   | 1, 2, 3, 3R, 4, 4X, 12, 13                                                                      |
| shock resistance                                   |                                                                                                 |
| • according to IEC 60068-2-27                      | sinusoidal half-wave 15g / 11 ms                                                                |
| • for railway applications according to EN 61373   | Category 1, Class B                                                                             |
| vibration resistance                               |                                                                                                 |
| • according to IEC 60068-2-6                       | 10 ... 500 Hz: 5g                                                                               |
| • for railway applications according to EN 61373   | Category 1, Class B                                                                             |
| operating frequency maximum                        | 1 800 1/h                                                                                       |
| mechanical service life (operating cycles) typical | 1 000 000                                                                                       |
| reference code according to IEC 81346-2            | S                                                                                               |
| Substance Prohibitance (Date)                      | 10/01/2014                                                                                      |

| Safety related data                                                  |         |
|----------------------------------------------------------------------|---------|
| <b>proportion of dangerous failures</b>                              |         |
| • with low demand rate according to SN 31920                         | 20 %    |
| • with high demand rate according to SN 31920                        | 20 %    |
| <b>B10 value with high demand rate according to SN 31920</b>         | 100 000 |
| <b>failure rate [FIT] with low demand rate according to SN 31920</b> | 100 FIT |

| Ambient conditions                                             |                                                                    |
|----------------------------------------------------------------|--------------------------------------------------------------------|
| <b>ambient temperature</b>                                     |                                                                    |
| • during operation                                             | -25 ... +70 °C                                                     |
| • during storage                                               | -40 ... +80 °C                                                     |
| environmental category during operation according to IEC 60721 | 3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 ... 95%) |

| Installation/ mounting/ dimensions                 |         |
|----------------------------------------------------|---------|
| <b>height</b>                                      | 44.8 mm |
| <b>width</b>                                       | 44.8 mm |
| <b>shape of the installation opening</b>           | round   |
| <b>mounting diameter</b>                           | 22.3 mm |
| <b>positive tolerance of installation diameter</b> | 0.4 mm  |
| <b>mounting height</b>                             | 28.8 mm |
| <b>installation width</b>                          | 44.8 mm |
| <b>installation depth</b>                          | 25.4 mm |

| Approvals Certificates          |                          |
|---------------------------------|--------------------------|
| <b>General Product Approval</b> | <b>Test Certificates</b> |



[Confirmation](#)



[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)

|                          |              |
|--------------------------|--------------|
| <b>Marine / Shipping</b> | <b>other</b> |
|--------------------------|--------------|



[Confirmation](#)

#### Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1032-2CF60-0AA0-Z Y15>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1032-2CF60-0AA0-Z Y15>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1032-2CF60-0AA0-Z Y15>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SU1032-2CF60-0AA0-Z Y15&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1032-2CF60-0AA0-Z Y15&lang=en)

last modified:

1/26/2022

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[A6X30138817](#)