

Siemens  
EcoTech



key-operated switch Siemens, 22 mm, round, metal, shiny, special lock, with 2 keys, 3 switch positions I>O<II, momentary contact on the left, latching on the right, actuating angle 2x45°, 10:30h/12h/13:30h, key removal O



|                                                    |                                                                                            |
|----------------------------------------------------|--------------------------------------------------------------------------------------------|
| product brand name                                 | SIRIUS ACT                                                                                 |
| product designation                                | Key-operated switches                                                                      |
| design of the product                              | Actuating/signaling element                                                                |
| product type designation                           | 3SU1                                                                                       |
| product line                                       | Metal, shiny, 22 mm                                                                        |
| Actuator                                           |                                                                                            |
| principle of operation of the actuating element    | momentary contact/latching, 2x45° (10:30 h/12 h/13:30 h), return from left, right latching |
| product extension optional light source            | No                                                                                         |
| color                                              |                                                                                            |
| • of the actuating element                         | silver                                                                                     |
| material of the actuating element                  | metal                                                                                      |
| shape of the actuating element                     | Key                                                                                        |
| outer diameter of the actuating element            | 29.5 mm                                                                                    |
| number of switching positions                      | 3                                                                                          |
| switch position for key distraction                | O                                                                                          |
| actuating angle                                    |                                                                                            |
| • clockwise                                        | 45°                                                                                        |
| • anticlockwise                                    | 45°                                                                                        |
| lock make                                          | Siemens                                                                                    |
| Front ring                                         |                                                                                            |
| product component front ring                       | Yes                                                                                        |
| design of the front ring                           | Standard                                                                                   |
| material of the front ring                         | Metal, high gloss                                                                          |
| color of the front ring                            | silver                                                                                     |
| General technical data                             |                                                                                            |
| protection class IP                                | IP66, IP67, IP69(IP69K)                                                                    |
| • of the terminal                                  | IP20                                                                                       |
| degree of protection NEMA rating                   | 1, 2, 3, 3R, 4, 4X, 12, 13                                                                 |
| shock resistance                                   |                                                                                            |
| • according to IEC 60068-2-27                      | sinusoidal half-wave 15g / 11 ms                                                           |
| vibration resistance                               |                                                                                            |
| • according to IEC 60068-2-6                       | 10 ... 500 Hz: 5g                                                                          |
| operating frequency maximum                        | 1 800 1/h                                                                                  |
| mechanical service life (operating cycles) typical | 300 000                                                                                    |
| reference code according to IEC 81346-2            | S                                                                                          |
| Substance Prohibitance (Date)                      | 10/01/2014                                                                                 |

| Safety related data                                                  |         |
|----------------------------------------------------------------------|---------|
| <b>proportion of dangerous failures</b>                              |         |
| • with low demand rate according to SN 31920                         | 20 %    |
| • with high demand rate according to SN 31920                        | 20 %    |
| <b>B10 value with high demand rate according to SN 31920</b>         | 300 000 |
| <b>failure rate [FIT] with low demand rate according to SN 31920</b> | 100 FIT |

| Ambient conditions                                             |                                                                    |
|----------------------------------------------------------------|--------------------------------------------------------------------|
| <b>ambient temperature</b>                                     |                                                                    |
| • during operation                                             | -25 ... +70 °C                                                     |
| • during storage                                               | -40 ... +80 °C                                                     |
| environmental category during operation according to IEC 60721 | 3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 ... 95%) |

| Environmental footprint                                |                 |
|--------------------------------------------------------|-----------------|
| Environmental Product Declaration (EPD)                | Yes             |
| Global Warming Potential [CO2 eq] total                | 0.593 kg        |
| Global Warming Potential [CO2 eq] during manufacturing | 0.625 kg        |
| Global Warming Potential [CO2 eq] during operation     | 0.235 kg        |
| Global Warming Potential [CO2 eq] after end of life    | -0.267 kg       |
| Siemens Eco Profile (SEP)                              | Siemens EcoTech |

| Installation/ mounting/ dimensions                 |         |
|----------------------------------------------------|---------|
| <b>height</b>                                      | 29.5 mm |
| <b>width</b>                                       | 29.5 mm |
| <b>shape of the installation opening</b>           | round   |
| <b>mounting diameter</b>                           | 22.3 mm |
| <b>positive tolerance of installation diameter</b> | 0.4 mm  |
| <b>mounting height</b>                             | 61 mm   |
| <b>installation width</b>                          | 29.5 mm |
| <b>installation depth</b>                          | 25.4 mm |

| Approvals Certificates          |                          |
|---------------------------------|--------------------------|
| <b>General Product Approval</b> | <b>Test Certificates</b> |

[Confirmation](#)



[Type Test Certificates/Test Report](#)

|                          |                          |              |
|--------------------------|--------------------------|--------------|
| <b>Test Certificates</b> | <b>Marine / Shipping</b> | <b>other</b> |
|--------------------------|--------------------------|--------------|

[Special Test Certificate](#)



[Confirmation](#)

| Environment |
|-------------|
|-------------|



[Environmental Confirmations](#)

| Further information |
|---------------------|
|---------------------|

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1050-5BP01-0AA0-Z Y01>

Cax online generator

<http://support.automation.siemens.com/VW/CAXorder/default.aspx?lang=en&mlfb=3SU1050-5BP01-0AA0-Z Y01>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/en/ps/3SU1050-5BP01-0AA0-Z Y01>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

---

last modified:

2/7/2024 

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[A6X30139410](#)