




|                                                    |                                                                                                 |
|----------------------------------------------------|-------------------------------------------------------------------------------------------------|
| product brand name                                 | SIRIUS ACT                                                                                      |
| product designation                                | Key-operated switches                                                                           |
| design of the product                              | Actuating/signaling element                                                                     |
| product type designation                           | 3SU1                                                                                            |
| product line                                       | Metal, shiny, 22 mm                                                                             |
| manufacturer's article number of included key      | <a href="#">3SU1950-0FR80-0AA0</a>                                                              |
| Actuator                                           |                                                                                                 |
| principle of operation of the actuating element    | latching, 90° (10:30 h/13:30 h)                                                                 |
| product extension optional light source            | No                                                                                              |
| color                                              |                                                                                                 |
| • of the actuating element                         | silver                                                                                          |
| material of the actuating element                  | metal                                                                                           |
| shape of the actuating element                     | Key                                                                                             |
| outer diameter of the actuating element            | 29.5 mm                                                                                         |
| marking of the actuating element                   | Customized labeling, text in lower case / capital letters, all words start with capital letters |
| number of switching positions                      | 2                                                                                               |
| switch position for key distraction                | O                                                                                               |
| actuating angle                                    |                                                                                                 |
| • clockwise                                        | 90°                                                                                             |
| lock make                                          | ICON                                                                                            |
| key number                                         | 360012K1                                                                                        |
| Front ring                                         |                                                                                                 |
| product component front ring                       | Yes                                                                                             |
| design of the front ring                           | Standard                                                                                        |
| material of the front ring                         | Metal, high gloss                                                                               |
| color of the front ring                            | silver                                                                                          |
| General technical data                             |                                                                                                 |
| protection class IP                                | IP66, IP67, IP69(IP69K)                                                                         |
| • of the terminal                                  | IP20                                                                                            |
| degree of protection NEMA rating                   | 1, 2, 3, 3R, 4, 4X, 12, 13                                                                      |
| shock resistance                                   |                                                                                                 |
| • according to IEC 60068-2-27                      | sinusoidal half-wave 15g / 11 ms                                                                |
| vibration resistance                               |                                                                                                 |
| • according to IEC 60068-2-6                       | 10 ... 500 Hz: 5g                                                                               |
| operating frequency maximum                        | 1 800 1/h                                                                                       |
| mechanical service life (operating cycles) typical | 300 000                                                                                         |

|                                                                |                                                                    |
|----------------------------------------------------------------|--------------------------------------------------------------------|
| reference code according to IEC 81346-2                        | S                                                                  |
| Substance Prohibittance (Date)                                 | 10/01/2014                                                         |
| <b>Ambient conditions</b>                                      |                                                                    |
| ambient temperature                                            |                                                                    |
| • during operation                                             | -25 ... +70 °C                                                     |
| • during storage                                               | -40 ... +80 °C                                                     |
| environmental category during operation according to IEC 60721 | 3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 ... 95%) |
| <b>Environmental footprint</b>                                 |                                                                    |
| Environmental Product Declaration (EPD)                        | Yes                                                                |
| Global Warming Potential [CO2 eq] total                        | 0.593 kg                                                           |
| Global Warming Potential [CO2 eq] during manufacturing         | 0.625 kg                                                           |
| Global Warming Potential [CO2 eq] during operation             | 0.235 kg                                                           |
| Global Warming Potential [CO2 eq] after end of life            | -0.267 kg                                                          |
| Siemens Eco Profile (SEP)                                      | Siemens EcoTech                                                    |
| <b>Installation/ mounting/ dimensions</b>                      |                                                                    |
| height                                                         | 29.5 mm                                                            |
| width                                                          | 29.5 mm                                                            |
| shape of the installation opening                              | round                                                              |
| mounting diameter                                              | 22.3 mm                                                            |
| positive tolerance of installation diameter                    | 0.4 mm                                                             |
| mounting height                                                | 56.2 mm                                                            |
| installation width                                             | 29.5 mm                                                            |
| installation depth                                             | 25.4 mm                                                            |
| <b>Approvals Certificates</b>                                  |                                                                    |
| General Product Approval                                       |                                                                    |



[Confirmation](#)



#### Test Certificates

#### Marine / Shipping

[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)



#### other

#### Environment

[Confirmation](#)



Siemens  
EcoTech



[Environmental Confirmations](#)

#### Further information

##### Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

##### Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

##### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1050-5XF01-0AA0-Z Y15>

##### Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1050-5XF01-0AA0-Z Y15>

##### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1050-5XF01-0AA0-Z Y15>

##### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SU1050-5XF01-0AA0-Z Y15&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1050-5XF01-0AA0-Z Y15&lang=en)

last modified:

3/2/2024



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[A6X30139627](#)