



Illuminable selector switch, 22 mm, round, metal shiny, black, Selector switch long, 3 switch positions I>O<II, momentary contact on the left, latching on the right, actuating angle 2x45°, 10:30 /12 /13:30, Z=50-unit packaging

|                                                    |                                                                                            |
|----------------------------------------------------|--------------------------------------------------------------------------------------------|
| product brand name                                 | SIRIUS ACT                                                                                 |
| product designation                                | Selector switches                                                                          |
| design of the product                              | Actuating/signaling element                                                                |
| product type designation                           | 3SU1                                                                                       |
| product line                                       | Metal, shiny, 22 mm                                                                        |
| Enclosure                                          |                                                                                            |
| number of command points                           | 1                                                                                          |
| Actuator                                           |                                                                                            |
| design of the actuating element                    | selector, long                                                                             |
| principle of operation of the actuating element    | momentary contact/latching, 2x45° (10:30 h/12 h/13:30 h), return from left, right latching |
| product extension optional                         |                                                                                            |
| • light source                                     | Yes                                                                                        |
| • contact module                                   | Yes                                                                                        |
| color of the actuating element                     | black                                                                                      |
| material of the actuating element                  | plastic                                                                                    |
| shape of the actuating element                     | Handle                                                                                     |
| outer diameter of the actuating element            | 44.8 mm                                                                                    |
| number of switching positions                      | 3                                                                                          |
| actuating angle                                    |                                                                                            |
| • clockwise                                        | 45°                                                                                        |
| • anticlockwise                                    | 45°                                                                                        |
| Front ring                                         |                                                                                            |
| product component front ring                       | Yes                                                                                        |
| design of the front ring                           | standard                                                                                   |
| material of the front ring                         | Metal, high gloss                                                                          |
| color of the front ring                            | silver                                                                                     |
| General technical data                             |                                                                                            |
| protection class IP                                | IP66, IP67, IP69(IP69K)                                                                    |
| degree of protection NEMA rating                   | 1, 2, 3, 3R, 4, 4X, 12, 13                                                                 |
| shock resistance                                   |                                                                                            |
| • according to IEC 60068-2-27                      | sinusoidal half-wave 15g / 11 ms                                                           |
| vibration resistance                               |                                                                                            |
| • according to IEC 60068-2-6                       | 10 ... 500 Hz: 5g                                                                          |
| operating frequency maximum                        | 1 800 1/h                                                                                  |
| mechanical service life (operating cycles) typical | 1 000 000                                                                                  |
| reference code according to IEC 81346-2            | S                                                                                          |

|                                                               |            |
|---------------------------------------------------------------|------------|
| Substance Prohibittance (Date)                                | 03/01/2017 |
| <b>Safety related data</b>                                    |            |
| proportion of dangerous failures                              |            |
| • with low demand rate according to SN 31920                  | 20 %       |
| • with high demand rate according to SN 31920                 | 20 %       |
| B10 value with high demand rate according to SN 31920         | 300 000    |
| failure rate [FIT] with low demand rate according to SN 31920 | 100 FIT    |

|                                                                |                                                                    |
|----------------------------------------------------------------|--------------------------------------------------------------------|
| <b>Ambient conditions</b>                                      |                                                                    |
| ambient temperature                                            |                                                                    |
| • during operation                                             | -25 ... +70 °C                                                     |
| • during storage                                               | -40 ... +80 °C                                                     |
| environmental category during operation according to IEC 60721 | 3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 ... 95%) |

|                                                        |                 |
|--------------------------------------------------------|-----------------|
| <b>Environmental footprint</b>                         |                 |
| Environmental Product Declaration(EPD)                 | Yes             |
| Global Warming Potential [CO2 eq] total                | 0.593 kg        |
| Global Warming Potential [CO2 eq] during manufacturing | 0.625 kg        |
| Global Warming Potential [CO2 eq] during operation     | 0.235 kg        |
| Global Warming Potential [CO2 eq] after end of life    | -0.267 kg       |
| Siemens Eco Profile (SEP)                              | Siemens EcoTech |

|                                             |         |
|---------------------------------------------|---------|
| <b>Installation/ mounting/ dimensions</b>   |         |
| height                                      | 44.8 mm |
| width                                       | 44.8 mm |
| shape of the installation opening           | round   |
| mounting diameter                           | 22.3 mm |
| positive tolerance of installation diameter | 0.4 mm  |
| mounting height                             | 28.8 mm |
| installation width                          | 44.8 mm |
| installation depth                          | 25.4 mm |

|                               |                   |                   |  |
|-------------------------------|-------------------|-------------------|--|
| <b>Approvals Certificates</b> |                   |                   |  |
| General Product Approval      | Test Certificates | Marine / Shipping |  |



[Special Test Certificate](#)



|                   |       |             |
|-------------------|-------|-------------|
| Marine / Shipping | other | Environment |
|-------------------|-------|-------------|



[Confirmation](#)



Siemens  
EcoTech



|                            |
|----------------------------|
| <b>Further information</b> |
|----------------------------|

#### Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

#### Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

#### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1052-2CP10-0AA0-Z X90>

#### Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1052-2CP10-0AA0-Z X90>

#### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1052-2CP10-0AA0-Z X90>

#### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SU1052-2CP10-0AA0-Z X90&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1052-2CP10-0AA0-Z X90&lang=en)



---

last modified:

2/6/2024 

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[A6X30140036](#)