



Pushbutton, 30 mm, round, Metal, matte, red, front ring for flush installation, latching, Push-to-release mechanism, with laser labeling, upper case and lower case, always upper case at beginning of line

|                                                    |                                                                                                |
|----------------------------------------------------|------------------------------------------------------------------------------------------------|
| product brand name                                 | SIRIUS ACT                                                                                     |
| product designation                                | Pushbuttons                                                                                    |
| design of the product                              | Actuating/signaling element                                                                    |
| product type designation                           | 3SU1                                                                                           |
| product line                                       | Metal, matt, flat, 30 mm                                                                       |
| <b>Enclosure</b>                                   |                                                                                                |
| number of command points                           | 1                                                                                              |
| <b>Actuator</b>                                    |                                                                                                |
| design of the actuating element                    | Flat button                                                                                    |
| principle of operation of the actuating element    | latching                                                                                       |
| product extension optional                         |                                                                                                |
| • light source                                     | No                                                                                             |
| • contact module                                   | Yes                                                                                            |
| color of the actuating element                     | red                                                                                            |
| material of the actuating element                  | plastic                                                                                        |
| shape of the actuating element                     | round                                                                                          |
| outer diameter of the actuating element            | 38 mm                                                                                          |
| marking of the actuating element                   | Customized labeling, text in lower case / capital letters, all lines start with capital letter |
| type of unlocking device                           | push-to-unlatch mechanism                                                                      |
| <b>Front ring</b>                                  |                                                                                                |
| product component front ring                       | Yes                                                                                            |
| design of the front ring                           | Flat                                                                                           |
| material of the front ring                         | Metal, matt                                                                                    |
| color of the front ring                            | sand gray                                                                                      |
| <b>General technical data</b>                      |                                                                                                |
| protection class IP                                | IP66, IP67, IP69(IP69K)                                                                        |
| degree of protection NEMA rating                   | 1, 2, 3, 3R, 4, 4X, 12, 13                                                                     |
| shock resistance                                   |                                                                                                |
| • according to IEC 60068-2-27                      | sinusoidal half-wave 15g / 11 ms                                                               |
| • for railway applications according to EN 61373   | Category 1, Class B                                                                            |
| vibration resistance                               |                                                                                                |
| • according to IEC 60068-2-6                       | 10 ... 500 Hz: 5g                                                                              |
| • for railway applications according to EN 61373   | Category 1, Class B                                                                            |
| operating frequency maximum                        | 1 800 1/h                                                                                      |
| mechanical service life (operating cycles) typical | 500 000                                                                                        |
| reference code according to IEC 81346-2            | S                                                                                              |
| Substance Prohibitance (Date)                      | 10/01/2014                                                                                     |
| <b>Ambient conditions</b>                          |                                                                                                |
| ambient temperature                                |                                                                                                |

- during operation
- during storage

-25 ... +70 °C  
-40 ... +80 °C

environmental category during operation according to IEC 60721

3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 ... 95%)

#### Installation/ mounting/ dimensions

|                                             |         |
|---------------------------------------------|---------|
| height                                      | 38 mm   |
| width                                       | 38 mm   |
| shape of the installation opening           | round   |
| mounting diameter                           | 30.5 mm |
| positive tolerance of installation diameter | 0.5 mm  |
| mounting height                             | 4.2 mm  |
| installation width                          | 38 mm   |
| installation depth                          | 31.1 mm |

#### Approvals Certificates

General Product Approval

Test Certificates

Marine / Shipping



[Special Test Certificate](#)



Marine / Shipping

other



[Confirmation](#)

#### Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1060-0JA20-0AA0-Z Y10>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1060-0JA20-0AA0-Z Y10>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1060-0JA20-0AA0-Z Y10>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SU1060-0JA20-0AA0-Z Y10&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1060-0JA20-0AA0-Z Y10&lang=en)

last modified:

1/26/2022

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[A6X30140047](#)