

Illuminable selector switch, 30 mm, round, Metal matt, black, Selector switch short, front ring for flush installation, latching, actuating angle 2x45°, 10:30h/12h/13:30h, with laser labeling, upper case and lower case, always upper case at the beginning of the word

|                                                               |                                                                                                 |
|---------------------------------------------------------------|-------------------------------------------------------------------------------------------------|
| product brand name                                            | SIRIUS ACT                                                                                      |
| product designation                                           | Selector switches                                                                               |
| design of the product                                         | Actuating/signaling element                                                                     |
| product type designation                                      | 3SU1                                                                                            |
| product line                                                  | Metal, matt, flat, 30 mm                                                                        |
| <b>Enclosure</b>                                              |                                                                                                 |
| number of command points                                      | 1                                                                                               |
| <b>Actuator</b>                                               |                                                                                                 |
| design of the actuating element                               | Selector, short                                                                                 |
| principle of operation of the actuating element               | latching, 2x45° (10:30 h/12 h/13:30 h)                                                          |
| product extension optional                                    |                                                                                                 |
| • light source                                                | Yes                                                                                             |
| • contact module                                              | Yes                                                                                             |
| color of the actuating element                                | black                                                                                           |
| material of the actuating element                             | plastic                                                                                         |
| shape of the actuating element                                | Handle                                                                                          |
| outer diameter of the actuating element                       | 38 mm                                                                                           |
| marking of the actuating element                              | Customized labeling, text in lower case / capital letters, all words start with capital letters |
| number of switching positions                                 | 3                                                                                               |
| actuating angle                                               |                                                                                                 |
| • clockwise                                                   | 45°                                                                                             |
| • anticlockwise                                               | 45°                                                                                             |
| <b>Front ring</b>                                             |                                                                                                 |
| product component front ring                                  | Yes                                                                                             |
| design of the front ring                                      | Flat                                                                                            |
| material of the front ring                                    | Metal, matt                                                                                     |
| color of the front ring                                       | sand gray                                                                                       |
| <b>General technical data</b>                                 |                                                                                                 |
| protection class IP                                           | IP66, IP67, IP69(IP69K)                                                                         |
| degree of protection NEMA rating                              | 1, 2, 3, 3R, 4, 4X, 12, 13                                                                      |
| shock resistance                                              |                                                                                                 |
| • according to IEC 60068-2-27                                 | sinusoidal half-wave 15g / 11 ms                                                                |
| • for railway applications according to EN 61373              | Category 1, Class B                                                                             |
| vibration resistance                                          |                                                                                                 |
| • according to IEC 60068-2-6                                  | 10 ... 500 Hz: 5g                                                                               |
| • for railway applications according to EN 61373              | Category 1, Class B                                                                             |
| operating frequency maximum                                   | 1 800 1/h                                                                                       |
| mechanical service life (operating cycles) typical            | 300 000                                                                                         |
| reference code according to IEC 81346-2                       | S                                                                                               |
| Substance Prohibitance (Date)                                 | 03/01/2017                                                                                      |
| <b>Safety related data</b>                                    |                                                                                                 |
| proportion of dangerous failures                              |                                                                                                 |
| • with low demand rate according to SN 31920                  | 20 %                                                                                            |
| • with high demand rate according to SN 31920                 | 20 %                                                                                            |
| B10 value with high demand rate according to SN 31920         | 300 000                                                                                         |
| failure rate [FIT] with low demand rate according to SN 31920 | 100 FIT                                                                                         |
| <b>Ambient conditions</b>                                     |                                                                                                 |
| ambient temperature                                           |                                                                                                 |

- during operation
- during storage

-25 ... +70 °C

-40 ... +80 °C

environmental category during operation according to IEC 60721

3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 ... 95%)

#### Installation/ mounting/ dimensions

|                                             |         |
|---------------------------------------------|---------|
| height                                      | 44.8 mm |
| width                                       | 38 mm   |
| shape of the installation opening           | round   |
| mounting diameter                           | 30.5 mm |
| positive tolerance of installation diameter | 0.5 mm  |
| mounting height                             | 22.1 mm |
| installation width                          | 38 mm   |
| installation depth                          | 32.1 mm |

#### Approvals Certificates

##### General Product Approval



[Confirmation](#)



#### Test Certificates

#### Marine / Shipping

[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)



#### other

#### Environment

[Confirmation](#)

[Environmental Confirmations](#)

#### Further information

##### Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

##### Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

##### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1062-2DL10-0AA0-Z Y15>

##### Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1062-2DL10-0AA0-Z Y15>

##### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1062-2DL10-0AA0-Z Y15>

##### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SU1062-2DL10-0AA0-Z Y15&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1062-2DL10-0AA0-Z Y15&lang=en)

last modified:

1/26/2022

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[A6X30140252](#)