



Pushbutton, 22 mm, round, plastic with metal front ring, white, pushbutton, flat, momentary contact type, with holder, 1 NO+1 NC, spring-type terminal, with laser labeling, inscription or symbol Customer-specific selection with SIRIUS ACT configurator (CIN)

|                                                 |                                                                                                                                 |
|-------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| product brand name                              | SIRIUS ACT                                                                                                                      |
| product designation                             | Pushbuttons                                                                                                                     |
| design of the product                           | Complete unit                                                                                                                   |
| product type designation                        | 3SU1                                                                                                                            |
| product line                                    | Plastic with metal front ring, matt, 22 mm                                                                                      |
| manufacturer's article number                   |                                                                                                                                 |
| • of supplied contact module at position 1      | <a href="#">3SU1400-1AA10-3FA0</a>                                                                                              |
| • of the supplied holder                        | <a href="#">3SU1550-0AA10-0AA0</a>                                                                                              |
| • of the supplied actuator                      | <a href="#">3SU1030-0AB60-0AA0</a>                                                                                              |
| number of command points                        | 1                                                                                                                               |
| Actuator                                        |                                                                                                                                 |
| design of the actuating element                 | Button, flat                                                                                                                    |
| principle of operation of the actuating element | momentary contact type                                                                                                          |
| product extension optional light source         | No                                                                                                                              |
| color of the actuating element                  | white                                                                                                                           |
| material of the actuating element               | plastic                                                                                                                         |
| shape of the actuating element                  | round                                                                                                                           |
| outer diameter of the actuating element         | 29.45 mm                                                                                                                        |
| marking of the actuating element                | Customized labeling, text or symbols, can only be ordered via SIRIUS ACT configurator/Configuration Identification Number (CIN) |
| number of contact modules                       | 1                                                                                                                               |
| Front ring                                      |                                                                                                                                 |
| product component front ring                    | Yes                                                                                                                             |
| design of the front ring                        | Standard                                                                                                                        |
| material of the front ring                      | Metal, matt                                                                                                                     |
| color of the front ring                         | sand gray                                                                                                                       |
| Holder                                          |                                                                                                                                 |
| material of the holder                          | Plastic                                                                                                                         |
| Display                                         |                                                                                                                                 |
| number of LED modules                           | 0                                                                                                                               |
| General technical data                          |                                                                                                                                 |
| product function positive opening               | Yes                                                                                                                             |
| product component light source                  | No                                                                                                                              |
| insulation voltage rated value                  | 500 V                                                                                                                           |
| degree of pollution                             | 3                                                                                                                               |
| type of voltage of the operating voltage        | AC/DC                                                                                                                           |
| surge voltage resistance rated value            | 6 kV                                                                                                                            |
| protection class IP                             | IP66, IP67, IP69(IP69K)                                                                                                         |
| • of the terminal                               | IP20                                                                                                                            |
| degree of protection NEMA rating                | 1, 2, 3, 3R, 4, 4X, 12, 13                                                                                                      |

|                                                                                                                                                                                                                            |                                                                                                                                               |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------|
| <b>shock resistance</b>                                                                                                                                                                                                    |                                                                                                                                               |
| <ul style="list-style-type: none"> <li>• according to IEC 60068-2-27</li> <li>• for railway applications according to EN 61373</li> </ul>                                                                                  | sinusoidal half-wave 15g / 11 ms<br>Category 1, Class B                                                                                       |
| <b>vibration resistance</b>                                                                                                                                                                                                |                                                                                                                                               |
| <ul style="list-style-type: none"> <li>• according to IEC 60068-2-6</li> <li>• for railway applications according to EN 61373</li> </ul>                                                                                   | 10 ... 500 Hz: 5g<br>Category 1, Class B                                                                                                      |
| <b>operating frequency maximum</b>                                                                                                                                                                                         | 3 600 1/h                                                                                                                                     |
| <b>mechanical service life (operating cycles) typical</b>                                                                                                                                                                  | 10 000 000                                                                                                                                    |
| <b>electrical endurance (operating cycles) typical</b>                                                                                                                                                                     | 10 000 000                                                                                                                                    |
| <b>thermal current</b>                                                                                                                                                                                                     | 10 A                                                                                                                                          |
| <b>reference code according to IEC 81346-2</b>                                                                                                                                                                             | S                                                                                                                                             |
| <b>continuous current of the C characteristic MCB</b>                                                                                                                                                                      | 10 A; for a short-circuit current smaller than 400 A                                                                                          |
| <b>continuous current of the quick DIAZED fuse link</b>                                                                                                                                                                    | 10 A                                                                                                                                          |
| <b>continuous current of the DIAZED fuse link gG</b>                                                                                                                                                                       | 10 A                                                                                                                                          |
| <b>Substance Prohibitance (Date)</b>                                                                                                                                                                                       | 10/01/2014                                                                                                                                    |
| <b>operating voltage</b>                                                                                                                                                                                                   |                                                                                                                                               |
| <ul style="list-style-type: none"> <li>• at AC <ul style="list-style-type: none"> <li>— at 50 Hz rated value</li> <li>— at 60 Hz rated value</li> </ul> </li> <li>• at DC rated value</li> </ul>                           | 5 ... 500 V<br>5 ... 500 V<br>5 ... 500 V                                                                                                     |
| <b>Power Electronics</b>                                                                                                                                                                                                   |                                                                                                                                               |
| <b>contact reliability</b>                                                                                                                                                                                                 | One maloperation per 100 million (17 V, 5 mA), one maloperation per 10 million (5 V, 1 mA)                                                    |
| <b>Auxiliary circuit</b>                                                                                                                                                                                                   |                                                                                                                                               |
| <b>design of the contact of auxiliary contacts</b>                                                                                                                                                                         | Silver alloy                                                                                                                                  |
| <b>number of NC contacts for auxiliary contacts</b>                                                                                                                                                                        | 1                                                                                                                                             |
| <b>number of NO contacts for auxiliary contacts</b>                                                                                                                                                                        | 1                                                                                                                                             |
| <b>Connections/ Terminals</b>                                                                                                                                                                                              |                                                                                                                                               |
| <b>type of electrical connection</b>                                                                                                                                                                                       | spring-loaded terminals                                                                                                                       |
| <ul style="list-style-type: none"> <li>• of modules and accessories</li> </ul>                                                                                                                                             | Spring-type terminal                                                                                                                          |
| <b>type of connectable conductor cross-sections</b>                                                                                                                                                                        |                                                                                                                                               |
| <ul style="list-style-type: none"> <li>• solid without core end processing</li> <li>• finely stranded with core end processing</li> <li>• finely stranded without core end processing</li> <li>• for AWG cables</li> </ul> | 2x (0.25 ... 1.5 mm <sup>2</sup> )<br>2x (0.25 ... 0.75 mm <sup>2</sup> )<br>2x (0.25 ... 1.5 mm <sup>2</sup> )<br>2x (24 ... 16)             |
| <b>tightening torque of the screws in the bracket</b>                                                                                                                                                                      | 1 ... 1.2 N·m                                                                                                                                 |
| <b>Ambient conditions</b>                                                                                                                                                                                                  |                                                                                                                                               |
| <b>ambient temperature</b>                                                                                                                                                                                                 |                                                                                                                                               |
| <ul style="list-style-type: none"> <li>• during operation</li> <li>• during storage</li> </ul>                                                                                                                             | -25 ... +70 °C<br>-40 ... +80 °C                                                                                                              |
| environmental category during operation according to IEC 60721                                                                                                                                                             | 3M6, 3S2, 3B2, 3C3, 3K6 (with relative air humidity of 10 ... 95%, no condensation in operation permitted for all devices behind front panel) |
| <b>Installation/ mounting/ dimensions</b>                                                                                                                                                                                  |                                                                                                                                               |
| <b>fastening method</b>                                                                                                                                                                                                    | front plate mounting                                                                                                                          |
| <ul style="list-style-type: none"> <li>• of modules and accessories</li> </ul>                                                                                                                                             | Front plate mounting                                                                                                                          |
| <b>height</b>                                                                                                                                                                                                              | 40 mm                                                                                                                                         |
| <b>width</b>                                                                                                                                                                                                               | 30 mm                                                                                                                                         |
| <b>shape of the installation opening</b>                                                                                                                                                                                   | round                                                                                                                                         |
| <b>mounting diameter</b>                                                                                                                                                                                                   | 22.3 mm                                                                                                                                       |
| <b>positive tolerance of installation diameter</b>                                                                                                                                                                         | 0.4 mm                                                                                                                                        |
| <b>mounting height</b>                                                                                                                                                                                                     | 11 mm                                                                                                                                         |
| <b>installation width</b>                                                                                                                                                                                                  | 29.5 mm                                                                                                                                       |
| <b>installation depth</b>                                                                                                                                                                                                  | 71.7 mm                                                                                                                                       |
| <b>Approvals Certificates</b>                                                                                                                                                                                              |                                                                                                                                               |
| <div> <div>General Product Approval</div> <div>Test Certificates</div> </div>                                                                                                                                              |                                                                                                                                               |



[Confirmation](#)



[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)

[Confirmation](#)

#### Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1130-0AB60-3FA0-Z Y19>

Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1130-0AB60-3FA0-Z Y19>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1130-0AB60-3FA0-Z Y19>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SU1130-0AB60-3FA0-Z Y19&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1130-0AB60-3FA0-Z Y19&lang=en)



last modified:

3/2/2024

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[A6X30142476](#)