




|                                                 |                                                 |
|-------------------------------------------------|-------------------------------------------------|
| product brand name                              | SIRIUS ACT                                      |
| product designation                             | Illuminated pushbuttons                         |
| design of the product                           | Complete unit                                   |
| product type designation                        | 3SU1                                            |
| product line                                    | Plastic, black, 22 mm                           |
| manufacturer's article number                   |                                                 |
| • of supplied contact module at position 1      | <a href="#">3SU1400-1AA10-3BA0</a>              |
| • of supplied LED module                        | <a href="#">3SU1401-1BC60-3AA0</a>              |
| • of the supplied holder                        | <a href="#">3SU1550-0AA10-0AA0</a>              |
| • of the supplied actuator                      | <a href="#">3SU1001-0AB60-0AA0</a>              |
| number of command points                        | 1                                               |
| Actuator                                        |                                                 |
| design of the actuating element                 | Button, flat                                    |
| principle of operation of the actuating element | momentary contact type                          |
| product extension optional light source         | Yes                                             |
| color of the actuating element                  | white                                           |
| material of the actuating element               | plastic                                         |
| shape of the actuating element                  | round                                           |
| outer diameter of the actuating element         | 29.45 mm                                        |
| marking of the actuating element                | Customized labeling, text in lower case letters |
| number of contact modules                       | 1                                               |
| Front ring                                      |                                                 |
| product component front ring                    | Yes                                             |
| design of the front ring                        | Standard                                        |
| material of the front ring                      | plastic                                         |
| color of the front ring                         | black                                           |
| Holder                                          |                                                 |
| material of the holder                          | Plastic                                         |
| Display                                         |                                                 |
| number of LED modules                           | 1                                               |
| General technical data                          |                                                 |
| product function positive opening               | No                                              |
| product component light source                  | Yes                                             |
| insulation voltage rated value                  | 320 V                                           |
| degree of pollution                             | 3                                               |
| type of voltage of the operating voltage        | AC/DC                                           |
| surge voltage resistance rated value            | 4 kV                                            |

|                                                                                                                                                                                                               |                                                                                                                                          |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------|
| <b>protection class IP</b><br>• of the terminal                                                                                                                                                               | IP66, IP67, IP69(IP69K)<br>IP20                                                                                                          |
| <b>degree of protection NEMA rating</b>                                                                                                                                                                       | 1, 2, 3, 3R, 4, 4X, 12, 13                                                                                                               |
| <b>shock resistance</b><br>• according to IEC 60068-2-27<br>• for railway applications according to EN 61373                                                                                                  | sinusoidal half-wave 15g / 11 ms<br>Category 1, Class B                                                                                  |
| <b>vibration resistance</b><br>• according to IEC 60068-2-6<br>• for railway applications according to EN 61373                                                                                               | 10 ... 500 Hz: 5g<br>Category 1, Class B                                                                                                 |
| <b>operating frequency maximum</b>                                                                                                                                                                            | 3 600 1/h                                                                                                                                |
| <b>mechanical service life (operating cycles) typical</b>                                                                                                                                                     | 3 000 000                                                                                                                                |
| <b>electrical endurance (operating cycles) typical</b>                                                                                                                                                        | 10 000 000                                                                                                                               |
| <b>thermal current</b>                                                                                                                                                                                        | 10 A                                                                                                                                     |
| <b>reference code according to IEC 81346-2</b>                                                                                                                                                                | S                                                                                                                                        |
| <b>continuous current of the C characteristic MCB</b>                                                                                                                                                         | 10 A; for a short-circuit current smaller than 400 A                                                                                     |
| <b>continuous current of the quick DIAZED fuse link</b>                                                                                                                                                       | 10 A                                                                                                                                     |
| <b>continuous current of the DIAZED fuse link gG</b>                                                                                                                                                          | 10 A                                                                                                                                     |
| <b>Substance Prohibitance (Date)</b>                                                                                                                                                                          | 10/01/2014                                                                                                                               |
| <b>operating voltage</b><br>• at AC<br>— at 50 Hz rated value<br>— at 60 Hz rated value<br>• at DC rated value                                                                                                | 5 ... 500 V<br>5 ... 500 V<br>5 ... 500 V                                                                                                |
| <b>Power Electronics</b>                                                                                                                                                                                      |                                                                                                                                          |
| <b>contact reliability</b>                                                                                                                                                                                    | One maloperation per 100 million (17 V, 5 mA), one maloperation per 10 million (5 V, 1 mA)                                               |
| <b>Supply voltage</b>                                                                                                                                                                                         |                                                                                                                                          |
| <b>type of voltage of the supply voltage of the light source</b>                                                                                                                                              | AC                                                                                                                                       |
| <b>supply voltage of the light source at AC</b><br>• at 50 Hz rated value<br>• at 60 Hz rated value                                                                                                           | 110 V<br>110 V                                                                                                                           |
| <b>Control circuit/ Control</b>                                                                                                                                                                               |                                                                                                                                          |
| <b>inrush current of LED module maximum</b>                                                                                                                                                                   | 3 A                                                                                                                                      |
| <b>Auxiliary circuit</b>                                                                                                                                                                                      |                                                                                                                                          |
| <b>design of the contact of auxiliary contacts</b>                                                                                                                                                            | Silver alloy                                                                                                                             |
| <b>number of NC contacts for auxiliary contacts</b>                                                                                                                                                           | 0                                                                                                                                        |
| <b>number of NO contacts for auxiliary contacts</b>                                                                                                                                                           | 1                                                                                                                                        |
| <b>Connections/ Terminals</b>                                                                                                                                                                                 |                                                                                                                                          |
| <b>type of electrical connection</b><br>• of modules and accessories                                                                                                                                          | spring-loaded terminals<br>Spring-type terminal                                                                                          |
| <b>type of connectable conductor cross-sections</b><br>• solid without core end processing<br>• finely stranded with core end processing<br>• finely stranded without core end processing<br>• for AWG cables | 2x (0.25 ... 1.5 mm <sup>2</sup> )<br>2x (0.25 ... 0.75 mm <sup>2</sup> )<br>2x (0.25 ... 1.5 mm <sup>2</sup> )<br>2x (24 ... 16)        |
| <b>tightening torque of the screws in the bracket</b>                                                                                                                                                         | 1 ... 1.2 N·m                                                                                                                            |
| <b>Lamp</b>                                                                                                                                                                                                   |                                                                                                                                          |
| <b>type of light source</b>                                                                                                                                                                                   | LED                                                                                                                                      |
| <b>color of the light source</b>                                                                                                                                                                              | white                                                                                                                                    |
| <b>light intensity</b>                                                                                                                                                                                        | 900 ... 1 400 mcd                                                                                                                        |
| <b>Ambient conditions</b>                                                                                                                                                                                     |                                                                                                                                          |
| <b>ambient temperature</b><br>• during operation<br>• during storage                                                                                                                                          | -25 ... +70 °C<br>-40 ... +80 °C                                                                                                         |
| <b>environmental category during operation according to IEC 60721</b>                                                                                                                                         | 3M6, 3S2, 3B2, 3K6 (with relative air humidity of 10 ... 95%, no condensation in operation permitted for all devices behind front panel) |
| <b>Environmental footprint</b>                                                                                                                                                                                |                                                                                                                                          |
| <b>Environmental Product Declaration(EPD)</b>                                                                                                                                                                 | Yes                                                                                                                                      |
| <b>Global Warming Potential [CO2 eq] total</b>                                                                                                                                                                | 0.787 kg                                                                                                                                 |
| <b>Global Warming Potential [CO2 eq] during manufacturing</b>                                                                                                                                                 | 0.566 kg                                                                                                                                 |
| <b>Global Warming Potential [CO2 eq] during operation</b>                                                                                                                                                     | 0.235 kg                                                                                                                                 |

|                                                     |                      |
|-----------------------------------------------------|----------------------|
| Global Warming Potential [CO2 eq] after end of life | -0.015 kg            |
| Siemens Eco Profile (SEP)                           | Siemens EcoTech      |
| <b>Installation/ mounting/ dimensions</b>           |                      |
| <b>fastening method</b>                             | front plate mounting |
| • of modules and accessories                        | Front plate mounting |
| <b>height</b>                                       | 40 mm                |
| <b>width</b>                                        | 30 mm                |
| <b>shape of the installation opening</b>            | round                |
| <b>mounting diameter</b>                            | 22.3 mm              |
| <b>positive tolerance of installation diameter</b>  | 0.4 mm               |
| <b>mounting height</b>                              | 11 mm                |
| <b>installation width</b>                           | 29.5 mm              |
| <b>installation depth</b>                           | 49.7 mm              |

#### Approvals Certificates

##### General Product Approval



[Confirmation](#)



##### Test Certificates

##### Marine / Shipping

[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)



##### other

##### Environment

[Confirmation](#)



Siemens  
EcoTech



#### Further information

##### Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

##### Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

##### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1103-0AB60-3BA0-Z Y12>

##### Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1103-0AB60-3BA0-Z Y12>

##### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1103-0AB60-3BA0-Z Y12>

##### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SU1103-0AB60-3BA0-Z Y12&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1103-0AB60-3BA0-Z Y12&lang=en)



last modified:

2/7/2024 

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[A6X30142087](#)