



holder, 3-way, metal, 1 NO, 1 NC, LED module, blue, 24 V AC/DC, spring-loaded terminal

product brand name	SIRIUS ACT
product designation	Holders
design of the product	holder for metal
product type designation	3SU1
manufacturer's article number	
• of supplied contact module	3SU1400-1AA10-3BA0, 3SU1400-1AA10-3CA0
• of supplied contact module at position 1	<a href="#">3SU1400-1AA10-3BA0</a>
• of supplied contact module at position 2	<a href="#">3SU1400-1AA10-3CA0</a>
• of supplied LED module	<a href="#">3SU1401-1BG50-3AA0</a>
• of the supplied holder	<a href="#">3SU1510-0AA10-0AA0</a>
<b>Actuator</b>	
design of the actuating element	3-way with module
number of contact modules	2
<b>Holder</b>	
material of the holder	Metal
<b>Display</b>	
number of LED modules	1
<b>General technical data</b>	
product function positive opening	Yes
product component	
• diode	Yes
• lamp transformer	No
• light source	Yes
• series resistor	No
insulation voltage rated value	320 V
degree of pollution	3
surge voltage resistance rated value	4 kV
protection class IP of the terminal	IP20
shock resistance	
• according to IEC 60068-2-27	sinusoidal half-wave 15g / 11 ms
• for railway applications according to EN 61373	Category 1, Class B
vibration resistance	
• according to IEC 60068-2-6	10 ... 500 Hz: 5g
• for railway applications according to EN 61373	Category 1, Class B
operating frequency maximum	3 600 1/h
mechanical service life (operating cycles) typical	10 000 000
thermal current	10 A
reference code according to IEC 81346-2	U
continuous current of the C characteristic MCB	10 A; for a short-circuit current smaller than 400 A
continuous current of the quick DIAZED fuse link	10 A

continuous current of the DIAZED fuse link gG		10 A	
Substance Prohibittance (Date)		10/01/2014	
operating voltage <ul style="list-style-type: none"><li>at AC<ul style="list-style-type: none"><li>at 50 Hz rated value</li><li>at 60 Hz rated value</li></ul></li><li>at DC rated value</li></ul>		24 ... 24 V 24 ... 24 V 24 ... 24 V	
Power Electronics			
contact reliability		One maloperation per 100 million (17 V, 5 mA), one maloperation per 10 million (5 V, 1 mA)	
Control circuit/ Control			
inrush current of LED module maximum		2 A	
Auxiliary circuit			
design of the contact of auxiliary contacts		Silver alloy	
number of NC contacts for auxiliary contacts		1	
number of NO contacts for auxiliary contacts		1	
operational current at AC-15 at 230 V rated value		6 A	
Connections/ Terminals			
type of electrical connection <ul style="list-style-type: none"><li>of modules and accessories</li></ul>		Spring-type terminal	
type of connectable conductor cross-sections <ul style="list-style-type: none"><li>solid without core end processing</li><li>finely stranded with core end processing</li><li>finely stranded without core end processing</li><li>for AWG cables</li></ul>		2x (0.25 ... 1.5 mm²) 2x (0.25 ... 0.75 mm²) 2x (0.25 ... 1.5 mm²) 2x (24 ... 16)	
tightening torque of the screws in the bracket		1 ... 1.2 N·m	
tightening torque <ul style="list-style-type: none"><li>for grounding</li></ul>		0.8 ... 1 N·m	
Lamp			
type of light source		LED	
color of the light source		blue	
Ambient conditions			
ambient temperature <ul style="list-style-type: none"><li>during operation</li><li>during storage</li></ul>		-25 ... +70 °C -40 ... +80 °C	
environmental category during operation according to IEC 60721		3M6, 3S2, 3B2, 3K6 (with relative air humidity of 10 ... 95%, no condensation in operation permitted)	
Installation/ mounting/ dimensions			
fastening method <ul style="list-style-type: none"><li>of modules and accessories</li></ul>		front plate mounting Front plate mounting	
height		40 mm	
width		30 mm	
shape of the installation opening		round	
installation width		30 mm	
installation depth		49.8 mm	
thickness of the front plate usable		1 ... 6 mm	
Certificates/ approvals			
General Product Approval		Declaration of Conformity	Test Certificates
			other

[Confirmation](#)



[Type Test Certificates/Test Report](#)

[Confirmation](#)

#### Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SU1511-1AB50-3MA0>

Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SU1511-1AB50-3MA0>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3SU1511-1AB50-3MA0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3SU1511-1AB50-3MA0&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SU1511-1AB50-3MA0&lang=en)





last modified:

6/25/2022

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[3SU15111AB503MA0](#)