

Operator panel with display for SIMOCODE pro V, installation in control cabinet door or front plate; can be plugged onto basic unit or extension modules, 7 LEDs for status display and 4 freely assignable keys for manual control, Languages en/cn/ru/ko Color: titanium gray



product brand name	SIRIUS
product designation	operating module with display
General technical data	
consumed active power	0.3 W
insulation voltage	
• rated value	300 V
surge voltage resistance rated value	4 000 V
protection class IP on the front	IP54
vibration resistance	1-6 Hz / 15 mm; 6-500 Hz / 2 g
reference code according to IEC 81346-2	A
Substance Prohibitation (Date)	07/01/2006
Electromagnetic compatibility	
EMC emitted interference according to IEC 60947-1	class A
EMC immunity according to IEC 60947-1	corresponds to degree of severity 3
conducted interference	
• due to burst according to IEC 61000-4-4	1 kV
• due to conductor-earth surge according to IEC 61000-4-5	2 kV
• due to conductor-conductor surge according to IEC 61000-4-5	1 kV
field-based interference according to IEC 61000-4-3	10 V/m
Installation/ mounting/ dimensions	
mounting position	vertical
fastening method	front plate mounting
height	60 mm
width	96 mm
depth	44 mm
Ambient conditions	
installation altitude at height above sea level	
• maximum	4 000 m
• 1 maximum	2 000 m
• 2 maximum	3 000 m; max. +50 °C (no protective separation)
• 3 maximum	4 000 m; max. +40 °C (no protective separation)
ambient temperature	
• during operation	0 ... 60 °C
• during storage	-20 ... +70 °C
• during transport	-20 ... +70 °C
environmental category	
• during operation according to IEC 60721	3K6 (no formation of ice, no condensation, relative humidity 10 ... 95%), 3C3 (no salt mist), 3S2 (sand must not get into the devices), 3M6
• during storage according to IEC 60721	1K6 (no condensation, relative humidity 10 ... 95%), 1C2 (no salt mist), 1S2 (sand must not get into the devices), 1M4

Certificates/ approvals

General Product Approval	EMC	Declaration of Con- formity
--------------------------	-----	--------------------------------



[Confirmation](#)



Declaration of Con- formity	Test Certificates	Marine / Shipping	other
--------------------------------	-------------------	-------------------	-------



EG-Konf.

[Type Test Certificates/Test Report](#)



ABS



RMRS



DNV-GL

[Confirmation](#)

other



Profibus

Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3UF7210-1BA01-0>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3UF7210-1BA01-0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)



<https://support.industry.siemens.com/cs/ww/en/ps/3UF7210-1BA01-0>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3UF7210-1BA01-0&lang=en


Test report No. A0258, protective separation

<https://support.industry.siemens.com/cs/ww/en/view/109748152>



-A

SIEMENS



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[3UF72101BA010](#)