


















Fail-safe digital module DM-F PROFIsafe, for fail-safe shutdown via bus/PROFIsafe, Us: 110...240 V AC/DC, 2 relay enabling circuits, 2 relay outputs, 3 inputs, maximum achievable SIL IEC 61508: 3, maximum achievable PL ISO 13849-1: E

product brand name	SIRIUS
product designation	Fail-safe digital module
design of the product	for fail-safe shutdown
product type designation	DM-FP
<b>General technical data</b>	
product function	
• EMERGENCY OFF function	No
• automatic start	No
• light barrier monitoring	No
• light array monitoring	No
• protective door monitoring	No
• magnetically operated switch monitoring NC-NO	No
• magnetically operated switch monitoring NC-NC	No
• pressure-sensitive mat monitoring	No
• monitored start-up	No
product feature cross-circuit-proof	Yes
product component	
• input for thermistor connection	No
• digital input	Yes
• input for analog temperature sensors	No
• input for ground fault detection	No
• relay output	Yes
apparent power consumption	11 VA
consumed active power	5.5 W
insulation voltage with degree of pollution 3 at AC rated value	300 V
surge voltage resistance rated value	4 000 V
protection class IP	IP20
shock resistance according to IEC 60068-2-27	15g / 11 ms
vibration resistance according to IEC 60068-2-6	1 ... 6 Hz: 15 mm, 6 ... 500 Hz: 2g
operating frequency maximum	360 1/y
switching capacity current of the NO contacts of the relay outputs at AC-15	
• at 24 V	3 A
• at 120 V	3 A
• at 240 V	1.5 A
switching capacity current of the NO contacts of the relay outputs at DC-13	
• at 24 V	4 A
• at 60 V	0.55 A
• at 125 V	0.22 A
• at 250 V	0.11 A

<b>switching capacity current of relay enabling circuits at AC-15</b>	
• at 24 V	3 A
• at 120 V	3 A
• at 240 V	1.5 A
<b>switching capacity current of relay enabling circuits at DC-13</b>	
• at 24 V	4 A
• at 60 V	0.55 A
• at 125 V	0.22 A
• at 250 V	0.11 A
<b>mechanical service life (operating cycles) typical</b>	10 000 000
<b>electrical endurance (operating cycles) typical</b>	100 000
<b>buffering time in the event of power failure</b>	200 ms
<b>backslide delay time in the event of power failure</b>	
• typical	220 ms
• maximum	320 ms
<b>reference code according to IEC 81346-2</b>	F
<b>reference code according to IEC 81346-2:2019</b>	F
<b>type of input characteristic</b>	Type 2 in accordance with EN 61131-2
<b>Substance Prohibittance (Date)</b>	05/01/2012
certificate of suitability according to ATEX directive 2014/34/EU	BVS 06 ATEX F001
explosion device group and category according to ATEX directive 2014/34/EU	II (2) G, II (2) D, I (M2)
<b>Electromagnetic compatibility</b>	
EMC emitted interference according to IEC 60947-1	class A
EMC immunity according to IEC 60947-1	corresponds to degree of severity 3
<b>conducted interference</b>	
• due to burst according to IEC 61000-4-4	2 kV network connection / 1 kV control connection
• due to conductor-earth surge according to IEC 61000-4-5	2 kV
• due to conductor-conductor surge according to IEC 61000-4-5	1 kV
• due to high-frequency radiation according to IEC 61000-4-6	10 V
<b>field-based interference according to IEC 61000-4-3</b>	10 V/m
<b>electrostatic discharge according to IEC 61000-4-2</b>	6 kV contact discharge / 8 kV air discharge
<b>conducted HF interference emissions according to CISPR11</b>	corresponds to degree of severity A
<b>field-bound HF interference emission according to CISPR11</b>	corresponds to degree of severity A
<b>Inputs/ Outputs</b>	
<b>product function</b>	
• parameterizable inputs	Yes
• parameterizable outputs	Yes
<b>number of inputs</b>	4
<b>input version with safety-related function</b>	3 sensor inputs 24 V DC, 1 feedback circuit input
<b>design of input</b>	
• feedback input	Yes
<b>number of digital inputs</b>	3
• with a common reference potential	4
<b>digital input version</b>	
• type 1 acc. to IEC 61131	No
• type 2 acc. to IEC 61131	Yes
<b>number of analog inputs</b>	0
<b>number of outputs</b>	2
<b>number of semiconductor outputs</b>	0
<b>number of outputs</b>	
• as contact-affected switching element	2
• as contact-affected switching element as NO contact safety-related instantaneous contact	2
<b>number of analog outputs</b>	0
<b>switching behavior</b>	monostable
<b>property of contacts of the relay outputs</b>	Fail-safe NO contacts
<b>wire length for digital signals maximum</b>	300 m

Product Function	
<b>suitability for use</b>	
• position switch monitoring	No
• EMERGENCY-OFF circuit monitoring	No
• valve monitoring	No
• opto-electronic protection device monitoring	No
• tactile sensor monitoring	No
• magnetically operated switch monitoring	No
• proximity switch monitoring	No
• safety switch	No
• safety-related circuits	No
Communication/ Protocol	
protocol is supported PROFIsafe protocol	Yes
Installation/ mounting/ dimensions	
<b>mounting position</b>	any
<b>fastening method</b>	screw and snap-on mounting
<b>height</b>	106 mm
<b>width</b>	45 mm
<b>depth</b>	124 mm
<b>required spacing</b>	
• top	40 mm
• bottom	40 mm
• left	0 mm
• right	0 mm
Connections/ Terminals	
<b>product component removable terminal for auxiliary and control circuit</b>	Yes
<b>type of connectable conductor cross-sections</b>	
• solid	1x (0.5 ... 4.0 mm <sup>2</sup> ), 2x (0.5 ... 2.5 mm <sup>2</sup> )
• finely stranded with core end processing	1x (0.5 ... 2.5 mm <sup>2</sup> ), 2x (0.5 ... 1.5 mm <sup>2</sup> )
• for AWG cables solid	1x (20 ... 12), 2x (20 ... 14)
• for AWG cables stranded	1x (20 ... 14), 2x (20 ... 16)
tightening torque with screw-type terminals	0.8 ... 1.2 N·m
tightening torque [lbf·in] with screw-type terminals	7 ... 10.3 lbf·in
Ambient conditions	
<b>installation altitude at height above sea level</b>	
• 1 maximum	2 000 m
• 2 maximum	3 000 m; max. +50 °C (no protective separation)
• 3 maximum	4 000 m; max. +40 °C (no protective separation)
<b>ambient temperature</b>	
• during operation	-25 ... +60 °C
• during storage	-40 ... +80 °C
• during transport	-40 ... +80 °C
<b>environmental category</b>	
• during operation according to IEC 60721	3K6 (no formation of ice, no condensation, relative humidity 10 ... 95%), 3C3 (no salt mist), 3S2 (sand must not get into the devices), 3M6
• during storage according to IEC 60721	1K6 (no condensation, relative humidity 10 ... 95%), 1C2 (no salt mist), 1S2 (sand must not get into the devices), 1M4
• during transport according to IEC 60721	2K2, 2C1, 2S1, 2M2
relative humidity during operation	5 ... 95 %
<b>contact rating of auxiliary contacts according to UL</b>	B300 / R300
Short-circuit protection	
design of the fuse link for short-circuit protection of relay enabling circuits required	gL/gG: 4 A
Safety related data	
<b>safety device type according to IEC 61508-2</b>	Type B
<b>Safety Integrity Level (SIL)</b>	
• according to IEC 61508	3
<b>SIL Claim Limit (subsystem)</b>	
• according to EN 62061	3
<b>performance level (PL)</b>	

<ul style="list-style-type: none"><li>• according to EN ISO 13849-1</li></ul>	e						
<b>category</b>							
<ul style="list-style-type: none"><li>• according to EN ISO 13849-1</li></ul>	4						
<b>stop category according to EN 60204-1</b>	0						
<b>average diagnostic coverage level (DCavg)</b>	99 %						
<b>failure rate [FIT]</b>							
<ul style="list-style-type: none"><li>• at rate of recognizable hazardous failures (<math>\lambda_{dd}</math>)</li></ul>	909 FIT						
<ul style="list-style-type: none"><li>• at rate of non-recognizable hazardous failures (<math>\lambda_{du}</math>)</li></ul>	7 FIT						
<b>safe state</b>	Safety outputs switched off						
<b>touch protection against electrical shock</b>	finger-safe						
<b>contact reliability</b>	0.1 million operating cycles (AC15, 230 V, 2 A)						
<b>Response times/ Monitoring times</b>							
<b>PROFIsafe monitoring time F-WD-Time</b>	250 ms						
<b>response time</b>							
<ul style="list-style-type: none"><li>• in case of failure OFDT</li></ul>	200 ms						
<ul style="list-style-type: none"><li>• in faultless state WCDT</li></ul>	150 ms						
<b>Galvanic isolation</b>							
<b>(electrically) protective separation according to IEC 60947-1</b>	All circuits in SIMOCODE pro are with protective separation, i.e. they are designed with doubled creepage paths and clearances. NOTICE: The information in the "Protective Separation" test report, No. 2668, must be observed.						
<b>design of the electrical isolation</b>	Protective separation in accordance with IEC 60947-1 for all circuits, up to installation altitude of 2000 m						
<b>Control circuit/ Control</b>							
<b>type of voltage of the control supply voltage</b>	AC/DC						
<b>control supply voltage at AC</b>							
<ul style="list-style-type: none"><li>• at 50 Hz rated value</li></ul>	110 ... 240 V						
<ul style="list-style-type: none"><li>• at 60 Hz rated value</li></ul>	110 ... 240 V						
<b>control supply voltage frequency 1</b>	50 ... 60 Hz						
<b>control supply voltage frequency</b>							
<ul style="list-style-type: none"><li>• 1 rated value</li></ul>	50 Hz						
<ul style="list-style-type: none"><li>• 2 rated value</li></ul>	60 Hz						
<b>control supply voltage at DC</b>							
<ul style="list-style-type: none"><li>• rated value</li></ul>	110 ... 240 V						
<b>operating range factor control supply voltage rated value at DC</b>							
<ul style="list-style-type: none"><li>• initial value</li></ul>	0.85						
<ul style="list-style-type: none"><li>• full-scale value</li></ul>	1.1						
<b>operating range factor control supply voltage rated value at AC at 50 Hz</b>							
<ul style="list-style-type: none"><li>• initial value</li></ul>	0.85						
<ul style="list-style-type: none"><li>• full-scale value</li></ul>	1.1						
<b>operating range factor control supply voltage rated value at AC at 60 Hz</b>							
<ul style="list-style-type: none"><li>• initial value</li></ul>	0.85						
<ul style="list-style-type: none"><li>• full-scale value</li></ul>	1.1						
<b>inrush current peak</b>							
<ul style="list-style-type: none"><li>• at 240 V</li></ul>	24 A						
<b>duration of inrush current peak</b>							
<ul style="list-style-type: none"><li>• at 240 V</li></ul>	0.5 ms						
<b>Certificates/ approvals</b>							
<table><tr><td>General Product Approval</td><td>EMC</td></tr></table>		General Product Approval	EMC				
General Product Approval	EMC						
<table><tr><td></td><td><a href="#">Confirmation</a></td><td></td><td></td><td></td><td></td></tr></table>			<a href="#">Confirmation</a>				
	<a href="#">Confirmation</a>						
<table><tr><td>For use in hazardous locations</td><td>Functional Safety/Safety of Machinery</td><td>Declaration of Conformity</td></tr></table>		For use in hazardous locations	Functional Safety/Safety of Machinery	Declaration of Conformity			
For use in hazardous locations	Functional Safety/Safety of Machinery	Declaration of Conformity					



[Explosion Protection Certificate](#)

[Type Examination Certificate](#)



Test Certificates	Marine / Shipping	other
-------------------	-------------------	-------

[Type Test Certificates/Test Report](#)



[Confirmation](#)



other

[PROFIsafe-Certification](#)

#### Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3UF7330-1AU00-0>

Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3UF7330-1AU00-0>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)



<https://support.industry.siemens.com/cs/ww/en/ps/3UF7330-1AU00-0>


Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3UF7330-1AU00-0&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3UF7330-1AU00-0&lang=en)

Test report No. A0258, protective separation

<https://support.industry.siemens.com/cs/ww/en/view/109748152>





last modified:

5/9/2023 

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

3UF73301AU000