



Figure similar

Contactor, AC-1, 4-pole, 1000 A, main contacts 4 NO, Auxiliary contacts 2 NO + 2 NC, AC operation 220...230 V AC 50 Hz/240 V AC 60 Hz

protection class IP on the front	IP00
reference code according to IEC 81346-2	Q
Substance Prohibittance (Date)	07/01/2006
ambient temperature during operation	-25 ... +55 °C
number of poles for main current circuit	4
number of NO contacts for main contacts	4
number of NC contacts for main contacts	0
operational current <ul style="list-style-type: none"> <li>at AC-1 at 400 V <ul style="list-style-type: none"> <li>at ambient temperature 40 °C rated value</li> </ul> </li> <li>at AC-3 at 400 V rated value</li> </ul>	1 000 A 700 A
operating power <ul style="list-style-type: none"> <li>at AC-1 at 400 V rated value</li> <li>at AC-3 at 400 V rated value</li> </ul>	655 kW 370 kW
type of voltage of the control supply voltage	AC
control supply voltage at AC <ul style="list-style-type: none"> <li>at 50 Hz rated value</li> </ul>	230 V
control supply voltage frequency <ul style="list-style-type: none"> <li>1 rated value</li> <li>2 rated value</li> </ul>	50 Hz 60 Hz
control version of the switch operating mechanism	conventional
number of NC contacts for auxiliary contacts <ul style="list-style-type: none"> <li>instantaneous contact</li> <li>lagging switching</li> </ul>	2 2 0
number of NO contacts for auxiliary contacts <ul style="list-style-type: none"> <li>instantaneous contact</li> <li>leading contact</li> </ul>	2 0
identification number and letter for switching elements	22
fastening method <ul style="list-style-type: none"> <li>side-by-side mounting</li> </ul>	screw fixing Yes
height	272 mm
width	266 mm
depth	225.5 mm
type of electrical connection <ul style="list-style-type: none"> <li>for main current circuit</li> <li>for auxiliary and control circuit</li> </ul>	screw-type terminals screw-type terminals

### Further information

Siemens has decided to exit the Russian market (see here).  
<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>  
 Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

**Information on the packaging**

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<https://www.siemens.com/ic10>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3TK1742-0AP0>

**Cax online generator**

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3TK1742-0AP0>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/en/ps/3TK1742-0AP0>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mlfb=3TK1742-0AP0&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3TK1742-0AP0&lang=en)

**Characteristic: Tripping characteristics, I<sup>2</sup>t, Let-through current**

<https://support.industry.siemens.com/cs/ww/en/ps/3TK1742-0AP0/char>

**Further characteristics (e.g. electrical endurance, switching frequency)**

<http://www.automation.siemens.com/bilddb/index.aspx?view=Search&mlfb=3TK1742-0AP0&objecttype=14&gridview=view1>

---

last modified:

12/23/2020 

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

3TK17420AP0