



SIRIUS safety relay Safety-oriented Speed monitoring 24 V DC, 45 mm overall width Spring-type terminal EC instantaneous: 2 NO EC delayed: 0 SC: 2 electrical Auto-start/manual start Basic device Maximum achievable PL according to EN 13849-1: e Maximum achievable SIL according to IEC 61508: 3

product brand name	SIRIUS
product designation	Speed monitor
design of the product	standstill and speed monitoring
General technical data	
protection class IP of the enclosure	IP20
touch protection against electrical shock	finger-safe
insulation voltage rated value	300 V
ambient temperature	
• during storage	-20 ... +70 °C
• during operation	0 ... 60 °C
air pressure according to SN 31205	90 ... 106 kPa
relative humidity during operation	10 ... 95 %
installation altitude at height above sea level maximum	2 000 m
vibration resistance according to IEC 60068-2-6	10 ... 55 Hz: 0.35 mm
shock resistance	8g / 10 ms
surge voltage resistance rated value	4 000 V
EMC emitted interference	EN 60947-5-1
installation environment regarding EMC	This product is suitable for Class A environments only. In household environments, this device can cause unwanted radio interference. The user is required to implement appropriate measures in this case.
reference code according to DIN 40719 extended according to IEC 204-2 according to IEC 750	KT
reference code according to EN 61346-2	F
number of sensor inputs	
• 2-channel	3
• 1-channel or 2-channel	0
design of the cascading	none
type of the safety-related wiring of the inputs	single-channel or two-channel
product feature cross-circuit-proof	Yes
Safety Integrity Level (SIL)	
• according to IEC 61508	3
• according to IEC 62061	3
• for delayed release circuit according to IEC 61508	SIL3
SIL Claim Limit (subsystem) according to EN 62061	3
performance level (PL)	
• according to ISO 13849-1	e
• for delayed release circuit according to EN ISO 13849-1	e
category according to EN ISO 13849-1	4
hardware fault tolerance according to IEC 61508	1
safety device type according to IEC 61508-2	Type B
PFHD with high demand rate according to EN 62061	3.4E-9 1/h

T1 value for proof test interval or service life according to IEC 61508	20 a
number of outputs as contact-affected switching element	
• as NC contact	
— for signaling function instantaneous contact	0
— for signaling function delayed switching	0
— safety-related instantaneous contact	0
— safety-related delayed switching	0
• as NO contact	
— for signaling function instantaneous contact	0
— for signaling function delayed switching	0
— safety-related instantaneous contact	1
— safety-related delayed switching	1
number of outputs as contact-less semiconductor switching element	
• safety-related	
— delayed switching	0
— instantaneous contact	0
• for signaling function	
— delayed switching	1
— instantaneous contact	1
stop category according to EN 60204-1	0
Inputs	
design of input	
• cascading input/functional switching	No
• feedback input	Yes
• start input	Yes
Encoder	
encoder signal evaluation	two signal tracks each with inverted signals
type of signal level of the encoder	optionally TTL, HTL or sin/cos ($U_a = 1V_{ss}$)
type of failure response of the encoder	high-resistance
Proximity switch	
type of voltage of the supply voltage of proximity switches	DC
supply voltage of proximity switches	24 V; provided by the device
current consumption of proximity switches maximum	30 mA
type of switching output	optionally PNP or NPN
input voltage for proximity switch minimum	10 V
pulse duration of proximity switches minimum	75 μ s
interpulse period of proximity switches minimum	75 μ s
adjustment range of signal frequency of proximity switches	1 Hz ... 2 kHz
measuring precision	+2 %
switching hysteresis	6.25 %
Outputs	
switching capacity current	
• of semiconductor outputs	
— for signaling function at DC-13 at 24 V	0.02 A
• of the NO contacts of the relay outputs at DC-13	
— at 24 V	2 A
— at 115 V	2 A
• of the NO contacts of the relay outputs at AC-15	
— at 24 V	3 A
— at 230 V	3 A
• of the NC contacts of the relay outputs at AC-15	
— at 24 V	3 A
— at 115 V	3 A
— at 230 V	2 A
thermal current of the switching element with contacts maximum	5 A
electrical endurance (operating cycles) typical	100 000
mechanical service life (operating cycles) typical	50 000 000
design of the fuse link for short-circuit protection of the NO contacts of the relay outputs required	gL/gG: 4 A

Control circuit/ Control			
type of voltage of the control supply voltage		DC	
control supply voltage 1			
• at DC rated value		24 V	
operating range factor control supply voltage rated value of magnet coil			
• at DC		0.9 ... 1.1	
Installation/ mounting/ dimensions			
mounting position		any	
fastening method		screw and snap-on mounting	
width		45 mm	
height		107.7 mm	
depth		124.3 mm	
Connections/ Terminals			
type of electrical connection		spring-loaded terminals	
type of connectable conductor cross-sections			
• solid		0.5 ... 4 mm²	
• finely stranded			
— with core end processing		2 x (0.25 ... 1.5 mm²)	
— without core end processing		2x (0.25 ... 1.5 mm²)	
type of connectable conductor cross-sections for AWG cables			
• solid		2x (24 ... 16)	
• stranded		2x (20 ... 16)	
Product Function			
product function			
• light barrier monitoring		No	
• standstill monitoring		Yes	
• protective door monitoring		Yes	
• automatic start		Yes	
• magnetically operated switch monitoring NC-NO		No	
• rotation speed monitoring		Yes	
• laser scanner monitoring		No	
• monitored start-up		Yes	
• light array monitoring		No	
• magnetically operated switch monitoring NC-NC		No	
• EMERGENCY OFF function		Yes	
• pressure-sensitive mat monitoring		No	
suitability for interaction press control		No	
suitability for use			
• monitoring of floating sensors		Yes	
• monitoring of non-floating sensors		No	
• safety switch		Yes	
• position switch monitoring		Yes	
• EMERGENCY-OFF circuit monitoring		No	
• valve monitoring		No	
• tactile sensor monitoring		No	
• magnetically operated switch monitoring		No	
• safety-related circuits		Yes	
Certificates/ approvals			
certificate of suitability		EN ISO 13849, EN 62061, IEC 61508	
• TÜV (German technical inspectorate) certificate		Yes	
• UL approval		Yes	
• BG BIA approval		No	
General Product Approval		Declaration of Con- formity	Test Certificates



[Special Test Certificate](#)

[Confirmation](#)[Confirmation](#)

Further information

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<https://www.siemens.com/ic10>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3TK2810-1BA42>

Cax online generator



<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3TK2810-1BA42>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3TK2810-1BA42>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3TK2810-1BA42&lang=en





last modified:

4/11/2022 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[3TK28101BA42](#)