



Figure similar

SIPLUS LOGO! DM8 24R based on 6ED1055-1HB00-0BA2 with conformal coating, -40...+70 °C, start up -25 °C, expansion module, power supply / I/O: 24 V/24 V/relay, 2 MW 4 DI/4 DQ, AC/DC/NPN input for LOGO! 8

Installation type/mounting	
Mounting	on 35 mm DIN rail, 2 spacing units wide
Supply voltage	
Rated value (DC)	
• 24 V DC	Yes
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V
Rated value (AC)	
• 24 V AC	Yes
Line frequency	
• permissible range, lower limit	47 Hz
• permissible range, upper limit	63 Hz
Digital inputs	
Number of digital inputs	4
Input voltage	
• Type of input voltage	AC/DC
• for signal "0"	< 5 V AC/DC
• for signal "1"	> 12 V AC/DC
Input current	
• for signal "0", max. (permissible quiescent current)	1.1 mA
• for signal "1", typ.	5.5 mA
Input delay (for rated value of input voltage)	
for standard inputs	
— at "0" to "1", max.	1.5 ms
— at "1" to "0", max.	15 ms
Digital outputs	
Number of digital outputs	4; Relays
Short-circuit protection	No
Controlling a digital input	Yes
Switching capacity of the outputs	
• on lamp load, max.	1 000 W
Output current	
• for signal "1" rated value	5 A
• for signal "1" minimum load current	100 mA
Parallel switching of two outputs	
• for uprating	No
Switching frequency	
• with resistive load, max.	2 Hz
• with inductive load, max.	0.5 Hz

• mechanical, max.	10 Hz
<b>Relay outputs</b>	
<b>Switching capacity of contacts</b>	
— with inductive load, max.	3 A
— with resistive load, max.	5 A
<b>EMC</b>	
<b>Emission of radio interference acc. to EN 55 011</b>	
• Limit class B, for use in residential areas	Yes
<b>Degree and class of protection</b>	
IP degree of protection	IP20
<b>Ambient conditions</b>	
<b>Ambient temperature during operation</b>	
• min.	-40 °C; = Tmin; Startup @ -25 °C
• max.	70 °C; = Tmax; Tmax > +55 °C max. load 3 A per relay or max. total current 10 A
• At cold restart, min.	-25 °C; incl. condensation / frost permitted (no commissioning under condensation conditions)
<b>Ambient temperature during storage/transportation</b>	
• min.	-40 °C
• max.	70 °C
<b>Altitude during operation relating to sea level</b>	
• Installation altitude above sea level, max.	5 000 m
• Ambient air temperature-barometric pressure-altitude	Tmin ... Tmax at 1 140 hPa ... 795 hPa (-1 000 m ... +2 000 m) // Tmin ... (Tmax - 10 K) at 795 hPa ... 658 hPa (+2 000 m ... +3 500 m) // Tmin ... (Tmax -20 K) at 658 hPa ... 540 hPa (+3 500 m ... +5 000 m)
<b>Relative humidity</b>	
• With condensation, tested in accordance with IEC 60068-2-38, max.	100 %; RH incl. condensation / frost (no commissioning in bedewed state), horizontal installation
<b>Resistance</b>	
<b>Coolants and lubricants</b>	
— Resistant to commercially available coolants and lubricants	Yes; Incl. diesel and oil droplets in the air
<b>Use in stationary industrial systems</b>	
— to biologically active substances according to EN 60721-3-3	Yes; Class 3B2 mold, fungus and dry rot spores (with the exception of fauna); Class 3B3 on request
— to chemically active substances according to EN 60721-3-3	Yes; Class 3C4 (RH < 75 %) incl. salt spray acc. to EN 60068-2-52 (severity degree 3); *
— to mechanically active substances according to EN 60721-3-3	Yes; Class 3S4 incl. sand, dust, *
<b>Use on ships/at sea</b>	
— to biologically active substances according to EN 60721-3-6	Yes; Class 6B2 mold and fungal spores (excluding fauna); Class 6B3 on request
— to chemically active substances according to EN 60721-3-6	Yes; Class 6C3 (RH < 75 %) incl. salt spray acc. to EN 60068-2-52 (severity degree 3); *
— to mechanically active substances according to EN 60721-3-6	Yes; Class 6S3 incl. sand, dust; *
<b>Usage in industrial process technology</b>	
— Against chemically active substances acc. to EN 60654-4	Yes; Class 3 (excluding trichlorethylene)
— Environmental conditions for process, measuring and control systems acc. to ANSI/ISA-71.04	Yes; Level GX group A/B (excluding trichlorethylene; harmful gas concentrations up to the limits of EN 60721-3-3 class 3C4 permissible); level LC3 (salt spray) and level LB3 (oil)
<b>Remark</b>	
— Note regarding classification of environmental conditions acc. to EN 60721, EN 60654-4 and ANSI/ISA-71.04	* The supplied plug covers must remain in place over the unused interfaces during operation!
<b>Conformal coating</b>	
• Coatings for printed circuit board assemblies acc. to EN 61086	Yes; Class 2 for high reliability
• Protection against fouling acc. to EN 60664-3	Yes; Type 1 protection
• Military testing according to MIL-I-46058C, Amendment 7	Yes; Discoloration of coating possible during service life
• Qualification and Performance of Electrical Insulating Compound for Printed Board Assemblies according to IPC-CC-830A	Yes; Conformal coating, Class A
<b>Dimensions</b>	
Width	35.5 mm

Height	90 mm
Depth	58 mm

**last modified:**

3/12/2021 

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6AG10551HB007BA2](#)