

product type designation

product description



PROFIBUS connector

PROFIBUS bus connector, RS 485, screw, without programming port, 90°

SIPLUS DP PROFIBUS plug with R - without PG - 90 degrees based on 6ES7972-0BA12-0XA0 with conformal coating, -25...+70 °C, connection plug for PROFIBUS up to 12 Mbps, 90° cable outlet, terminating resistor with isolating function, without PG socket

suitability for use

For connecting PROFIBUS stations to the PROFIBUS bus cable

transfer rate

transfer rate / with PROFIBUS DP

9.6 kbit/s ... 12 Mbit/s

interfaces

number of electrical connections

- for PROFIBUS cables

2

- for network components or terminal equipment

1

type of electrical connection

- for PROFIBUS cables

Screw

- for network components or terminal equipment

9-pin sub D connector

mechanical data

design of terminating resistor

Resistor combination integrated and connectable via slide switch

material / of the enclosure

plastic

locking mechanism design

Screwed joint

design, dimensions and weights

type of cable outlet

90 degree cable outlet

width

15.8 mm

height

64 mm

depth

35.6 mm

net weight

10 g

ambient conditions

ambient temperature

- during operation
- during storage
- during transport
- in horizontal mounting position / during operation
- during storage and transport

-40 ... +70 °C

-40 ... +70 °C

-40 ... +70 °C

70 ... -40 °C

70 ... -40 °C

installation altitude / at height above sea level / maximum

5000 m

ambient condition / relating to ambient temperature - air pressure - installation altitude

Tmin ... Tmax at 1 140 hPa ... 795 hPa (-1 000 m ... +2 000 m) // Tmin ... (Tmax - 10 K) at 795 hPa ... 658 hPa (+2 000 m ... +3 500 m) // Tmin ... (Tmax -20 K) at 658 hPa ... 540 hPa (+3 500 m ... +5 000 m)

relative humidity

- with condensation / maximum
- with condensation / according to IEC 60068-2-38 / maximum

100 %; RH incl. condensation/frost permitted (no commissioning in bedewed state)

100 %; RH incl. condensation / frost (no commissioning in bedewed state), horizontal installation

resistance to biologically active substances

- conformity according to EN 60721-3-3

Yes; Class 3B2 mold, fungus and dry rot spores (with the exception of fauna); Class 3B3 on request

<ul style="list-style-type: none"> conformity according to EN 60721-3-6 	Yes; Class 6B2 mold and fungal spores (excluding fauna); Class 6B3 on request
resistance to chemically active substances <ul style="list-style-type: none"> conformity according to EN 60721-3-3 conformity according to EN 60721-3-6 	Yes; Class 3C4 (RH < 75 %) incl. salt spray acc. to EN 60068-2-52 (severity degree 3); * Yes; Class 6C3 (RH < 75 %) incl. salt spray acc. to EN 60068-2-52 (severity degree 3); *
resistance to mechanically active substances <ul style="list-style-type: none"> conformity according to EN 60721-3-3 conformity according to EN 60721-3-6 	Yes; Class 3S4 incl. sand, dust, * Yes; Class 6S3 incl. sand, dust; *
environmental category / according to IEC 60721 / note	* The supplied plug covers must remain in place over the unused interfaces during operation!
coating / for equipped printed circuit board / according to EN 61086	Yes; Class 2 for high reliability
type of coating <ul style="list-style-type: none"> protection against pollution according to EN 60664-3 for electronic devices in railway applications according to EN 50155 	Yes; Type 1 protection Yes; protective coating of the Class PC2 according to EN 50155:2020
type of test / of the coating / according to MIL-I-46058C	Yes; Discoloration of coating possible during service life
product conformity / of the coating / Qualification and Performance of Electrical Insulating Compound for Printed Board Assemblies according to IPC-CC-830A	Yes; Conformal coating, Class A
protection class IP	IP20
product features, product functions, product components / general	
product feature <ul style="list-style-type: none"> silicon-free 	Yes
product component <ul style="list-style-type: none"> PG connection socket strain relief 	No Yes
standards, specifications, approvals	
certificate of suitability <ul style="list-style-type: none"> RoHS conformity 	Yes
reference code <ul style="list-style-type: none"> according to IEC 81346-2 	XG
further information / internet links	
internet link <ul style="list-style-type: none"> to web page: selection aid TIA Selection Tool to website: Industrial communication to website: Industry Mall to website: Information and Download Center to website: Selection guide for cables and connectors to website: Image database to website: CAX-Download-Manager to website: Industry Online Support 	http://www.siemens.com/snst http://www.siemens.com/simatic-net https://mall.industry.siemens.com http://www.siemens.com/industry/infocenter https://sie.ag/2QdlxcP http://automation.siemens.com/bilddb http://www.siemens.com/cax https://support.industry.siemens.com

last modified:

8/11/2023 

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6AG19720BA122XA0](#)