

SIMATIC HMI KP32F PN, Key Panel, 32 short-stroke keys with multi-colored LEDs, PROFINET interfaces with PROFIsafe, 16 DI+16 DI/DO, 4 safety DI pins, 24 V DC can be looped through parameterizable as of STEP 7 V5.5



General information	
Product type designation	KP32F PN
Control elements	
With parameterizable keys	Yes
Keyboard fonts	
<ul style="list-style-type: none"> <li>Membrane keyboard <ul style="list-style-type: none"> <li>— user-definable label membrane keys</li> </ul> </li> <li>Function keys <ul style="list-style-type: none"> <li>— Number of function keys</li> </ul> </li> <li>Short-stroke keys <ul style="list-style-type: none"> <li>— Number of short-stroke keys</li> </ul> </li> </ul>	 Yes  32  32
Expansions for operator control of the process	
<ul style="list-style-type: none"> <li>DP direct LEDs (LEDs as S7 output I/O)</li> <li>Number of color modes for LED</li> <li>Direct keys (keys as S7 input I/O)</li> </ul>	 8; Adjustable brightness 5; red, green, blue, yellow, white 32
Installation type/mounting	
Mounting type	Mounting clip
Mounting position	vertical
Rack mounting	No
Front mounting	Yes
Rail mounting	No
Wall mounting/direct mounting	No
Mounting in portrait format possible	Yes
Mounting in landscape format possible	Yes
maximum permissible angle of inclination without external ventilation	30°; To the front/rear
Number of slots for command devices and signaling units	0
Supply voltage	
Type of supply voltage	DC
Rated value (DC)	24 V; 24 V looped through at connector, no interruption on pulling
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V
Input current	
Current consumption (rated value)	1 A
Type of output	
LED colors	
<ul style="list-style-type: none"> <li>red</li> <li>yellow</li> <li>green</li> <li>white</li> </ul>	 Yes Yes Yes Yes

• blue	Yes
<b>Digital inputs</b>	
Number of digital inputs	32; Total inputs and outputs max. 32 and 2x SIL 2 or 4x SIL 3
<b>Input voltage</b>	
• Rated value (DC)	24 V
<b>Digital outputs</b>	
Number of digital outputs	16; Max. 32 inputs and outputs (total)
Short-circuit protection	Yes
<b>Switching capacity of the outputs</b>	
• with resistive load, max.	100 mA
<b>Output voltage</b>	
• Rated value (DC)	24 V; Non-isolated
<b>Total current of the outputs</b>	
• Current per channel, max.	100 mA
• Current per group, max.	800 mA
<b>Interfaces</b>	
Number of industrial Ethernet interfaces	2; For the construction of lines and rings without external switch
Number of PROFINET interfaces	2; Incl. switch
<b>Industrial Ethernet</b>	
• Industrial Ethernet status LED	2; Per port
• Number of ports of the integrated switch	2; Per port
<b>Protocols</b>	
PROFINET	Yes; incl. shared device, 3rd party PLC
Supports protocol for PROFINET IO	Yes
PROFINET CBA	No
IRT	Yes
PROFIsafe	Yes; 2x SIL 3 (two-channel) or 4x SIL 2 (single-channel) emergency stop sensors
PROFIBUS	No
EtherNet/IP	No
MPI	No
AS-Interface	No
EIB/KNX	No
<b>Protocols (Ethernet)</b>	
• TCP/IP	No
<b>Redundancy mode</b>	
<b>Media redundancy</b>	
— MRP	Yes
<b>Further protocols</b>	
• AS-Interface Safety at Work	No
• CAN	No
• Data-Highway	No
• DeviceNet	No
• DeviceNet Safety	No
• Foundation Fieldbus	No
• INTERBUS	No
• INTERBUS-Safety	No
• Local Operating Network	No
• MODBUS	No
• SafetyBUS p	No
• SERCOS	No
• SUCOnet	No
• other bus systems	No
<b>Test commissioning functions</b>	
Illuminant test	Yes; During switch on
Key and signal lamp test	Yes; automatically when switching on
<b>EMC</b>	
<b>Emission of radio interference acc. to EN 55 011</b>	
• Limit class A, for use in industrial areas	Yes; Group 1, measured at a distance of 10 m
• Limit class B, for use in residential areas	No

<b>Degree and class of protection</b>	
IP (at the front)	IP65
IP (rear)	IP20
NEMA (front)	
• Enclosure Type 4 at the front	No
• Enclosure Type 4x at the front	Yes; Incl. NEMA12
<b>Standards, approvals, certificates</b>	
CE mark	Yes
cULus	Yes
RCM (formerly C-TICK)	Yes
KC approval	Yes
EAC (formerly Gost-R)	Yes
CCC	No; not necessary
Suitable for safety functions	Yes
<b>Use in hazardous areas</b>	
• ATEX Zone 2	No
• ATEX Zone 22	No
• cULus Class I Zone 1	No
• cULus Class I Zone 2, Division 2	No
• FM Class I Division 2	No
<b>Marine approval</b>	
• Germanischer Lloyd (GL)	No
• American Bureau of Shipping (ABS)	No
• Bureau Veritas (BV)	No
• Det Norske Veritas (DNV)	No
• Lloyds Register of Shipping (LRS)	No
• Nippon Kaiji Kyokai (Class NK)	No
• Polski Rejestr Statkow (PRS)	No
<b>Ambient conditions</b>	
<b>Ambient temperature during operation</b>	
• min.	0 °C
• max.	55 °C
<b>Operation (vertical installation)</b>	
— For vertical installation, min.	0 °C
— For vertical installation, max.	55 °C
<b>Operation (max. tilt angle)</b>	
— At maximum tilt angle, min.	0 °C
— At maximum tilt angle, max.	45 °C
<b>Operation (vertical installation, portrait format)</b>	
— For vertical installation, min.	0 °C
— For vertical installation, max.	55 °C
<b>Operation (max. tilt angle, portrait format)</b>	
— At maximum tilt angle, min.	0 °C
— At maximum tilt angle, max.	45 °C
<b>Ambient temperature during storage/transportation</b>	
• min.	-20 °C
• max.	60 °C
<b>Relative humidity</b>	
• Operation, max.	95 %; no condensation
<b>configuration / header</b>	
<b>Configuration software</b>	
• STEP 7 Basic (TIA Portal)	Yes
• STEP 7 Professional (TIA Portal)	Yes
<b>Functionality under WinCC (TIA Portal)</b>	
<b>Process coupling</b>	
• S7-1200	Yes; with ET 200pro CPU and ET 200S CPU
• S7-1500	Yes
• S7-200	No
• S7-300/400	Yes; with F-CPU: STEP 7 V11 SP1 or higher and Safety V11 (or higher), without F-CPU STEP 7 or SIMATIC STEP 7 Basic V11 (or higher)
• LOGO!	No

• WinAC	Yes
• SINUMERIK	No
• SIMOTION	No
• Allen Bradley (EtherNet/IP)	No
• Allen Bradley (DF1)	No
• Mitsubishi (MC TCP/IP)	No
• Mitsubishi (FX)	No
• OMRON (FINS TCP)	No
• OMRON (LINK/Multilink)	No
• Modicon (Modbus TCP/IP)	No
• Modicon (Modbus)	No
<b>Mechanics/material</b>	
Enclosure material (front)	
• Plastic	No
• Aluminum	Yes
• Stainless steel	No
<b>Service life</b>	
• Short-stroke keys (in switching cycles)	1 500 000
• LEDs (ON period)	100 %
<b>Dimensions</b>	
Width of the housing front	295 mm
Height of housing front	155 mm
Mounting cutout, width	277 mm; Max. thickness of mounting plate 2 - 6 mm
Mounting cutout, height	137 mm
Overall depth	69 mm; Incl. angled SIMATIC Ethernet connector
<b>Weights</b>	
Weight (without packaging)	1 220 g
<b>last modified:</b>	8/7/2023 

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6AV36883EH470AX0](#)