

SITOP PSU100D/1AC/24VDC/4.1A

***** spare part ***** PSU100D 24 V/4.1 A stabilized power supply input:
100-240 V AC output: 24 V DC/4.1 A



Input	
type of the power supply network	1-phase AC
supply voltage at AC	
• minimum rated value	100 V
• maximum rated value	240 V
• initial value	85 V
• full-scale value	264 V
design of input wide range input	Yes
operating condition of the mains buffering	at $V_{in} = 115/230$ V
buffering time for rated value of the output current in the event of power failure minimum	15 ms
operating condition of the mains buffering	at $V_{in} = 115/230$ V
line frequency	
• 1 rated value	50 Hz
• 2 rated value	60 Hz
line frequency	47 ... 63 Hz
input current	
• at rated input voltage 100 V	2 A
• at rated input voltage 240 V	1.1 A
current limitation of inrush current at 25 °C maximum	75 A
I ² t value maximum	4 A ² s
fuse protection type	internal
• in the feeder	Recommended miniature circuit breaker: from 10 A characteristic C or from 16 A characteristic B
Output	
voltage curve at output	Controlled, isolated DC voltage
output voltage at DC rated value	24 V
output voltage	
• at output 1 at DC rated value	24 V
relative overall tolerance of the voltage	2 %
relative control precision of the output voltage	
• on slow fluctuation of input voltage	0.5 %
• on slow fluctuation of ohm loading	1 %
residual ripple	
• maximum	100 mV
voltage peak	
• maximum	100 mV
adjustable output voltage	22 ... 28 V
product function output voltage adjustable	Yes
type of output voltage setting	via potentiometer
display version for normal operation	Green LED for 24 V OK

behavior of the output voltage when switching on	Overshoot of Vout < 2 %
response delay maximum	1 s
voltage increase time of the output voltage • maximum	30 ms
output current • rated value • rated range	4.1 A 0 ... 4.1 A; +50 ... +70 °C: Derating 2.5%/K
supplied active power typical	100 W
product feature • bridging of equipment	Yes
number of parallel-switched equipment resources for increasing the power	2
Efficiency	
efficiency in percent	86 %
power loss [W] • at rated output voltage for rated value of the output current typical	16 W
Closed-loop control	
relative control precision of the output voltage with rapid fluctuation of the input voltage by +/- 15% typical	0.5 %
relative control precision of the output voltage load step of resistive load 50/100/50 % typical	5 %
Protection and monitoring	
design of the overvoltage protection • typical	< 35 V 4.9 A
property of the output short-circuit proof	Yes
design of short-circuit protection	Electronic shutdown, automatic restart
enduring short circuit current RMS value • typical	10 A
display version for overload and short circuit	-
Safety	
galvanic isolation between input and output	Yes
galvanic isolation	Safety extra low output voltage Vout according to EN 60950-1
operating resource protection class	Class I
leakage current • maximum • typical	3.5 mA 1 mA
protection class IP	IP20
Approvals	
certificate of suitability • CE marking • UL approval • CSA approval • cCSAus, Class 1, Division 2 • ATEX	Yes Yes; cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cURus (UL 60950-1, CSA C22.2 No. 60950-1), File E151273 Yes; cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259; cURus (UL 60950-1, CSA C22.2 No. 60950-1), File E151273 No No
certificate of suitability • IECEx • NEC Class 2 • ULhazloc approval • FM registration	No No No No
type of certification CB-certificate	Yes
certificate of suitability • EAC approval	Yes
certificate of suitability shipbuilding approval	No
shipbuilding approval	-
Marine classification association • American Bureau of Shipping Europe Ltd. (ABS) • French marine classification society (BV) • DNV GL • Lloyds Register of Shipping (LRS)	No No No No

• Nippon Kaiji Kyokai (NK)	No
EMC	
standard	
• for emitted interference	EN 55022 Class B
• for mains harmonics limitation	EN 61000-3-2
• for interference immunity	EN 61000-6-2
environmental conditions	
ambient temperature	
• during operation	-10 ... +70 °C; with natural convection
• during transport	-40 ... +85 °C
• during storage	-40 ... +85 °C
Mechanics	
type of electrical connection	screw-type terminals
• at input	L, N, PE: 1 screw terminal each for 0.3 ... 1.3 mm ² single-core/finely stranded
• at output	+, -: 2 screw terminals each for 0.3 ... 1.3 mm ²
• for auxiliary contacts	-
width of the enclosure	97 mm
height of the enclosure	158 mm
depth of the enclosure	38 mm
required spacing	
• top	20 mm
• bottom	0 mm
• left	20 mm
• right	20 mm
net weight	0.5 kg
fastening method	Wall mounting
other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Siemens:](#)

[6EP13321LD10](#)