



SITOP PSU3400/1ACDC/DC24V/2.5A

SITOP PSU3400 uni 24 V/2.5 A Stabilized power supply Input: 230 V AC (88...264 V) input: 24 V DC (18...264 V) output: 24 V DC/2.5 A

Input	
type of the power supply network	1-phase AC or DC
supply voltage at AC <ul style="list-style-type: none"> <li>• minimum rated value</li> <li>• maximum rated value</li> <li>• initial value</li> <li>• full-scale value</li> </ul>	120 V 240 V 88 V; Startup as of 18 V 264 V
supply voltage <ul style="list-style-type: none"> <li>• at DC</li> </ul>	24 ... 24 V
input voltage <ul style="list-style-type: none"> <li>• at DC</li> </ul>	18 ... 264 V
design of input wide range input	Yes
overvoltage overload capability	-
operating condition of the mains buffering	at Vin rated
buffering time for rated value of the output current in the event of power failure minimum	5 ms
operating condition of the mains buffering	at Vin rated
line frequency <ul style="list-style-type: none"> <li>• 1 rated value</li> <li>• 2 rated value</li> </ul>	50 Hz 60 Hz
line frequency	47 ... 63 Hz
input current <ul style="list-style-type: none"> <li>• at rated input voltage 24 V</li> </ul>	1.9 A
current limitation of inrush current at 25 °C maximum	15 A
I <sup>2</sup> t value maximum	0.09 A <sup>2</sup> ·s
fuse protection type <ul style="list-style-type: none"> <li>• in the feeder</li> </ul>	15 A (not accessible), breaking capacity 100 A Recommended miniature circuit breaker: 16 A characteristic B or C
Output	
voltage curve at output	Controlled, isolated DC voltage
output voltage at DC rated value	24 V
output voltage <ul style="list-style-type: none"> <li>• at output 1 at DC rated value</li> </ul>	24 V
relative overall tolerance of the voltage	1 %
relative control precision of the output voltage <ul style="list-style-type: none"> <li>• on slow fluctuation of input voltage</li> <li>• on slow fluctuation of ohm loading</li> </ul>	0.1 % 0.2 %
residual ripple <ul style="list-style-type: none"> <li>• maximum</li> <li>• typical</li> </ul>	150 mV 30 mV
voltage peak	

<ul style="list-style-type: none"> <li>• maximum</li> </ul>	250 mV
<ul style="list-style-type: none"> <li>• typical</li> </ul>	70 mV
adjustable output voltage	24 ... 28 V
product function output voltage adjustable	Yes
type of output voltage setting	via potentiometer
display version for normal operation	Green LED for 24 V OK
behavior of the output voltage when switching on	No overshoot of Vout (soft start)
response delay maximum	0.5 s
voltage increase time of the output voltage	
<ul style="list-style-type: none"> <li>• typical</li> </ul>	10 ms
<ul style="list-style-type: none"> <li>• maximum</li> </ul>	20 ms
output current	
<ul style="list-style-type: none"> <li>• rated value</li> </ul>	2.5 A
<ul style="list-style-type: none"> <li>• rated range</li> </ul>	0 ... 3.5 A; +60 to +70 °C: without derating
supplied active power typical	85 W
product feature	
<ul style="list-style-type: none"> <li>• bridging of equipment</li> </ul>	Yes
number of parallel-switched equipment resources for increasing the power	2
<b>Efficiency</b>	
efficiency in percent	85 %
power loss [W]	
<ul style="list-style-type: none"> <li>• at rated output voltage for rated value of the output current typical</li> </ul>	7 W
<ul style="list-style-type: none"> <li>• during no-load operation maximum</li> </ul>	1.5 W
<b>Closed-loop control</b>	
relative control precision of the output voltage with rapid fluctuation of the input voltage by +/- 15% typical	0.3 %
relative control precision of the output voltage load step of resistive load 50/100/50 % typical	2 %
setting time	
<ul style="list-style-type: none"> <li>• load step 50 to 100% typical</li> </ul>	1 ms
<ul style="list-style-type: none"> <li>• load step 100 to 50% typical</li> </ul>	1 ms
<b>Protection and monitoring</b>	
design of the overvoltage protection	Ua < 35 V
<ul style="list-style-type: none"> <li>• typical</li> </ul>	3.8 A
property of the output short-circuit proof	Yes
design of short-circuit protection	Electronic shutdown, automatic restart
display version for overload and short circuit	LED yellow for "overload"
<b>Safety</b>	
galvanic isolation between input and output	Yes
galvanic isolation	Safety extra low output voltage Vout according to EN 60950-1
operating resource protection class	Class III
protection class IP	IP20
<b>Approvals</b>	
certificate of suitability	
<ul style="list-style-type: none"> <li>• CE marking</li> </ul>	Yes
<ul style="list-style-type: none"> <li>• UL approval</li> </ul>	Yes; cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259
<ul style="list-style-type: none"> <li>• CSA approval</li> </ul>	Yes; cULus-Listed (UL 508, CSA C22.2 No. 107.1), File E197259
<ul style="list-style-type: none"> <li>• cCSAus, Class 1, Division 2</li> </ul>	No
<ul style="list-style-type: none"> <li>• ATEX</li> </ul>	No
certificate of suitability	
<ul style="list-style-type: none"> <li>• IECEx</li> </ul>	No
<ul style="list-style-type: none"> <li>• NEC Class 2</li> </ul>	No
<ul style="list-style-type: none"> <li>• ULhazloc approval</li> </ul>	No
<ul style="list-style-type: none"> <li>• FM registration</li> </ul>	No
type of certification CB-certificate	Yes
certificate of suitability	
<ul style="list-style-type: none"> <li>• EAC approval</li> </ul>	No
<ul style="list-style-type: none"> <li>• Regulatory Compliance Mark (RCM)</li> </ul>	Yes
certificate of suitability shipbuilding approval	No
shipbuilding approval	-

Marine classification association	
• American Bureau of Shipping Europe Ltd. (ABS)	No
• French marine classification society (BV)	No
• DNV GL	No
• Lloyds Register of Shipping (LRS)	No
• Nippon Kaiji Kyokai (NK)	No
<b>EMC</b>	
standard	
• for emitted interference	EN 61000-6-3
• for mains harmonics limitation	not applicable
• for interference immunity	EN 61000-6-2
<b>environmental conditions</b>	
ambient temperature	
• during operation	-25 ... +70 °C; with natural convection
• during transport	-40 ... +85 °C
• during storage	-40 ... +85 °C
environmental category according to IEC 60721	Climate class 3K3, 5 ... 95% no condensation
<b>Mechanics</b>	
type of electrical connection	screw-type terminals
• at input	L, N, FE: 1 screw terminal each for 0.5 ... 2.5 mm <sup>2</sup> single-core/finely stranded
• at output	+, -: 2 screw terminals each for 0.5 ... 2.5 mm <sup>2</sup>
width of the enclosure	32 mm
height of the enclosure	100 mm
depth of the enclosure	100 mm
required spacing	
• top	50 mm
• bottom	50 mm
• left	0 mm
• right	0 mm
net weight	0.32 kg
product feature of the enclosure housing can be lined up	Yes
fastening method	Snaps onto DIN rail EN 60715 35x7.5/15
electrical accessories	Buffer module
MTBF at 40 °C	1 934 648 h
other information	Specifications at rated input voltage and ambient temperature +25 °C (unless otherwise specified)



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Siemens:

[6EP33320TA000AY0](#)